

## ix Industrial 10B-1 plug A1-S



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 181 9020 XL
Specification	ix Industrial 10B-1 plug A1-S
HARTING eCatalogue	<a href="https://b2b.harting.com/09451819020XL">https://b2b.harting.com/09451819020XL</a>

### Identification

Category	Connectors
Series	HARTING ix Industrial®
Identification	Signal
Element	Cable connector
Specification	Angled bottom

### Version

Termination method	Solder termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	10
Coding	Type B
Pack contents	Bulk packaging

### Technical characteristics

Conductor cross-section	AWG 28/7 ... AWG 22/7
Wire outer diameter	≤1.55 mm
Rated current	1.5 A
Rated current	3 A when used with 4 contacts (1,2,6,7)
Rated voltage	50 V AC 60 V DC
Insulation resistance	>500 MΩ
Contact resistance	≤30 mΩ
Shielding resistance	≤100 mΩ



**Pushing Performance**  
Since 1945

## Technical characteristics

Limiting temperature	-40 ... +85 °C
Storage temperature	-30 ... +60 °C
Relative humidity	95 % Non-condensing (operation) 95 % Non-condensing (storage/transport)
Insertion force	≤25 N
Withdrawal force	≤25 N
Mating cycles	≥5,000
Degree of protection acc. to IEC 60529	IP20
Cable diameter	5.5 ... 7.2 mm
Test voltage $U_{r.m.s.}$	0.5 kV
Retention force	≥80 N locking

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side ( $\geq 0.2 \mu\text{m}$ ) Au over Ni Termination side ( $\geq 0.03 \mu\text{m}$ ) Ni Termination side (shielding case $\geq 1 \mu\text{m}$ ) Ni Termination side (shielding shell $\geq 0.2 \mu\text{m}$ )
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Specifications	IEC 61076-3-124 EN 45545-2 IEEE 802.3af Power over Ethernet (PoE) IEEE 802.3at Power over Ethernet (PoE+) IEEE 802.3bt Power over Ethernet (4PPoE)
----------------	--

## Specifications and approvals


UL / CSA

UL 1977 ECBT2.E102079  
CSA-C22.2 No. 182.3 ECBT8.E102079

## Commercial data

Packaging size	100
Net weight	4.88 g
Country of origin	Japan
European customs tariff number	85366990
GTIN	5713140223325
eCl@ss	27440114 Rectangular connector (for field assembly)

## Contact configuration



## Environmental Specifications

Rapid change of temperature (IEC 60512-11d)	10 cycles between -55°C and 85°C with 30 minutes dwell at temp. extremes and 2 to 3 minutes transition between temperatures
Dry heat (IEC 60512-11i)	+85°C, 500 h
Damp heat cycles (IEC 60068-2-38)	25°C to 65°C; cold sub-cycle: -10°C; relative humidity 93%; 10 cycles, 1 cycle/24h
Cold (IEC 60512-11j)	-55°C, 240h
Flow mixed gas test (IEC 60068-2-60)	4 d, Method 4 (mated and unmated)
Corrosion salt mist	Exposed at 5% salt water, 35°C, 48h (unmated); no heavy corrosion of contacts
Vibration, sinusoidal (IEC 60512-test 6d)	10 to 500 Hz; 0.35 mm, 50 m/s <sup>2</sup> , 2h / 3 axis; no contact disturbances ≥ 1µs
Mechanical shock (IEC 60512-test 6d)	half-sine shock 300 m/s <sup>2</sup> , 11 ms 3 shocks / both directions / 3 axis - totally 18 shocks no contact disturbances ≥ 1µs
Fretting Corrosion	490 m/s <sup>2</sup> , 230 times/min at 1000 times no contact disturbances ≥ 1µs