



Ledinaire Waterproof WT065C

WT065C G2 LED24S/840 PSU L1200

Ledinaire Waterproof WT065C - L1200 mm - Symmetrical - Opal - IP65 - IK08 - TW1-ready

The Ledinaire Waterproof range provides maximum performance and durability at great value. As an off-the-shelf LED luminaire solution for all your everyday needs, it can be deployed in a wide variety of locations.

Product data

General information	
Light source replaceable	Yes
Number of gear units	Unit
Driver included	Yes
Lighting Technology	LED
Value ladder	Value
Light technical	
Luminous Flux	2,400 lm
Saturated Red (R9)	<50
Correlated Colour Temperature	4000 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Colour rendering index (CRI)	>80
Flickering value (PstLM)	1
Stroboscopic effect	2
Light source colour	840 neutral white
Optic type	Symmetrical
Luminaire light beam spread	120°

Unified Glare Rating (CEN)	28
Operating and electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Input frequency	50 or 60 Hz
Inrush current	5.16 A
Inrush time	0.047 ms
Power Consumption	22 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	60
Temperature	
Ambient temperature range	-20 to +40 °C

Ledinaire Waterproof WT065C

Controls and dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit
Constant light output	No

Mechanical and housing

Housing material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	Grey
Optical cover/lens finish	Opal
Overall length	1,207 mm
Overall width	71 mm
Overall height	74 mm
Dimensions (height x width x depth)	74 x 71 x 1207 mm

Approval and application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Sustainability rating	-
Protection class IEC	Safety class I
Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	-
Warranty period	3 years
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m

EU RoHS compliant	Yes
-------------------	-----

Initial performance (IEC compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38) SDCM≤6
Power consumption tolerance	+/-10%

Over time performance (IEC compliant)

Control gear failure rate at median useful life 50,000 h	7.5 %
Lumen maintenance at median useful life* 50,000 h	65

Application conditions


Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No

Product data

Full EOC	871951453104899
Order product name	WT065C G2 LED24S/840 PSU L1200
Order code	53104899
Local order code	TEST1
SAP numerator – quantity per pack	1
Numerator – packs per outer box	9
Material number (12NC)	911401854882
Full product name	WT065C G2 LED24S/840 PSU L1200
EAN/UPC - Case	8719514531093
Local code description	TEST2



Dimensional drawing



WT065C G2 L1200

Ledinaire Waterproof WT065C

