

TECHNICAL DATA SHEET

Description: 791-2170MHz SMT Antenna

Series: Domino
PART NUMBER: W3326

Features:

- Frequency:791-960/1710-2170MHz
- Size 20 x 7 x 1.5mm
- Gain 0.6 / 2.3dBi
- Efficiency >50/50%
- SMD compatible





Applications:

- Nb-IoT
- LTE Cat-M1
- High and low bands combo
- Sensors
- IoT connected devices

All dimensions are in mm / inches

Issue: 2039

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:

Pulse Worldwide Headquarters 15255 Innovation Drive #100 San Diego, CA 92128 USA Tel:1-858-674-8100 Pulse/Larsen Antennas 18110 SE 34th St Bldg 2 Suite 250 Vancouver, WA 98683 USA Tel: 1-360-944-7551 Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0 Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4th Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998



TECHNICAL DATA SHEET

Description: 791-2170MHz SMT Antenna

Series: Domino

PART NUMBER: W3326

ELECTRICAL SPECIFICATIONS

Antenna Type PCB, SMD Frequency 791-960MHz

1710-2170MHz

Nominal Impedance 50Ω Return loss 5dB Radiation Pattern Omni

Peak Gain 0.6 / 2.3 dBi
Nominal Efficiency 50 / 50 %
Polarization Vertical

MECHANICAL SPECIFICATIONS

Overall Length 20mm(L) * 7mm(W) * 1.5mm(T)

Weight 1.3g

Antenna Color / Material Black / Composite

Assembly method SMD / Reflow Packing Tape & Reel

Moisture Sensitivity Level MSL3

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature -40~+85° C
Storage Temperature -40~+85° C

RoHS Compliant Yes

OTHER SPECIFICATIONS

(*) All RF parameters measured on Pulse reference test PCB









Series: Domino

PART NUMBER: W3326










Series: Domino

PART NUMBER: W3326









Series: Domino

PART NUMBER: W3326












Series: Domino

PART NUMBER: W3326



Detail A






Series: Domino

PART NUMBER: W3326

TEST SETUP









Series: Domino

PART NUMBER: W3326

CHARTS

Return Loss










Series: Domino


PART NUMBER: W3326

CHARTS

Gain(dBi)



Efficiency(%)









Series: Domino

PART NUMBER: W3326

CHARTS

Radiation Pattern 2D (791-960MHz)







790MHz

790MHz

Avg(dBi) = -2.19

Peak(dBi) = -1.48

Avg -3(deg) = 359 5

Avg (dBi) = -1.52Peak (dBi) = -0.84

Avg -3 (deg) = 359.5

960MHz

Avg (dBi) = -0.68

Peak (dBi) = 0.43

Avg -3 (deg) = 359.5

870MHz

870MHz

-960MHz







Series: Domino


PART NUMBER: W3326

CHARTS

Radiation Pattern 2D (1710-2170MHz)












Series: Domino

PART NUMBER: W3326

PACKAGING

1000pcs Antennas Per 1pcs 13" Tape & Reel 1pc Reel per vacuum bag 3 pcs 13" reel with vacuum bag per carton box Total 3000pcs Antennas per 1 box Carton Box Dimension: 350x350x120 mm



According to MSL3 packing requirement, MBB-Moisture Barrel Bag, Desiccant, HIC-Humidity Indicator Card, MSID Label, Caution Label are required.