









Vehicular – Twin Castle (TWC) Series

5G-FR1+WiFi 6E+GNSS L1 Direct Mount 9-in-1 Antenna

TWC94411DM and TWC94412DM - 617 to 7125 MHz



Features & Applications:

-  Vehicle roof mount, directly on metal plane
-  4 port 5G/4G
-  4 port WiFi 6E, DSRC, V2X
-  1 port Active GNSS L1 with low noise 30dB amplifier
-  Cable length and connector type per request
-  Available in Black (P/N TWC94411DM) or White (P/N TWC94412DM)
-  Heavy and light vehicles
-  IoT, navigation, tracking

ELECTRICAL SPECIFICATIONS @ 25°C

General Specifications – 5G FR1 + WiFi 6E

Antenna type	Nominal Impedance	Polarization	Radiation pattern	Power withstanding	DC Ground
Monopole ¹	50Ω	Vertical / Linear	Omni	45W	No

5G FR1 Antennas: 617 – 7125MHz

Ports	Frequency (MHz)	617-960	1710-2700	3300-4200	4400-5000	5150-5925	6000-7125
Port 1 & 4 (Main)	VSWR	3:1	2:1	2.5:1	2.5:1	2.5:1	2.5:1
	Avg. Peak Gain (dBi)	2.5	5.0	5.9	7.2	6.4	4.5
	Avg. Efficiency (%)	60	64	58	56	58	51
	Avg. HPBW (°)	82	40	27	21	23	40
Port 2 & 3 (Secondary)	VSWR	3:1	2:1	2.5:1	2.5:1	2.5:1	2.5:1
	Avg. Peak Gain (dBi)	2.4	5.5	7.4	7.2	6.8	5.5
	Avg. Efficiency (%)	47	61	60	57	58	51
	Avg. HPBW (°)	77	31	27	24	26	21
Port – Port Isolation ²	Port 1-2 / Port 3-4 (dB)	8	20	19	18	20	29
	Port 1-3 / Port 2-4 (dB)	13	25	24	30	28	36
	Port 1-4 (dB)	21	24	26	29	36	39

WiFi 6E Antennas: 2400-2500/ 4900-7125MHz

Ports	Frequency (MHz)	2400-2500	4900-7125
Port 1 & 4 (WiFi)	VSWR	2:1	2:5
	Avg. Peak Gain (dBi)	6.3	5.8
	Avg. Efficiency (%)	69	60
	Avg. HPBW (°)	34	23
Port 2 & 3 (WiFi)	VSWR	2:1	2:5
	Peak Gain (dBi)	6.0	6.5
	Avg. Efficiency (%)	60	60
	Avg. HPBW (°)	35	30
Port – Port Isolation ³	Port 1-2 / Port 3-4 (dB)	17	17
	Port 1-3 / Port 2-4 (dB)	23	28
	Port 1-4 (dB)	26	37

Notes:

1. (8) Multi-Band Monopoles with built in ground plane, Independent from external ground plane
2. Minimum Isolation (dB)
3. Black antenna P/N TWC94411DM, White antenna P/N TWC94412DM

Vehicular – Twin Castle (TWC) Series 5G-FR1+WiFi 6E+GNSS L1 Direct Mount 9-in-1 Antenna

TWC94411DM and TWC94412DM - 617 to 7125 MHz

GNSS Antenna: 1561.098 +/- 2.046MHz, 1575.42 +/- 1.023MHz, 1602.5625 +/- 4MHz				
Frequency (MHz)	1561.098 +/- 2.046	1575.42 +/- 1.023	1602.5625 +/- 4	
VSWR	2:1	2:1	2:1	
Gain – Radiating Element (dBic)	-5 +/- 1	-0.8 +/- 1	4.4 +/- 1	
Polarization	LNA Gain (dB)	Noise Figure (dB)	Operating Voltage (V _{dc})	Current Consumption (mA)
RHCP	30 +/- 2	< 2.4	3.3 – 5.0	< 11
Frequency (MHz)	960	1710	2170	2400
Out of Band Rejection (dB)	> 65	> 60	> 65	> 65

MECHANICAL SPECIFICATIONS

TWC94411DM (2DM)

Dimension (Length x Width x Height)	Housing Material	Color ³	Weight	Fixing System	Mounting Hole Diameter
275.3 x 123.4 x 92.3 mm (10.84 x 4.86 x 3.63 inch)	PC/ABS, UV Protected	Black or White	894g (1.85lbs)	Direct Mount	1.063" (27mm)
Wireless Technology	No. of Port	Cable Length	Cable Type	Connector Type	
5G FR1	4	1ft (0.3m)	RG-316	SMA (Male)	
WiFi 6E	4	1ft (0.3m)	RG-316	SMA (Male)	
GNSS L1	1	1ft (0.3m)	RG-174	SMA (Male)	


ENVIRONMENTAL SPECIFICATIONS

TWC94411DM (2DM)

Operating Temperature	Storage Temperature	Ingress Protection	RoHS Compliant
-40/+85° C	-40/+85° C	IP67	Yes

Mechanical Drawing

TWC94411DM (2DM)




Dimensions: inches (mm) Unless otherwise specified, all tolerances are ±.010 (0.25mm)

Test Setup


General / Chamber Setup

- All measurements done on Ø 600mm (24") round ground plane.
- S-parameters with 0.3m (1ft) RG316 cable
- Gain and Efficiency with 0.3m (1ft) RG316 cable
- Measured at Pulse, USA (in ETS chamber)




Charts-VSWR

5G FR1




Charts-Isolation

5G FR1




Charts-Isolation

5G FR1




Charts-Peak Gain

5G FR1




Charts- Peak Efficiency

5G FR1




Radiation Pattern – 5G FR1 – Port 1 – XY & XZ Gain Plots

5G FR1 Port 1




Radiation Pattern – 5G FR1 – Port 2 – XY & XZ Gain Plots

5G FR1 Port 2




Radiation Pattern – 5G FR1 – Port 3 - XY & XZ Gain Plots

5G FR1 Port 3




Radiation Pattern – 5G FR1 – Port 4 - XY & XZ Gain Plots

5G FR1 Port 4




Charts-VSWR

WiFi 6E




Charts-Isolation

WiFi 6E




Charts-Peak Gain

WiFi 6E




Charts- Peak Efficiency

WiFi 6E




Radiation Pattern – WiFi 6E – Port 1 - XY & XZ Gain Plots

WiFi 6E Port 1




Radiation Pattern – WiFi 6E – Port 2 - XY & XZ Gain Plots

WiFi 6E Port 2




Radiation Pattern – WiFi 6E – Port 3 - XY & XZ Gain Plots

WiFi 6E Port 3



Radiation Pattern – WiFi 6E – Port 4 - XY & XZ Gain Plots

WiFi 6E Port 4




Vehicular – Twin Castle (TWC) Series 5G-FR1+WiFi 6E+GNSS L1 Direct Mount 9-in-1 Antenna


TWC94411DM and TWC94412DM - 617 to 7125 MHz

GNSS Antenna - LNA Gain and Radiation Pattern (YZ Plane) Plots

LNA gain and Out-of-band Rejection



YZ Plane: Passive measurement with 6" cable



Vehicular – Twin Castle (TWC) Series 5G-FR1+WiFi 6E+GNSS L1 Direct Mount 9-in-1 Antenna

TWC94411DM and TWC94412DM - 617 to 7125 MHz

PACKAGING

TWC94411DM (2DM)

1pcs antennas per plastic bag
2pcs antennas per package box
Package box: 17x x12 x 9in

Additional Product Info

Cable Assemblies for
TWC94411DM (2DM) (Not included)



TWC (Twin Castle) Cable Assemblies

TWC Cable Assemblies

Orderable P/N ¹	5G FR1 Port 1	5G FR1 Port 2	5G FR1 Port 3	5G FR1 Port 4	WiFi 6E Port 1	WiFi 6E Port 2	WiFi 6E Port 3	WiFi 6E Port 4	GNSS Port 1
TWC9-3M	SMA-M	SMA-M	SMA-M	SMA-M	RPSMA-M	RPSMA-M	RPSMA-M	RPSMA-M	SMA-M
TWC9-5M	SMA-M	SMA-M	SMA-M	SMA-M	RPSMA-M	RPSMA-M	RPSMA-M	RPSMA-M	SMA-M

Family Products – TWC (Twin Castle)

Multiport TWC Products - 5G FR1/ WiFi/ GNSS

Orderable P/N	No. of Total Ports	No. of 5G FR1 Ports	No. of WiFi 6E Ports	No. of GNSS Ports	Cable Length (Total)	Color
TWC94411DM	9	4	4	1	0.3M	Black
TWC94412DM	9	4	4	1	0.3M	White
TWC94411DM3MKIT	9	4	4	1	3.3M	Black
TWC94412DM3MKIT	9	4	4	1	3.3M	White
TWC94411DM5MKIT	9	4	4	1	5.3M	Black
TWC94412DM5MKIT	9	4	4	1	5.3M	White
TWC74211DM06M	7	4	2	1	0.6M	Black
TWC44001DM	4	4	0	0	0.3M	Black
TWC44002DM	4	4	0	0	0.3M	White

Notes:

1. TWC9-3M Included in TWC94411DM3MKIT (2DM3MKIT). TWC9-5M Included in TWC94411DM5MKIT (2DM5MKIT)
2. Please contact sales for availability, lead time, and/or any special requests. Samples available upon request.

For More Information:

Americas - antennas.us@pulseelectronics.com | Europe – antennas.eu@pulseelectronics.com | Asia – antennas.as@pulseelectronics.com | Questions? +1-800-ANTENNA
Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright , 2020. Pulse Electronics, Inc. All rights reserved.