

# Raise3D Premium ABS Technical Data Sheet

Raise3D Premium ABS is a ABS based filament designed specifically for desktop FDM/FFF 3D printing. It offers superior printing quality, excellent mechanical strength and heat resistance, with moderate printing temperatures and great warping resistance.

### **Physical Properties**

Property	Testing Method	Typical Value
Density (g/cm <sup>3</sup> at 21.5 °C)	ASTM D792 (ISO 1183, GB/T 1033)	1.10 - 1.15
Glass transition temperature (°C)	DSC, 10 °C/min	<b>98.10</b> ℃
Softening temperature of filament (for 1.75 mm; °C)	Custom method	100-110
Melt index (g/10 min)	220 °C, 10 kg	9 - 14
Moisture content <sup>1</sup> (%)	Thermogravimetric	≤ 0.1%
Odor	/	Almost odorless
Solubility	1	Insoluble in water

Note:

## Mechanical Properties<sup>1</sup>

Property	Testing Method	Typical Value
Young's modulus (MPa)	ASTM D638 (ISO 527, GB/T 1040)	2174 ± 285
Tensile strength (MPa)	ASTM D638 (ISO527, GB/T 1040)	33.3 ± 0.8
Elongation at break (%)	ASTM D638 (ISO527, GB/T 1040)	2.7 ± 0.4
Bending modulus (MPa)	ASTM D790 (ISO 178, GB/T 9341)	1339 ± 238
Bending strength (MPa)	ASTM D790 (ISO 178, GB/T 9341)	59.0 ± 1.3
Impact strength (kJ/m²)	ASTM D256 (ISO 179, GB/T 1043)	12.6 ± 1.1

Note

1. All testing specimens were printed using a Raise3D N2 under the following conditions: Printing temperature = 255 °C, printing speed = 60 mm/s, number of shells = 2, and 100% infill.

<sup>1.</sup> For newly opened filaments; filaments may absorb higher levels of moisture during use.



### **Testing Geometries**




Fig 1. Tensile testing specimen




Fig 3. Impact testing specimen

### Disclaimer

The typical values presented in this data sheet are intended for reference and comparison purposes only. They should not be used for design specifications or quality control purposes. Actual values may vary significantly with printing conditions. End-use performance of printed parts depends not only on materials, but also on part design, environmental conditions, printing conditions, etc. Product specifications are subject to change without notice.

Each user is responsible for determining the safety, lawfulness, technical suitability, and disposal/recycling practices of Raise3D materials for the intended application. Raise3D makes no warranty of any kind, unless announced separately, to the fitness for any particular use or application. Raise3D shall not be made liable for any damage, injury or loss induced from the use of Raise3D materials in any particular application.