

**Part no.**                    **HLR25/1H(DC)600V**  
**360051**

<b>General specifications</b>	
Product name	Eaton Moeller series HLR solid state relay
Part no.	HLR25/1H(DC)600V
EAN	4015081998180
Product Length/Depth	28.8 millimetre
Product height	58.2 millimetre
Product width	44.8 millimetre
Product weight	0.06 kilogram
Compliances	CE Marked RoHS Compliant
Certifications	EAC UL 508 CE CCC UL-File No.: E338590 CSA-File No.: 603498
Product Tradename	HLR
Product Type	Solid-state relay
Product Sub Type	None
<b>General information</b>	
Degree of protection	IP20
Frequency rating	45 Hz - 65 Hz
Mounting position	Mount device in specified orientation and do not obstruct the heatsink
Number of phases	1
Number of pilot lights	1
Overvoltage category	III
Pollution degree	2
Rated impulse withstand voltage (Uimp)	6 kV (1.2/50 µs)
Series	HLR
Shock resistance	15/11 g/ms (according to EN 50155, EN 61373)
Type	Solid-state relay
Vibration resistance	2 g/axis (2-100 Hz, IEC 60068-2-6, EN 50155, EN 61373)
Voltage type	DC
<b>Features &amp; Functions</b>	
Functions	Switching at zero-crossing
Electrical connection type for auxiliary- and control-current circuit	Screw connection
Electrical connection type of main circuit	Screw connection
<b>Climatic environmental conditions</b>	
Altitude	9
Ambient storage temperature - min	-40 °C
Ambient storage temperature - max	100 °C
Climatic proofing	95% relative humidity non-condensing at 40°C
Operating temperature - min	-40 °C
Operating temperature - max	80 °C
<b>Electro magnetic compatibility</b>	
Air discharge	8 kV (according to IEC/EN 61000-4-2)
Burst Impulse	Main: 2 kV, 5 kHz PC 1 (according to IEC/EN 61000-4-4) Control: 1 kV, 5 kHz PC 1 (according to IEC/EN 61000-4-4)
Contact discharge	4 kV (according to IEC/EN 61000-4-2)
Electromagnetic fields	10 V/m, 80 - 1000 MHz and 1.4 - 2.0 GHz, PC 1 3 V/m, 2.0 - 2.7 GHz, PC 1

Immunity to line-conducted interference		10 V/m, 0.15 - 80 MHz, PC 1 (according to IEC/EN 61000-4-6)
Radio interference class		Class A
<b>Terminal capacities</b>		
Terminal capacity (flexible with ferrule)		Main: 1 x 1-4 mm <sup>2</sup> , 2 x 1-4 mm <sup>2</sup> Control: 1 x 0.5-2.5 mm <sup>2</sup> , 2 x 0.5-2.5 mm <sup>2</sup>
Terminal capacity (solid)		Main: 1 x 2.5-6 mm <sup>2</sup> , 2 x 2.5-6 mm <sup>2</sup> Control: 1 x 0.5-2.5 mm <sup>2</sup> , 2 x 0.5-2.5 mm <sup>2</sup>
Terminal capacity (solid/stranded AWG)		Main: 1 x 14-10, 2 x 14-10 Control: 1 x 18-12, 2 x 18-12
Terminal capacity (stranded)		Main: 1 x 2.5-6 mm <sup>2</sup> , 2 x 2.5-6 mm <sup>2</sup> Control: 1 x 0.5-2.5 mm <sup>2</sup> , 2 x 0.5-2.5 mm <sup>2</sup>
Tightening torque		Main: 2.4 Nm (21.2 lb-in) Control: 0.5 Nm (4.4 lb-in)
Screwdriver size		Main: Pozidriv 2 Control: Pozidriv 1
<b>Electrical rating</b>		
Operating voltage - max.		660 V
Operating voltage - min.		42 V
Rated operational current (Ie) at AC-1		0 A
Rated operational current (Ie) at AC-3		0 A
Rated operational current (Ie) at AC-51		25 A
Rated operational current (Ie) at AC-53A		5 A
Rated operational current (Ie) at AC-53B		0 A
Rated operational voltage (Ue) at AC - min		42 V
Rated operational voltage (Ue) at AC - max		660 V
<b>Short-circuit rating</b>		
Rated conditional short-circuit current, type 1, 600 Y/347 V		kA
Rated conditional short-circuit current (Iq), type 2, 230 V		kA
Rated conditional short-circuit current (Iq), type 2, 380 V, 400 V, 415 V		kA
<b>Control circuit</b>		
Delay time		1/2 period
Drop-out time		< 1/2 period
Drop-out voltage		1.2 V DC
Input current		< 12 mA
Pick-up voltage		3.5 V DC
Rated control supply voltage (Us) at AC, 50 Hz - min		0 V
Rated control supply voltage (Us) at AC, 50 Hz - max		0 V
Rated control supply voltage (Us) at AC, 60 Hz - min		0 V
Rated control supply voltage (Us) at AC, 60 Hz - max		0 V
Rated control supply voltage (Us) at DC - min		4 V
Rated control supply voltage (Us) at DC - max		32 V
<b>Design verification</b>		
Equipment heat dissipation, current-dependent Pvid		28 W
Heat dissipation per pole, current-dependent Pvid		28 W
Rated operational current for specified heat dissipation (In)		25 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Please enquire
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Technical data ETIM 8.0

Relays (EG000019) / Solid state relay (EC002055)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Contactor (LV) / Solid state relay (ecl@ss10.0.1-27-37-10-14 [ACN970011])		
Rated control supply voltage Us at AC 50HZ	V	0 - 0
Rated control supply voltage Us at AC 60HZ	V	0 - 0
Rated control supply voltage Us at DC	V	4 - 32
Voltage type for actuating		DC
Operating voltage	V	42 - 660
Rated operation current Ie at AC-1	A	0
Rated operation current Ie at AC-3	A	0
Rated operation current Ie at AC-51	A	25
Rated operation current Ie at AC-53a	A	5
Rated operation current Ie at AC-53b	A	0
Number of phases		1
Modular version		No
Switching at zero-crossing		Yes