




Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**

Contact Mating Area Plating Material: **Precious Metal**

Wire Size: **.75 – 1.5 mm²**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Power Contact Type	Contact
Connector & Contact Terminates To	Wire & Cable

Contact Features

Contact Size	Size 16
Contact Mating Area Plating Material	Precious Metal
Contact Current Rating (Max)	13 A
Contact Type	Pin
Contact Retention Within Housing	With
Mating Pin Diameter	1.57 mm[.062 in]
Contact Base Material	Brass
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Mating Area Plating Material Finish	Bright
Wire Contact Termination Area Plating Thickness	1.02 µm[40 µin]
Wire Contact Termination Area Plating Material	Tin



Wire Contact Termination Area Plating Material Finish	Bright
Contact Orientation	Straight
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	.75 – 1.5 mm²
Compatible Insulation Diameter Range	2 – 2.5 mm[.078 – .098 in]

Usage Conditions

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Contact Color Code	Blue
--------------------	------

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free




Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 58495-2 PROCRIMPER DIE ASSY MULTIMATE	 TE Part # 200893-2 INSERTION TOOL CONT	 TE Part # 58495-1 PRO CRIMPER ASSY MULTIMATE	 TE Part # 539972-1 EXTRACTION TOOL
 TE Part # 305183 EXTRACT TOOL TYPE 2 20-16	 TE Part # 2151023-1 OCEAN_2.0_Applicator-S-080F1200	 TE Part # 91505-1 CCII TYPE III+ 24-16 ASSY	 TE Part # 2-2151023-1 OCEAN_2.0_Applicator-S-080F1200
 TE Part # 2-2151023-2 OCEAN_2.0_Applicator-S-080F1200	 TE Part # 2151023-2 OCEAN_2.0_Applicator-S-080F1200	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 5-2151023-1 OCEAN_2.0_Applicator-S-080F1200



TE Part # 5-2151023-2
OCEAN_2.0_Applicator-S-080F1200

KIT
TE Part # 7-2151023-7
OCEAN_2.0_SPARE_PART_KIT-080F1200

TE Part # 169422-1
MINI CERTI-LOK III+

Also in the Series | AMP Type III+

Insertion & Extraction Tools(4)

Power Contacts(409)

Customers Also Bought

TE Part #W4PC
Wedgelocks: DEUTSCH DT

TE Part #182921-1
CPC SQ FL. RCPT REV SEX

TE Part #163087-8
062 SOC.ASS. TYP3+

TE Part #213845-3
POWERBAND CONT ASSY,SILVER PLT

TE Part #HDP26-18-14PN
PLG, 14P, BLK, N, 16, P

TE Part #929986-1
1,5MM SOCK CONTACT

TE Part #213900-1
CPC SEAL ASSY KIT,SRS 6,17-10

TE Part #1-154719-1
PL 250 REC HSG 1P NYLON NAT

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_1-163081-1_BA.2d_dxf.zip
- English



Customer View Model

[ENG_CVM_CVM_1-163081-1_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-163081-1_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English