

### LMR®-400-FR FLEXIBLE LOW LOSS CABLE ASSEMBLIES

Times LMR cable assemblies are high performance broadband, flexible, low-loss RF coaxial cables that can be used virtually anywhere, either indoors or outdoors. As a completely Times manufactured solution, performance and reliability are assured.



- Low smoke fire retardant
- Excellent RF Shielding, better than 90 dB
- UV and weather resistant
- Flexible and easy to use

#### **Mechanical Properties**


	Units	
Diameter	in (mm)	0.405 (10.287)
Weight	lb/ft (kg/m)	0.068 (0.10)
Minimum Bend Radius	in(mm)	1.00 (25.4)
<b>Operating Temperature</b>	°F (°C)	-40° to 185°(-40 to 85)
Tensile Strength	lb (kg)	160 (72.6)
<b>Bending Moment</b>	ft lb (N-m)	0.5 (0.68)
Flat Plate Crush	lb/in (kg/mm)	40 (0.71)
Storage Temp	°F (°C)	-94 to 185 (-70 to 85)

#### **KEY APPLICATIONS**

- Antenna feeder runs
- Inter/intra cabinet jumpers
- Internal component equipment wiring
- GPS system wiring

#### **Electrical Properties**

	Units	
Impedance	Ω	50 +/- 2
Maximum Frequency	GHz	8.0
Capacitance	pF/ft (pF/m)	23.9 (78.4)
Velocity of Propagation	1	84%
Delay	ns/ft (ns/m)	1.20 (3.94)
Shielding		>90dB minimum
Voltage Withstand	Volts DC	2500
Jacket Spark	Volts RMS	8000
Attenuation	dB/ft	dB/m
900 MHz	0.04	(0.13)
2.5 GHz	0.07	(0.23)
5.8 GHz	0.11	(0.36)



Inner Conductor

2 Dielectric

3 Outer Conductor

4 Overall Braid

5 Jacket

Solid CCA

Foam PE

Aluminum Tape

Tinned Copper

FR-PE

## LMR®-400-FR FLEXIBLE LOW LOSS CABLE ASSEMBLIES

### Ordering Guide

### LFR400- NMNM-3.0 F

Interface NM N Male TM TNC Male BM BNC Male Length

Units of Measure F Feet M Meters







# WORLD HEADQUARTERS 358 Hall Avenue, Wallingford, CT 06492 1-800-867-2629

