
Refrigerator Switches



Long recognised as a leader in refrigerator door switches, Bulgin's wide range of types and configurations will suit almost any need. With both double contact and single contact options, our switches are not only ideal for traditional refrigerator and freezer applications but can and have been used in a variety of door applications as well.

- O Door switches
- Switch rating from 0.2A, 250V ac up to 5A, 250Vac
- Splash resistant variants
- Choice of actuators
- Momentary on and momentary off switching
- Hazardous Location EN IEC 60079-0 & 60079-15
- C Ex II 3 G & Ex nC IIA Gc
- Cert no. UL 22 ATEX 2897U
- Rated up to 2.5A 250VAC



0055 Door Switches







C0055RB ---





Key Features

- Ratings up to 0.2A, 250V ac
- O High temperature rating up to 125°C
- Long overtravel
- Choice of terminal orientation

Approvals and specifications

© 0055 & 0056 0.2(0.2)A 250Vac 25T125 5E4 (50,000 operations)

μ contact gap

Dimensions and Properties

C0055RB

C0056RB





Terminal	Function	Actuator	Body	Options
9.1 6.3x0.8	ON - OFF (momentary OFF) 90° terminals	R	Panel cut - out	Finish Gloss finish only Colour White or black Call sales for custom colours.
Н	0056		Panel thickness 0055 1.0 - 1.6 0056 1.0 - 2.6	
4.8x0.8	ON - OFF (momentary OFF) straight terminals		Flange 024.1 6.6	

3005 Refrigerator Door Switches Splash Resistant





Key Features

- O Door switches
- Momentary on and momentary off switching
- O Splash resistant
- Choice of terminal orientation
- Choice of actuators


Approvals and specifications

© 3005 25W 25T85 5E4 (50,000 Operations) 250Vac 3006 65W 25T85 5E4 (50,000 Operations) 250Vac


R1 © UL 0.3A 250Vac (Black Versions Only) R1 UL 0.2A 125Vac (Black Versions Only)

μ contact gap

Dimensions and Properties



R, L & B terminals



B Actuator C Actuator R, L & B terminals

Terminal	Function	Actuator	Body	Options
C 9.1 6.3x0.8	3005 ON - OFF (momentary OFF) 1mm max travel to OFF position	B 26.0	R L B Terminal direction (viewed from hinge end)	Finish Gloss finish only Colour White or black Call sales for custom colours. A full range is available for large orders.
H 9.1 4.8x0.8	3006 ON - OFF (momentary ON) 3mm min travel to ON position	13.0	Panel cut - out Bezel Bezel Profile 254 255 12.1712.2	

3100 ATEX Refrigerator Door Switches





Key Features

- ATEX Rated up to 2.5A, 250Vac
- Splash resistant
- Changeover, momentary ON and momentary OFF
- Choice of actuators & colours

Approvals and specifications

ATEX Approved for hazardous locations 2.5A 250Vac

Compiles with: EN IEC 60079-0 & 60079-15 Ex II 3 G & Ex nC IIA Gc

Type Examination Certificate no. UL 22 ATEX 2897U

91 UL CSA 5A 250Vac (Standard location only) UL 85°C, file E45221, CSA file LR10990

terminals 1,2 terminals 1,2 terminals 1,2 terminals 1,2 aterminals 1,2,3 ap.

Dimensions and Properties

3101 uses terminals 1,2 3102 uses terminals 1,2 3111 uses terminals 1,2,3

 μ contact gap.

For details of actuator travel and switching angles call sales.

Finish: Gloss finish only

Terminal	Function	Actuator	Body	Colour	Options	Approval
E		Α	Α	W	Α	EX
7.9	3101	17.6 max	3.68 27.31 3.68 2.93 2.93 1.65 1.14 2.93	White	Standard	ATEX Approved
4.8x0.5 QC	0N - OFF	В	Optional 22 73 cut-out 22 99 for	В		
	(momentary CLOSED)	15.6 max	orientation ↓	Black		
	3102	C		P		
	ON - OFF (momentary OFF)	23.0 max		Polar White		
	3111 2 1 3 ON - ON (momentary 1 side)	17.1 max		Call sales for custom colours. A full range is available for large orders.	Call sales for plated contacts and sealed terminal options.	

Part Code System

E	31XX	/ x /	Α	/ x	/ x	/ x
Terminal	Function	Actuator	Body	Colour	Options	Approval
Е	3101 3102 3111	Type A B C D	A	W B P	А	EX

3140 ATEX Refrigerator Door Switches





Function

Terminal

Key Features

- ATEX Rated up to 2.5A, 250Vac
- Splash resistant
- Momentary action
- Choice of actuators & colours
- 2 circuit switch

Approvals and specifications

ATEX Approved for hazardous locations 2.5A 250Vac

Compiles with: EN IEC 60079-0 & 60079-15 Ex II 3 G & Ex nC IIA Gc Type Examination Certificate no. UL 22 ATEX 2897U

SA 250Vac (Standard location only) 25T85 5E4 (50,000 Operations)

**UL CSA 5A 250Vac (Standard location only) UL 85°C, file E45221, CSA file LR10990

Options



Approval

3141 uses terminals 1,2,3,4

Colour

3145 uses terminals 3,4 3146 uses terminals 1,2

3141, μ contact gap. 3145 and 3146, 3mm contact gap.

Body

Dimensions and Properties

Finish: Gloss finish only

Actuator

Н	1 2	A	Α	w	A	EX
0.8	<u>3</u> <u>4</u>	17.6 max	3.68 2.93 2.93 3.68 2.93	White	Standard	ATEX Approved
↓ ♦ 4.8×0.8	3141	_	1.65 V Optional 22.73 cut-out 22.99			
	↓	B saves	Optional 22.73 cut-out for orientation	Black		
	ON - ON (momentary)	15.6 max		Diack		
K	3145	C		P		
3141 Only	√ 3 4	23.0 max		Polar White		
2.6	ON - OFF (momentary OFF)	THE WAY				
2.8x0.8	3146	D				
	↑ • • 1 2	17.1 max suss				
Standard format is H terminals	ON - OFF			Call sales for custom colours.	Call sales for plated contacts and sealed	
in positions 1 & 2 and K terminals in positions 3 & 4 (HK3141)	(momentary ON)			A full range is available for large orders.	terminal options.	
art Code System	1					
X	314X	/ x	A	/ x	/ x	/ x
Terminal	Function	Actuator	Body	Colour	Options	Approval
HK (3141 only)	3141	Туре	А	W	А	EX
Н	3145 3146	A B		B P		
		C				