AC Axial Fan

multicomp PRO

RoHS **Compliant**



Characteristics

Motor Design Insulation Resistance **Dielectric Strength** Motor Protection Noise Level

Tolerance Air Performance

Specification

Rated Voltage : 110V AC to 230V AC 50Hz/60Hz **Operating Voltage Range** : 90V AC to 265V AC 50Hz/60Hz Safety Certification Voltage Range : 100V AC to 240V AC 50Hz/60Hz Starting Voltage : 85V AC (25°C Power ON/OFF) Rated Speed : 2000 RPM ±15% Air Delivery : 64.3 CFM / Min. 47.3 CFM : 0.17 Inch-H2O / min. 0.11 Inch-H2O Static Pressure Rated Current : 37 mA 22mA Rated Power : 1.8 Watts Noise Level : 31.4 dB(A) / Max. 35.9 dB(A) : Counter-clockwise viewed from front of fan blade **Direction of Rotation** : -25°C to +70°C **Operating Temperature** Storage Temperature : -40°C to +70°C **Bearing System** : Precision ball bearing system Weight : 317g Safety : UL/CUR/TUV/CE Approvals Protection : Automatic Restart Capability IP Class : IP68


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

- : Single phase, 4-poles Brushless DC motor.
- : 10 MΩ minimum at 500V DC.
- : 1800V AC for one second.
- : Impedance Protected.
- : Measured in a semi-anechoic chamber with background noise level below 15 dB(A). The fan is running in free air with the microphone at a distance of one meter from the fan intake.
- : ±20% on rated power and current.
- : Measured by a double chamber. The values are recorded when the fan speed has stabilized at rated voltage.

multicomp PRO

multicomp PRO

Performance Curves



Material

Frame	: Thermoplastic PBT of UL 94V-0
Impeller	: Thermoplastic PBT of UL 94V-0
Lead Wire	: UL 3266 #24AWG, Gray


Dimensions

Screw Type (Pan Head)	Torque	Screw Spec.	
		Size	Standard
Machine Screw	3~4 kgf-cm	M4	JIS B1111-1974
Self-Tapping Screw	5~8 kgf-cm	Ø5	JIS B1122 Type 2

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



AC Axial Fan



Best Mounting Direction: Any orientation.

Dimensions : Millimetres

Part Number Table

Description		Part Number	
AC Axial Fan, 120mm	× 38mm, 100V-230V AC, IP68	MP-CF4113LBL-0000-AE9	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

