
## multicomp PRO



## Specifications

Rating	: 20A, 125/250V
Contact Resistance	: 20mΩ Initial (Max.)
Insulation Resistance	: 500V DC - 100MΩ (Min.)
Dielectric Strength	: 1500V AC for 1 Minute (Terminal to Encloser) 500V AC for 1 Minute (Terminal to Terminal) Protection Level : IP68
Electrical Life	: 10,000 cycles
Mechanical Life	: 50,000 cycles

## Diagram



## Part Number Table

	Description	Part Number
	Toggle Switch, Single Pole, 3P, (On)-Off-(On), Brass Lever type	MP-TB1-AB11
Dimensions : Millimetres	Toggle Switch, Single Pole, 3P, (On)-Off-(On), Plastic Lever type	MP-TB1-AP11

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

