
# **Electro-Holding Magnet: 30mm**



## **Energise To Hold ElectroMagnet**

#### **Technical Data**

Mountings Threaded holes in rear face Finish Bright nickel-plated with machined face Weight 108g Typical Holding 28.0kg Force **ED Rating** 100% **IP Rating** 54 Standard 12VDC M52173/12VDC Operating 24VDC M52173/24VDC Voltage Current 12V - 280mA 24V - 140mA **Typical** 3.3W Power Connection 12VDC & 24VDC Free Leads (500mm Long) Type




## **Recommended Armature Plate**

Finish Bright nickel-plated


Diameter 30mm
Height 4mm
Screw M4

Part Number M52171/30ARM

Weight 30g



Air Gap (mm)	Pull Force* (kg)
0.00	28.00
0.09	14.90
0.18	8.00
0.27	4.30
0.36	2.60
0.59	1.20
1.00	0.50
1.50	0.20
2.00	0.10



### \* +/- 10% at room temperature

To achieve the optimum pull force 100% contact area must be achieved using the recommended armature plate. The force will be affected if other material specifications, thicknesses and surfaces are used, or if the armature fails to make positive contact over the full diameter of the face of the magnet.

Where misalignment is likely to be an issue we recommend that an oversized armature plate is used to ensure 100% full contact, this however will reduce the stated pull force by approximately 10%.