

Search



FIBER OPTICS

---

RADIO FREQUENCY

---

LOW AND HIGH VOLTAGE





FIBER OPTICS

RADIO FREQUENCY

LOW AND HIGH VOLTAGE



 Enlarge image



Distributor Availability






## FIBER OPTICS

## RADIO FREQUENCY

## LOW AND HIGH VOLTAGE

Item no.: 84099988

Datasheet:  

Description: Straight PCB jack

Interface: MMPX

Highlights: Precision connector

Outline drawing:  

3D model: 

Picture: 

Frequency Range 1: 0 GHz to 26.5 GHz

### Electrical data

Impedance (Ohm): 50



Interface freq. max. (GHz): 67



## FIBER OPTICS

## RADIO FREQUENCY

## LOW AND HIGH VOLTAGE

Frequency Range 3:	50 GHz to 67 GHz
--------------------	------------------

Return Loss[-dB]3:	10 DB
--------------------	-------

VSWR3:	1,92
--------	------

### Mechanical data

Number of matings:	100
--------------------	-----

Board mounting type:	pin-in-hole / SMT
----------------------	-------------------

Number of printlegs:	4
----------------------	---

Height above PCB HA:	5,47 mm
----------------------	---------

Height of stand off HS:	0,37 mm
-------------------------	---------

Weight:	0,0004 kg
---------	-----------



### Environmental and general data



## FIBER OPTICS

## RADIO FREQUENCY

## LOW AND HIGH VOLTAGE

Available packagings:

Bulk 10 pcs

Tape and Reel

### Fiber optics

Cables

Connectors

Adapters

Accessories



Assembly & Cable  
Systems

### Radio frequency

Antennas & accessories

Cables and cable  
assemblies

Connectors

Adapters

Passive components

### Low and high voltage

Databus cables

Signal & power cables



FIBER OPTICS

---

RADIO FREQUENCY

---

LOW AND HIGH VOLTAGE

---

DISCLAIMER

[Data Protection Statement](#)

[Our Terms & Conditions](#)

© HUBER+SUHNER AG

