

LCANGPS1007

Features

- I ow Profile
- · Embedded Low Noise Amplifier
- MIL-STD-810G
- · Linearly Polarized
- · 10 dBic Gain

Applications

- · Military, Law Enforcement, or Private Security
- · Hand-held/Portable Devices
- · Asset and Fleet Tracking
- · Scientific Instrumentation

- SMA Male
- · IP67 Rated
- Operating Frequency Range 1559 MHz to 1610 MHz
- · Operating Voltage 3.3 Vdc
- · Oil, Gas, and Mining Industries
- · M2M Applications
- · GPS L1, GALLILEO E1, AND GLONASS

Description

L-Com's Active GNSS Antenna LCANGPS1007 is Linearly polarized and conforms to MIL-STD-810G. The LCANGPS1007 is an active GPS L1 band antenna with 10 dBic Gain. These Mil Spec active GNSS antenna units are ideally suited for use in rugged terrain where low profile, low drag, bullet style antennas are needed.

Our GNSS antenna specialists are ready and available to answer any questions you may have on the LCANGPS1007. This high quality multi-standard SMA male antenna meets GPS L1, GALLILEO E1 and GLONASS G1 requirements by operating in the 1559MHz to 1610MHz frequency range.

The LCANGPS1007 GNSS antenna series from L-Com are designed for portable, hand-held, or mobile devices which receive GNSS signals from satellite constellations to triangulate geolocations for navigation, tracking, surveying, mobile network timing, or munitions targeting. Order your Active GNSS LCANGPS1007 Antenna from L-Com today. There is no MOQ (minimum order quantity) and the product ships same day from our warehouse.

Configuration

Design
Band Type
Polarization
Connector Type

GPS/GNSS Active Single Linear, Vertical SMA Male

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	1,597		1,607	MHz
Output VSWR			2.5:1	
Impedance		50		Ohms
Gain	10			dBic
Noise Figure		0.55		dB
Operating DC Voltage	2		3.5	Volts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: GPS Active Antenna, 1597 MHz to 1607 MHz, 10dBic, Linear Polarization SMA mount LCANGPS1007





LCANGPS1007

Current	3.8	mA

Mechanical Specifications

Radome Material Polyetherimide

Size

Length 1.75 in [44.45 mm] Weight 0.02 lbs [9.07 g]

Environmental Specifications

Temperature

Operating Range -40 to +71 deg C Storage Range -40 to +85 deg C

Environment MIL-STD-810G

 Humidity
 MIL-STD-810G, Meth 507.5, Proc II

 Shock
 MIL-STD-810G, Meth. 516.6, Proc. I

 Vibration
 MIL-STD-810G, Meth. 514.6, Proc. I

 Corrosion
 MIL-STD-810G, Meth 509.5, 4 x 24 h

Altitude MIL-STD-810G

Environmental Specification Notes:

Operating Temp MIL-STD-810G, Meth. 501.5 & 502.5, Proc. II. Storage Temp MIL-STD-810G, Meth. 501.5 & 502.5, Proc. I. Transit Drops MIL-STD-810G, Meth. 516.6, Proc. IV, 26 drops 1.2m.

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



LCANGPS1007

ELECTRICAL PERFORMANCES




Figure 1: VSWR



LCANGPS1007




Figure 2: Radiation pattern on ground plane at 1575 MHz (RHCP)

GPS Active Antenna, 1597 MHz to 1607 MHz, 10dBic, Linear Polarization SMA mount from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

