Fuseholder Open Design, 6.3 x 32 mm, THT



2.5W / 10A @Tu 23°C · 500 VAC · 16 A (UL)

See below:

Approvals and Compliances

Description - Through hole mounting		Weblinks pdf data sheet, html datasheet, General Product Information, Distributor-Stock-Check, Detailed request for product, Microsite	
Technical Data			
Fuse-Link	6.3 x 32mm	Soldering Methods	Wave
Mounting	PCB		Soldering Profile
Attachment	Screw/rivet/THT	Solderability	245°C / 3 sec acc. to IEC 60068-2-20,
Terminal	Solder THT		Test Ta, method 1
Rated Voltage	500 VAC (UL)	Resistance to Soldering Heat	260°C / 10 sec acc. to IEC 60068-2-20,
Rated current	16A (UL)		Test Tb, method 1A
Rated Power Acceptance IEC	2.5W / 10A @Tu 23°C	Solderability	245 °C / 3 sec acc. to IEC 60068-2-20,
Admissible Ambient Air Temp.	-40 °C to 85 °C		Test Ta, method 1
Climatic Category	40/085/21 acc. to IEC 60068-1	Contact Resistance	≤ 10 mΩ at 100 mA acc. to IEC
Material: Terminals	Copper alloy, tin-plated	<u></u>	60127-6
Unit Weight	7.23 g	Dielectric Strength	> 3kV between life parts
Storage Conditions	0°C to 60°C, max. 70% r.h.	Impulse Withstand Voltage	(50 Hz: 1 min)
Product Marking	Rated Voltage, Rated current, Certification marks	Impulse Withstand Voltage Insulation Resistance	> 4kV between life parts > 10 MΩ between life parts (500 VDC: 1 min)

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: OG (Holder) 6.3x32

Approval Logo	Certificates	Certification Body	Description
c FU °us	UL Approvals	UL	UR File Number: E39328

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
(UL)	Designed according to	UL 4248-1	Industrial Control Equipment
GFA Group	Designed according to	CSA C22.2 no. 4248.1	Industrial Control Equipment

Application standards

Application standards where the product can be used


Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements


Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
UK CA	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
ROHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimension [mm]






Drilling diagram

Derating Curves

acc. to IEC



All Variants

Holder Order Number

• 0031.8002

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging Unit Bulk (100 pcs.)