### 1-stage filter with 3-phase CEE connector





### See below:

## **Approvals and Compliances**

# **Description**

- 3 Phase CEE Connector with Filter
- Easy and time saving handling

### **Unique Selling Proposition**

- First CEE power entry module with EMC filter
- Easy prewired solution
- Universal flange for front or rear mounting
- Optimal filter position direct on the power entry

## **Applications**

- Protection against interference voltage from the mains
- Possible interferences generated in the equipment are strongly attenuated
- Suitable for equipment with detachable power cord

#### Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Detailed request for product, Microsite

| Technical Data          |                                    |
|-------------------------|------------------------------------|
| Rated Current           | 16 - 32 A @ Ta 40°C                |
| Rated voltage           | 277/480 VAC, 50/60 Hz              |
| Approval for            | 16 - 32 A / 277/480 VAC            |
| Overload Current        | 1.5 x lr for 1 minute, per hour    |
| Leakage Current         | industrial < 10 mA (440 V / 50 Hz) |
| Dielectric Strength     | 277/480 VAC:                       |
|                         | 2.25 kVDC between L-L              |
|                         | 1.7 kVDC between L-N               |
|                         | 3 kVDC between L-PE                |
|                         | Test voltage (2 sec)               |
| Number of Filter Stages | 1-stage                            |
| Weight                  | 1.4kg                              |
| Material: Housing       | Metal                              |
| Sealing Compound        | UL 94V-0                           |

| Mounting              | Screw-on mounting on chassis                                      |
|-----------------------|---|
| Terminal              | Screw clamps  |
| Operating Temperature | -40 °C to 85 °C   |
| Climatic Category     | 40/085/21 acc. to IEC 60068-1                                     |
| Degree of Protection  | IP20 acc. to IEC 60529  |
| Protection Class      | Suitable for appliances with protection class I acc. to IEC 61140 |
| MTBF                  | > 200'000h acc. to MIL-HB-217 F                                   |
|                       |   |

#### **Approvals and Compliances**

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

## **Approvals**

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: FMAD CEE

| Approval Logo Certificates   |                 | Certification Body | Description                    |  |  |
|------------------------------|-----------------|--------------------|--------------------------------|--|--|
| <b>I</b> 14                  | SEMKO Approvals | SEMKO              | Certificate Number: SE/09137-4 |  |  |
| c <b>FU</b> ° <sub>IIS</sub> | UL Approvals    | UL                 | UR File Number: E72928         |  |  |

#### **Application standards**

Application standards where the product can be used

| Organization | Design                         | Standard       | Description   |
|--------------|--------------------------------|----------------|---|
| <u>IEC</u>   | Designed for applications acc. | IEC/UL 62368-1 | Audio/video, information and communication technology equipment - Part 1: Safety requirements |


# Compliances


The product complies with following Guide Lines


| Identification | Details                        | Initiator   | Description   |
|----------------|--------------------------------|-------------|---|
| CE             | CE declaration of conformity   | SCHURTER AG | The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008. |
| UK<br>CA       | UKCA declaration of conformity | SCHURTER AG | The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.  |
| RoHS           | RoHS                           | SCHURTER AG | Directive RoHS 2011/65/EU, Amendment (EU) 2015/863  |
| <b>©</b>       | China RoHS                     | SCHURTER AG | The law SJ $/T$ 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.   |
| REACH          | REACH                          | SCHURTER AG | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.                               |


# Dimension [mm]

Case QT1










- 1) Line 2) Load
- 3) Blue
- 4) Yellow-Green


# Case QT3



PΕ

- 1) Line
- 2) Load
- 3) Blue
- 4) Yellow-Green

# **Diagrams**



30 / 32 A


1) Line

2) Load

16 A

 $\textbf{Attenuation Loss} \dots 0.1/100\Omega \ \ \text{differential mode} \quad \dots \dots 100/0.1\Omega \ \text{differential mode} \quad \text{----} 50\Omega \ \text{differential mode} \\ \underline{\qquad} 50\Omega \ \text{common mode}$ 

Industrial version



# All Variants

| Rated Current @ Ta<br>50°C (40°C) [A] | Rated Voltage [VAC] | Powerloss @ 25°C,<br>50Hz [W] | Leakage<br>Current @<br>400VAC, 50Hz | Weight [kg] | Screw clamps<br>[mm2] 2) | Housing | Packaging<br>unit | Order Number      |  |
|---------------------------------------|---------------------|-------------------------------|--------------------------------------|-------------|--------------------------|---------|-------------------|-------------------|--|
| 16                                    | 240/415             | 5.6                           | 10                                   | 1.3 kg      | 4                        | QT1     | 1                 | FMAD-T4QT-1660.EU |  |
| 30                                    | 277/480             | 4.3                           | 10                                   | 1.4 kg      | 10                       | QT3     | 1                 | FMAD-T4QT-3060.US |  |
| 32                                    | 240/415             | 4.9                           | 10                                   | 1.4 kg      | 10                       | QT3     | 1                 | FMAD-T4QT-3260.EU |  |

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

**EMC Products** 

<sup>1)</sup> Leakage current according IEC 60939-1

<sup>2)</sup> Maximum conductor cross section (wire gauge) to be used; a comparative table for AWG and mm² values can be found in the general product information https://www.schurter.com/en/FAQ#10