

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture MOISTURE REMOVER FG

Registration number -

Synonyms None.

Product code UDS001040AE

Issue date 17-November-2022

Version number 1.0

Revision date 17-November-2022

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Lubricants

Uses advised against None known.

1.3. Details of the supplier of the safety data sheet

Company name CRC Industries UK Ltd.

Address Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom

Telephone +44 1278 727200

Fax +44 1278 425644

E-mail hse.uk@crcind.com

Website www.crcind.com

Company name CRC Industries Europe bv

Address Touwslagerstraat 1
9240 Zele
Belgium

Telephone +32(0)52/45.60.11

Fax +32(0)52/45.00.34

E-mail hse@crcind.com

Website www.crcind.com

1.4. Emergency telephone number Tel.:(+44)(0)1278 72 7200 (office hours: 9-17h GMT)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

Physical hazards

Aerosols Category 1

H222 - Extremely flammable aerosol.
H229 - Pressurized container: May burst if heated.

Environmental hazards

Hazardous to the aquatic environment, long-term aquatic hazard Category 3

H412 - Harmful to aquatic life with long lasting effects.

2.2. Label elements

Hazard pictograms



Signal word

Danger

Hazard statements

H222

Extremely flammable aerosol.

H229

Pressurized container: May burst if heated.

H412

Harmful to aquatic life with long lasting effects.

Precautionary statements

Prevention

P102

Keep out of reach of children.

P210

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P211

Do not spray on an open flame or other ignition source.

P251

Do not pierce or burn, even after use.

Response

Not assigned.

Storage

P410 + P412

Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Disposal

P501

Dispose of contents/container in accordance with local/regional/national/international regulations.

Supplemental label information

EUH066 - Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII. The product does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General information

Chemical name	%	CAS-No. / EC No.	REACH Registration No.	Index No.	Notes
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	30 - 60	- 926-141-6	01-2119456620-43	-	
Classification: Asp. Tox. 1;H304					
1H-Imidazole-1-ethanol, 2-(8-heptadecenyl)-4,5-dihydro-	0 - 1	95-38-5 202-414-9	01-2119777867-13	-	
Classification: Acute Tox. 4;H302, Skin Corr. 1C;H314, Eye Dam. 1;H318, STOT RE 2;H373, Aquatic Acute 1;H400(M=10), Aquatic Chronic 1;H410(M=10)					
Glycine, N-methyl-N-(1-oxo-9-octadecenyl)-, (Z)-	0 - 1	110-25-8 203-749-3	01-2119488991-20	-	
Classification: Acute Tox. 4;H332, Skin Irrit. 2;H315, Eye Dam. 1;H318, Aquatic Acute 1;H400					

List of abbreviations and symbols that may be used above

#: This substance has been assigned Union workplace exposure limit(s).

ATE: Acute toxicity estimate.

M: M-factor

PBT: persistent, bioaccumulative and toxic substance.

vPvB: very persistent and very bioaccumulative substance.

All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

Composition comments

The full text for all H-statements is displayed in section 16.

SECTION 4: First aid measures

General information

Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

4.1. Description of first aid measures

Inhalation

Move to fresh air. Call a physician if symptoms develop or persist.

Skin contact

Wash off with soap and water. Get medical attention if irritation develops and persists.

Eye contact

Rinse with water. Get medical attention if irritation develops and persists.

Ingestion

In the unlikely event of swallowing contact a physician or poison control centre.

4.2. Most important symptoms and effects, both acute and delayed Exposure may cause temporary irritation, redness, or discomfort.

4.3. Indication of any immediate medical attention and special treatment needed Treat symptomatically.

SECTION 5: Firefighting measures

General fire hazards Extremely flammable aerosol.

5.1. Extinguishing media

Suitable extinguishing media Water fog. Foam. Dry chemical powder. Carbon dioxide (CO₂).

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture Contents under pressure. Pressurised container may explode when exposed to heat or flame. During fire, gases hazardous to health may be formed.

5.3. Advice for firefighters

Special protective equipment for firefighters Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

Special fire fighting procedures Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapour pressure build up. For massive fire in cargo area, use unmanned hose holder or monitor nozzles, if possible. If not, withdraw and let fire burn out.

Specific methods Use standard firefighting procedures and consider the hazards of other involved materials. Use water spray to cool unopened containers. In the event of fire and/or explosion do not breathe fumes.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing.

For emergency responders Keep unnecessary personnel away. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained.

6.2. Environmental precautions Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up Stop leak if you can do so without risk. Move the cylinder to a safe and open area if the leak is irreparable. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil etc) away from spilled material. Prevent product from entering drains.

Large Spills: Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Scoop up used absorbent into drums or other appropriate container. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

6.4. Reference to other sections Not available.

SECTION 7: Handling and storage

7.1. Precautions for safe handling Pressurised container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. All equipment used when handling the product must be grounded. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices.

7.2. Conditions for safe storage, including any incompatibilities Pressurised container. Protect from sunlight and do not expose to temperatures exceeding 50°C. Keep away from heat, sparks and open flame. This material can accumulate static charge which may cause spark and become an ignition source. Prevent electrostatic charge build-up by using common bonding and grounding techniques. Store away from incompatible materials (see Section 10 of the SDS).

Storage class (TRGS 510): 2B (Aerosol dispensers and lighters)

7.3. Specific end use(s) Not available.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits	No exposure limits noted for ingredient(s).
Biological limit values	No biological exposure limits noted for the ingredient(s).
Recommended monitoring procedures	Not available.

Derived no effect levels (DNELs)

General population

Components	Value	Assessment factor	Notes
White mineral oil (CAS 8042-47-5)			
Long-term, Systemic, Dermal	93 mg/kg bw/day		
Long-term, Systemic, Inhalation	35 mg/m3		

Workers

Components	Value	Assessment factor	Notes
1H-Imidazole-1-ethanol, 2-(8-heptadecenyl)-4,5-dihydro- (CAS 95-38-5)			
Long-term, Systemic, Dermal	0.06 mg/kg	300	Repeated dose toxicity
Long-term, Systemic, Inhalation	0.46 mg/m3	75	Repeated dose toxicity
Short-term, Systemic, Dermal	2 mg/kg	10	Repeated dose toxicity
Short-term, Systemic, Inhalation	14 mg/m3	2.5	Repeated dose toxicity
White mineral oil (CAS 8042-47-5)			
Long-term, Systemic, Dermal	220 mg/kg bw/day		
Long-term, Systemic, Inhalation	160 mg/m3		

Predicted no effect concentrations (PNECs)

Components	Value	Assessment factor	Notes
1H-Imidazole-1-ethanol, 2-(8-heptadecenyl)-4,5-dihydro- (CAS 95-38-5)			
Freshwater	0 mg/l	1000	
Marine water	0 mg/l	10000	
Sediment (freshwater)	0.376 mg/kg		
Sediment (marine water)	0.038 mg/kg		
Soil	0.075 mg/kg		
STP	0.27 mg/l	100	
White mineral oil (CAS 8042-47-5)			
Secondary poisoning	17 g/kg	300	Oral

8.2. Exposure controls

Appropriate engineering controls	Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.
---	---

Individual protection measures, such as personal protective equipment

General information	Use personal protective equipment as required. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.
Eye/face protection	Wear safety glasses with side shields (or goggles). Use eye protection conforming to EN 166.
Skin protection	
- Hand protection	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through. Nitrile gloves are recommended. Suitable gloves can be recommended by the glove supplier.
- Other	Wear suitable protective clothing.
Respiratory protection	In case of insufficient ventilation, wear suitable respiratory equipment. Chemical respirator with organic vapour cartridge and full facepiece. (Filter type A)
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.

Hygiene measures	When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.
-------------------------	--

Environmental exposure controls	Inform appropriate managerial or supervisory personnel of all environmental releases. Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. Fume scrubbers, filters or engineering modifications to the process equipment may be necessary to reduce emissions to acceptable levels.
--	--

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state	Liquid.
Form	Aerosol.
Colour	Yellow.
Odour	Characteristic odor.
Odour threshold	Not available.
pH	Not applicable.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	180 °C (356 °F)
Flash point	> 70.0 °C (> 158.0 °F)
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Explosive limit - lower (%)	0.6 %
Explosive limit – upper (%)	6 %
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	0.83 g/cm ³ 20 °C
Solubility(ies)	
Solubility (water)	Insoluble in water
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	> 200 °C (> 392 °F)
Decomposition temperature	Not available.
Viscosity	Not available.
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.
9.2. Other information	No relevant additional information available.

SECTION 10: Stability and reactivity

10.1. Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
10.4. Conditions to avoid	Avoid high temperatures.
10.5. Incompatible materials	Strong oxidising agents.
10.6. Hazardous decomposition products	Carbon oxides.

SECTION 11: Toxicological information

General information	Occupational exposure to the substance or mixture may cause adverse effects.
Information on likely routes of exposure	
Inhalation	Based on available data, the classification criteria are not met.
Skin contact	Based on available data, the classification criteria are not met.
Eye contact	Based on available data, the classification criteria are not met.
Ingestion	May cause discomfort if swallowed. However, ingestion is not likely to be a primary route of occupational exposure.
Symptoms	Exposure may cause temporary irritation, redness, or discomfort.
11.1. Information on toxicological effects	
Acute toxicity	Based on available data, the classification criteria are not met.

Components	Species	Test Results
1H-Imidazole-1-ethanol, 2-(8-heptadecenyl)-4,5-dihydro- (CAS 95-38-5)		
Acute		
Oral		
LD50	Rat	1265 mg/kg
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics		
Acute		
Dermal		
LD50	Rabbit	> 5000 mg/kg
Inhalation		
LC50	Rat	> 5000 mg/m3, 8 h
Oral		
LD50	Rat	> 5000 mg/kg
Skin corrosion/irritation	Based on available data, the classification criteria are not met.	
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met.	
Respiratory sensitisation	Based on available data, the classification criteria are not met.	
Skin sensitisation	Based on available data, the classification criteria are not met.	
Germ cell mutagenicity	Based on available data, the classification criteria are not met.	
Carcinogenicity	Based on available data, the classification criteria are not met.	
Reproductive toxicity	Based on available data, the classification criteria are not met.	
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are not met.	
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.	
Aspiration hazard	Not likely, due to the form of the product.	
Mixture versus substance information	Not available.	

SECTION 12: Ecological information

12.1. Toxicity Harmful to aquatic life with long lasting effects.

Components	Species	Test Results
1H-Imidazole-1-ethanol, 2-(8-heptadecenyl)-4,5-dihydro- (CAS 95-38-5)		
Aquatic		
<i>Acute</i>		
Algae	EC50	Algae 0.03 mg/l, 72 hours
Crustacea	EC50	Daphnia magna 0.136 mg/l, 48 hours
Fish	LC50	(Brachydanio rerio) 0.3 mg/l, 96 hours
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics		
Aquatic		
<i>Acute</i>		
Crustacea	EC50	Daphnia 1000 mg/l, 48 h
Fish	LC50	Oncorhynchus mykiss 1000 mg/l, 96 h

12.2. Persistence and degradability No data is available on the degradability of any ingredients in the mixture.

12.3. Bioaccumulative potential No data available.

Partition coefficient n-octanol/water (log Kow) Not available.

Bioconcentration factor (BCF) Not available.

12.4. Mobility in soil No data available.

12.5. Results of PBT and vPvB assessment This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.

12.6. Other adverse effects GWP: 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.
EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.

SECTION 14: Transport information

ADR

14.1. UN number	UN1950
14.2. UN proper shipping name	AEROSOLS, flammable
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Hazard No. (ADR)	Not assigned.
Tunnel restriction code	D
ADR/RID - Classification code:	5F
14.4. Packing group	Not assigned.
14.5. Environmental hazards	No
14.6. Special precautions for user	Not assigned.

RID

14.1. UN number	UN1950
14.2. UN proper shipping name	AEROSOLS, flammable
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
14.4. Packing group	Not assigned.
14.5. Environmental hazards	No
14.6. Special precautions for user	Not assigned.

ADN

14.1. UN number	UN1950
14.2. UN proper shipping name	AEROSOLS, flammable
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
14.4. Packing group	Not assigned.
14.5. Environmental hazards	No
14.6. Special precautions for user	Not assigned.

IATA

14.1. UN number	UN1950
14.2. UN proper shipping name	Aerosols, flammable
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
14.4. Packing group	Not assigned.
14.5. Environmental hazards	No
ERG Code	10L

14.6. Special precautions for user	Not assigned.
Other information	
Passenger and cargo aircraft	Allowed with restrictions.
Cargo aircraft only	Allowed with restrictions.

IMDG

14.1. UN number	UN1950
14.2. UN proper shipping name	Aerosols, flammable
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
14.4. Packing group	Not assigned.
14.5. Environmental hazards	
Marine pollutant	No
EmS	F-D, S-U
14.6. Special precautions for user	Not assigned.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not established.

ADN; ADR; IATA; IMDG; RID



SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Retained direct EU regulations

- Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended**
Not listed.
- Regulation (EU) 2019/1021 On persistent organic pollutants (recast), as amended**
Not listed.
- Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended**
Not listed.
- Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended**
Not listed.
- Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended**
Not listed.
- Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended**
Not listed.
- Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry, as amended**
Not listed.
- Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA**
Not listed.

Authorisations

- Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended**
Not listed.

Restrictions on use

- Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended**
Not listed.

Other EU regulations

Directive 2012/18/EU on major accident hazards involving dangerous substances, as amended

Not listed.

Other regulations

Not available.

15.2. Chemical safety assessment

No Chemical Safety Assessment has been carried out.

SECTION 16: Other information

List of abbreviations

ADN: European Agreement Concerning the International Carriage of Dangerous Goods by Inland Waterways.
ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.
ADR: European Agreement Concerning the International Carriage of Dangerous Goods by Road.
ATE: Acute Toxicity Estimate according to REGULATION (EC) No 1272/2008 (CLP).
CAS: Chemical Abstract Service.
Ceiling: Short Term Exposure Limit Ceiling value.
CEN: European Committee for Standardization.
CLP: Classification, Labeling and Packaging REGULATION (EC) No 1272/2008 on classification, labeling and packaging of substances and mixtures.
GWP: Global Warming Potential.
IATA: International Air Transport Association.
IBC Code: International Code for the Construction and Equipment of Ships Carrying Dangerous Chemicals in Bulk.
IMDG: International Maritime Dangerous Goods.
MAK: Threshold limit values Germany (Maximale Arbeitsplatzkonzentration - DFG).
MARPOL: International Convention for the Prevention of Pollution from Ships.
PBT: Persistent, bioaccumulative and toxic.
REACH: Registration, Evaluation and Authorization of Chemicals (REGULATION (EC) No 1907/2006 concerning Registration, Evaluation, Authorization and Restriction of Chemicals).
RID: Regulations concerning the international carriage of dangerous goods by rail (Règlement International concernant le transport de marchandises dangereuses par chemin de fer).
RID: Regulations concerning the International Carriage of Dangerous Goods by Rail.
STEL: Short term exposure limit.
TLV: Threshold Limit Value.
TWA: Time Weighted Average.
VOC: Volatile organic compounds.
vPvB: Very persistent and very bioaccumulative.
STEL: Short-term Exposure Limit.

References

Not available.

Information on evaluation method leading to the classification of mixture

Not available.

Full text of any statements, which are not written out in full under sections 2 to 15

H302 Harmful if swallowed.
H304 May be fatal if swallowed and enters airways.
H314 Causes severe skin burns and eye damage.
H315 Causes skin irritation.
H318 Causes serious eye damage.
H332 Harmful if inhaled.
H373 May cause damage to organs through prolonged or repeated exposure.
H400 Very toxic to aquatic life.
H410 Very toxic to aquatic life with long lasting effects.

Revision information

None.

Training information

Not available.

Disclaimer

CRC Industries Europe UK Limited cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC. The products are governed by Regulation (EC) No 1272/2008 on the classification, labelling and packaging of substances and mixtures (CLP); Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (in each case, as amended and replaced) and other applicable laws. It is an importers or downstream users responsibility to ensure compliance of product they import. An SDS provided in the official language(s) of a country is not a guarantee of compliance in that country.