

2N3713 thru 2N3716 NPN

361-392

SILICON NPN POWER TRANSISTORS


... designed for medium-speed switching and amplifier applications. These devices feature:

- Total Switching Time at 3 A typically 1.15 μ s
- Gain Ranges Specified at 1 A and 3 A
- Low $V_{CE(sat)}$: typically 0.5V at $I_C = 5A$ and $I_B = 0.5A$
- Excellent Safe Operating Areas
- Complement to 2N3789-92

10 AMPERE

POWER TRANSISTORS
SILICON NPN

60-80 VOLTS
150 WATTS



MAXIMUM RATINGS

Rating	Symbol	2N3713 2N3715	2N3714 2N3716	Unit
Collector-Base Voltage	V_{CB}	80	100	Volts
Collector-Emitter Voltage	V_{CEO}	60	80	Volts
Emitter-Base Voltage	V_{EB}	7.0	7.0	Volts
Collector Current	I_C	10	10	Amps
Base Current	I_B	4.0	4.0	Amps
Power Dissipation	P_D	150	150	Watts
Thermal Resistance	θ_{JC}	1.17	1.17	$^{\circ}C/W$
Operating Junction and Storage Temperature Range	T_J and T_{stg}	-65 to +200		$^{\circ}C$

3





FIGURE 1 - POWER-TEMPERATURE DERATING CURVE



Safe Area Limits are indicated by Figures 12, 13. Both limits are applicable and must be observed.

STYLE 1:
PIN 1: BASE
2: EMITTER
CASE: COLLECTOR

NOTE:
1. DIM "Q" IS DIA.

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	-	39.37	-	1.550
B	-	21.08	-	0.830
C	6.35	7.62	0.250	0.300
D	0.99	1.09	0.039	0.043
E	-	3.43	-	0.135
F	29.90	30.40	1.177	1.197
G	10.67	11.18	0.420	0.440
H	5.33	5.59	0.210	0.220
J	16.64	17.15	0.655	0.675
K	11.18	12.19	0.440	0.480
Q	3.84	4.09	0.151	0.161
R	-	26.67	-	1.050

Collector connected to case.

CASE 11-01

(TO-3)



2N3713 thru 2N3716 NPN

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Characteristic		Symbol	Min	Max	Unit
Emitter-Base Cutoff Current (V _{EB} = 7 Vdc)	All Types	I _{EB0}	—	5	mAdc
Collector-Emitter Cutoff Current (V _{CE} = 80 Vdc, V _{BE} = -1.5 Vdc) (V _{CE} = 100 Vdc, V _{BE} = -1.5 Vdc) (V _{CE} = 60 Vdc, V _{BE} = -1.5 Vdc, T _C = 150°C) (V _{CE} = 80 Vdc, V _{BE} = -1.5 Vdc, T _C = 150°C)	2N3713, 2N3715 2N3714, 2N3716 2N3713, 2N3715 2N3714, 2N3716	I _{CEX}	— — — —	1 1 10 10	mAdc
Collector-Emitter Sustaining Voltage* (I _C = 200 mAdc, I _B = 0)	2N3713, 2N3715 2N3714, 2N3716	V _{CEO(sus)} *	60 80	— —	Vdc
DC Current Gain* (I _C = 1 Adc, V _{CE} = 2 Vdc) (I _C = 3 Adc, V _{CE} = 2 Vdc)	2N3713, 2N3714 2N3715, 2N3716 2N3713, 2N3714 2N3715, 2N3716	h _{FE} *	25 50 15 30	90 150 — —	—
Collector-Emitter Saturation Voltage* (I _C = 5 Adc, I _B = 0.5 Adc)	2N3713, 2N3714 2N3715, 2N3716	V _{CE(sat)} *	— —	1.0 0.8	Vdc
Base-Emitter Saturation Voltage* (I _C = 5 Adc, I _B = 0.5 Adc)	2N3713, 2N3714 2N3715, 2N3716	V _{BE(sat)} *	— —	2.0 1.5	Vdc
Base-Emitter Voltage* (I _C = 3 Adc, V _{CE} = 2 Vdc)	All Types	V _{BE} *	—	1.5	Vdc
Small Signal Current Gain (V _{CE} = 10 Vdc, I _C = 0.5 Adc, f = 1 MHz)	All Types	h _{fe}	4	—	—
Switching Times (Figure 2) (I _C = 5 A, I _{B1} = I _{B2} = 0.5 Adc) Rise Time Storage Time Fall Time		t _r t _s t _f	Typ		μs
			0.45 0.3 0.4		

*Use sweep test to prevent overheating

FIGURE 2 - TYPICAL SWITCHING TIMES



2N3713 thru 2N3716 NPN

FIGURE 3 - COLLECTOR CURRENT versus BASE CURRENT





FIGURE 4 - BASE CURRENT-VOLTAGE VARIATIONS





FIGURE 5 - COLLECTOR CURRENT-VOLTAGE VARIATIONS



NOTE 1. Dotted line indicates metered base current plus the I_{CBO} of the transistor at 175°C.

NOTE 2. Pulse test: pulse width $\approx 200 \mu\text{sec}$, duty cycle $\approx 1.5\%$

3

2N3713 thru 2N3716 NPN

FIGURE 6 - COLLECTOR-EMITTER SATURATION VOLTAGE VARIATIONS




FIGURE 7 - BASE-EMITTER SATURATION VOLTAGE VARIATIONS




FIGURE 8 - COLLECTOR CURRENT versus BASE-EMITTER VOLTAGE





FIGURE 9 - COLLECTOR CURRENT versus BASE-EMITTER RESISTANCE



2N3713 thru 2N3716 NPN

FIGURE 10 – CURRENT GAIN VARIATIONS






FIGURE 11 – CURRENT GAIN – BANDWIDTH PRODUCT versus COLLECTOR CURRENT



2N3713 thru 2N3716 NPN

SAFE OPERATING AREAS

FIGURE 12 - 2N3713, 2N3715





FIGURE 13 - 2N3714, 2N3716



V_{CE} , COLLECTOR-EMITTER VOLTAGE (VOLTS)

The Safe Operating Area Curves indicate $I_C - V_{CE}$ limits below which the device will not go into secondary breakdown. Collector load lines for specific circuits must fall within the applicable Safe Area to avoid causing a collector-emitter short. (Duty cycle of the excursions make no signifi-

cant change in these safe areas.) To insure operation below the maximum T_J , the power-temperature derating curve must be observed for both steady state and pulse power conditions.