



N-Channel JFETs

| PRODUCT SUMMARY | | | | |
|-----------------|--------------------------|------------------------------|--------------------------|---------------------------|
| Part Number | V _{GS(off)} (V) | V _{(BR)GSS} Min (V) | g _{fs} Min (mS) | I _{DSS} Max (mA) |
| 2N4338 | -0.3 to -1 | -50 | 0.6 | 0.6 |
| 2N4339 | -0.6 to -1.8 | -50 | 0.8 | 1.5 |
| 2N4340 | -1 to -3 | -50 | 1.3 | 3.6 |
| 2N4341 | -2 to -6 | -50 | 2 | 9 |

FEATURES

- Low Cutoff Voltage: 2N4338 <1 V
- High Input Impedance
- Very Low Noise
- High Gain: A_V = 80 @ 20 μA

BENEFITS

- Full Performance from Low-Voltage Power Supply: Down to 1 V
- Low Signal Loss/System Error
- High System Sensitivity
- High-Quality Low-Level Signal Amplification


APPLICATIONS

- High-Gain, Low-Noise Amplifiers
- Low-Current, Low-Voltage Battery-Powered Amplifiers
- Infrared Detector Amplifiers
- Ultrahigh Input Impedance Pre-Amplifiers

DESCRIPTION

The 2N4338/4339/4340/4341 n-channel JFETs are designed for sensitive amplifier stages at low- to mid-frequencies. Low cut-off voltages accommodate low-level power supplies and low leakage for improved system accuracy.

The TO-206AA (TO-18) package is hermetically sealed and suitable for military processing (see Military Information). For similar products in TO-226AA (TO-92) and TO-236 (SOT-23) packages, see the J/SST201 series data sheet.



ABSOLUTE MAXIMUM RATINGS

| | |
|--------------------------------|--------------|
| Gate-Source/Gate-Drain Voltage | -50 V |
| Forward Gate Current | 50 mA |
| Storage Temperature | -65 to 200°C |
| Operating Junction Temperature | -55 to 175°C |

| | |
|--|--------|
| Lead Temperature (¹ / ₁₆ " from case for 10 sec.) | 300°C |
| Power Dissipation ^a | 300 mW |

Notes
a. Derate 2 mW/°C above 25°C

For applications information see AN102 and AN106.



| SPECIFICATIONS FOR 2N4338 AND 2N4339 (T _A = 25 °C UNLESS OTHERWISE NOTED) | | | | | | | | |
|--|----------------------|---|------------------|--------|------|--------|------|------------|
| Parameter | Symbol | Test Conditions | Typ ^a | Limits | | | | Unit |
| | | | | 2N4338 | | 2N4339 | | |
| | | | | Min | Max | Min | Max | |
| Static | | | | | | | | |
| Gate-Source Breakdown Voltage | V _{(BR)GSS} | I _G = -1 μA, V _{DS} = 0 V | -57 | -50 | | -50 | | V |
| Gate-Source Cutoff Voltage | V _{GS(off)} | V _{DS} = 15 V, I _D = 0.1 μA | | -0.3 | -1 | -0.6 | -1.8 | |
| Saturation Drain Current ^b | I _{DSS} | V _{DS} = 15 V, V _{GS} = 0 V | | 0.2 | 0.6 | 0.5 | 1.5 | mA |
| Gate Reverse Current | I _{GSS} | V _{GS} = -30 V, V _{DS} = 0 V T _A = 150 °C | -2 | | -100 | | -100 | pA |
| | | | -4 | | -100 | | -100 | nA |
| Gate Operating Current ^b | I _G | V _{DG} = 15 V, I _D = 0.1 mA | -2 | | | | | pA |
| Drain Cutoff Current | I _{D(off)} | V _{DS} = 15 V, V _{GS} = -5 V | 2 | | 50 | | 50 | |
| Gate-Source Forward Voltage ^c | V _{GS(F)} | I _G = 1 mA, V _{DS} = 0 V | 0.7 | | | | | V |
| Dynamic | | | | | | | | |
| Common-Source Forward Transconductance | g _{fs} | V _{DS} = 15 V, V _{GS} = 0 V, f = 1 kHz | | 0.6 | 1.8 | 0.8 | 2.4 | mS |
| Common-Source Output Conductance | g _{os} | | | | | 5 | | 15 |
| Drain-Source On-Resistance | r _{ds(on)} | V _{DS} = 0 V, V _{GS} = 0 V, f = 1 kHz | | | 2500 | | 1700 | Ω |
| Common-Source Input Capacitance | C _{iss} | V _{DS} = 15 V, V _{GS} = 0 V, f = 1 MHz | 5 | | 7 | | 7 | pF |
| Common-Source Reverse Transfer Capacitance | C _{rss} | | 1.5 | | 3 | | 3 | |
| Equivalent Input Noise Voltage ^c | e _n | V _{DS} = 10 V, V _{GS} = 0 V, f = 1 kHz | 6 | | | | | nV/ √Hz |
| Noise Figure | NF | V _{DS} = 15 V, V _{GS} = 0 V f = 1 kHz, R _G = 1 MΩ | | | 1 | | 1 | dB |

| SPECIFICATIONS FOR 2N4340 AND 2N4341 (T _A = 25 °C UNLESS OTHERWISE NOTED) | | | | | | | | |
|--|----------------------|---|-------------------------|--------|------|--------|------|------|
| Parameter | Symbol | Test Conditions | Typ ^a | Limits | | | | Unit |
| | | | | 2N4340 | | 2N4341 | | |
| | | | | Min | Max | Min | Max | |
| Static | | | | | | | | |
| Gate-Source Breakdown Voltage | V _{(BR)GSS} | I _G = -1 μA, V _{DS} = 0 V | -57 | -50 | | -50 | | V |
| Gate-Source Cutoff Voltage | V _{GS(off)} | V _{DS} = 15 V, I _D = 0.1 μA | | -1 | -3 | -2 | -6 | |
| Saturation Drain Current ^b | I _{DSS} | V _{DS} = 15 V, V _{GS} = 0 V | | 1.2 | 3.6 | 3 | 9 | mA |
| Gate Reverse Current | I _{GSS} | V _{GS} = -30 V, V _{DS} = 0 V T _A = 150 °C | -2 | | -100 | | -100 | pA |
| | | | -4 | | -100 | | -100 | nA |
| Gate Operating Current ^b | I _G | V _{DG} = 15 V, I _D = 0.1 mA | -2 | | | | | pA |
| Drain Cutoff Current | I _{D(off)} | V _{DS} = 15 V | V _{GS} = -5 V | 2 | | 50 | | |
| | | | V _{GS} = -10 V | 3 | | | 70 | |
| Gate-Source Forward Voltage | V _{GS(F)} | I _G = 1 mA, V _{DS} = 0 V | 0.7 | | | | | V |



SPECIFICATIONS FOR 2N4340 AND 2N4341 (T_A = 25 °C UNLESS OTHERWISE NOTED)



| Parameter | Symbol | Test Conditions | Typ ^a | Limits | | | | Unit |
|---|--------------|---|------------------|--------|------|--------|-----|------------------------|
| | | | | 2N4340 | | 2N4341 | | |
| | | | | Min | Max | Min | Max | |
| Dynamic | | | | | | | | |
| Common-Source Forward Transconductance | g_{fs} | $V_{DS} = 15\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ kHz}$ | | 1.3 | 3 | 2 | 4 | mS |
| Common-Source Output Conductance | g_{os} | | | | 30 | | 60 | μS |
| Drain-Source On-Resistance | $r_{ds(on)}$ | $V_{DS} = 0\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ kHz}$ | | | 1500 | | 800 | Ω |
| Common-Source Input Capacitance | C_{iss} | $V_{DS} = 15\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ MHz}$ | 5 | | 7 | | 7 | pF |
| Common-Source Reverse Transfer Capacitance | C_{rss} | | 1.5 | | 3 | | 3 | |
| Equivalent Input Noise Voltage ^c | \bar{e}_n | $V_{DS} = 10\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ kHz}$ | 6 | | | | | nV/ $\sqrt{\text{Hz}}$ |
| Noise Figure | NF | $V_{DS} = 15\text{ V}, V_{GS} = 0\text{ V}$ $f = 1\text{ kHz}, R_G = 1\text{ M}\Omega$ | | | 1 | | 1 | dB |

Notes







- a. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.
- b. Pulse test: PW \leq 300 μs , duty cycle \leq 3%.
- c. This parameter not registered with JEDEC.

NPA

TYPICAL CHARACTERISTICS (T_A = 25 °C UNLESS OTHERWISE NOTED)




TYPICAL CHARACTERISTICS (T_A = 25°C UNLESS OTHERWISE NOTED)






TYPICAL CHARACTERISTICS (T_A = 25°C UNLESS OTHERWISE NOTED)


Transfer Characteristics




Transfer Characteristics




Transconductance vs. Gate-Source Voltage




Transconductance vs. Gate-Source Voltage



Circuit Voltage Gain vs. Drain Current




On-Resistance vs. Drain Current




TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)


Common-Source Input Capacitance vs. Gate-Source Voltage




Common-Source Reverse Feedback Capacitance vs. Gate-Source Voltage



Output Conductance vs. Drain Current



Equivalent Input Noise Voltage vs. Frequency





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.