

## PRODUCT DATASHEET

### P MR16 50 36 ° 8 W/2700 K GU5.3

PARATHOM® MR16 | Low-voltage LED reflector lamps MR16 with retrofit pin base



#### Areas of application

- Shops and exhibition rooms
- Domestic applications
- Commercial applications
- Accent lighting
- Outdoor use in suitable outdoor luminaires only

#### Product benefits

- Quick, simple and safe replacement without rewiring
- Design, dimensions, luminous flux comparable to an incandescent or halogen lamp
- Low maintenance costs thanks to long lifetime
- No UV and near-IR radiation in the light beam
- Instant 100 % light, no warm-up time

#### Product features

- LED alternative to low voltage halogen lamps
- High color consistency:  $\leq 6$  SDCM
- Not dimmable
- Base: GU5.3
- Lamp made of glass



- Good quality of light; color rendering index  $R_a \geq 80$
- Lifetime: up to 15,000 h


## TECHNICAL DATA

### Electrical data

Nominal wattage	8 W
Construction wattage	8.00 W
Nominal voltage	12 V
Claimed equiv. conventional lamp power	50 W
Nominal current	720 mA
Type of current	AC/DC
Inrush current	11.2 A
Operating frequency	50/60 Hz
Mains frequency	50/60 Hz
Max. lamp no. on circuit break. 10 A (B)	22
Max. lamp no. on circuit break. 16 A (B)	36
Power factor $\lambda$	0.90

### Photometrical data

Luminous intensity	1000 cd
Luminous flux	621 lm
Nominal useful luminous flux 90°	621 lm
Luminous efficacy	77 lm/W
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 K
Color rendering index Ra	$\geq 80$
Light color	827
Standard deviation of color matching	$\leq 6$ sdcM
Rated peak intensity	1000 cd
Rated LLMF at 6,000 h	0.80
Flickering metric (Pst LM)	0.2
Stroboscope effect metric (SVM)	0.4



### Light technical data

Beam angle	36 °
Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

### Dimensions & Weight

Overall length	46.00 mm
Diameter	51.00 mm
Maximum diameter	51 mm
Product weight	46.00 g

### Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
Maximum temperature at tc test point	102 °C

### Lifespan

Lifespan	15000 h <sup>1)</sup>
Number of switching cycles	100000
Lumen maintenance at end of service lifetime	0.70
Rated lamp survival factor at 6,000 h	≥ 0.90

1) L70/B50

### Additional product data

Base (standard designation)	GU5.3
Mercury content	0.0 mg

### Capabilities

Dimmable	No
----------	----

### Certificates & Standards

Energy efficiency class	G 1)
Energy consumption	9.00 kWh/1000h
Type of protection	IP20
Standards	CE / EAC
Photobiological safety group acc. to EN62778	RG1

1) Energy efficiency class (EEC) on a scale of A (highest efficiency) to G (lowest efficiency)

### Country-specific categorizations

Order reference	LPMR165036 8W/8
-----------------	-----------------

### Energy labelling regulation data acc EU 2019/2015

Lighting technology used	LED
Non-directional or directional	DLS
Mains or non-mains	NMLS
Light source cap-type (or other electric interface)	GU5.3
Connected light source (CLS)	No
Color-tuneable light source	No
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	SINGLE_VALUE
Claim of equivalent power	Yes
Length	46.00 mm
Height	51.00 mm
Width	51.00 mm
Chromaticity coordinate x	0.455
Chromaticity coordinate y	0.405
R9 Colour rendering index	1
Beam angle correspondence	NARROW_CONE_90
Survival factor	0,9
Displacement factor	0.70
LED light source replaces a fluorescent light source	No
EPREL ID	523010
Model number	AC32715

### EQUIPMENT / ACCESSORIES

- Equipped with high-power LEDs

### DOWNLOAD DATA

#### Documents and certificates



Declarations Of Conformity CE

#### Photometric and lighting design files



Spectral power distribution

### LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075609259	Folding box 1	49 mm x 49 mm x 62 mm	52.00 g	0.15 dm <sup>3</sup>
4058075609266	Shipping box 10	255 mm x 107 mm x 72 mm	573.00 g	1.96 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

### References / Links

- For further products and actual information concerning LED lamps see [www.ledvance.com/ledlamps](http://www.ledvance.com/ledlamps)
- For Guarantee see [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)
- Further information see [www.ledvance.com/low-voltage-ledlamps](http://www.ledvance.com/low-voltage-ledlamps)

### DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.