## ()ideal-tek

## **Product Datasheet**

Product code:	E5250.CR.BG	
Product type:	High Precision Cutters	
Made in:	Switzerland	
Description:	The 5250 is a high precision cutter belonging to the oblique head cutter family. The angled blade geometry supports the operator's ergonomics during the cut. The full-flush cutting edge is suitable to perform very clean cuts on small size material. The 5250 is equipped with an ESD Ergo-tek handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The blades are hardened to 67HRC hardness.	
Head description:	Small Oblique	
Cutting edges:	Full-Flush	
Cutting capacity:	soft wire 0.20-1.20 mm (32-17 AWG)	
Body material:	High carbon-chromium low alloy steel (100Cr6)	
Body finishing:	Sandblasted	
Handle material:	Ergo-tek - Thermoplastic Elastomer + PP compound	
Picture:		





Dimensions:	OAL (A)	130.0 mm – 5.118 inch
	Width	60.0 mm – 2.362 inch
	Height	21.0 mm – 0.827 inch
Head		
dimensions:	Width (C)	10.0 mm – 0.394 inch
	Thickness (D)	6.4 mm – 0.252 inch
	В	14.5 mm – 0.571 inch
	G	11.0 mm – 0.433 inch



