

RNF-100-1/16-0-STK

✓ ACTIVE

RAYCHEM | RAYCHEM RNF-100


TE Internal #: 5052892055

Black, 2:1, Single Wall Tubing, Shrinks To .031 in [.8 mm], Irradiated Modified Polyolefin, .063 in [1.6 mm] Inner Diameter, RAYCHEM RNF-100

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Single Wall**

Expanded Inside Diameter (Min): **1.6 mm [.063 in]**

Recovered Inside Diameter (Max): **.8 mm [.031 in]**

Shrink Ratio: **2:1**

Features

Product Type Features

Wall Type	Single Wall
-----------	-------------

Electrical Characteristics

Operating Voltage (Max)	.6 kV
-------------------------	-------

Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	.2 mm[.008 in]
Recovered Wall Thickness (Nominal)	.45 mm[.018 in]
Product Length	1220 mm[48.031 in]
Expanded Inside Diameter (Min)	1.6 mm[.063 in]
Recovered Inside Diameter (Max)	.8 mm[.031 in]
Tubing Size Range	.8 – 1.6 mm[.031 – .063 in]



Usage Conditions

Shrink Temperature (Min)	95 °C
Fluid Resistance	Splash Protection
Tubing Flammability Type	Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Recovery Temperature	121 °C

Operation/Application

Mechanical Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
-----------------------	----------------------------------------------------

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

RNF-100-1/16-0-STK

Black, 2:1, Single Wall Tubing, Shrinks To .031 in [.8 mm], Irradiated Modified Polyolefin, .063 in [1.6 mm] Inner Diameter, RAYCHEM RNF-100




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM RNF-100



Heat Shrink Tubing(885)



Power Cable Tubing & Accessories(8)

Customers Also Bought



TE Part #8-326875-1
TERMINAL,PIDG R 26-22 6



TE Part #3-641193-3
03P MTA100 CONN ASSY GRN LF



TE Part #5052842031
RNF-100-3/64-0-STK



TE Part #5053092090
RNF-100-1/4-0-STK




TE Part #5053142077
RNF-100-3/8-0-STK



TE Part #5052902015
RNF-100-1/16-2-STK



TE Part #ZPF000000000008584
983-6S 12-12 PN



TE Part #APH3-09-08-1-B
APH3-09-08-1-B



Documents

Product Drawings

RNF-100-1/16-0-STK

English

Datasheets & Catalog Pages

Measuring_Single_Wall_Tubing

English

RNF-100 Pages from 9-1773447-9

English

Selecting_Correct_Tubing_1216

English

Flexible, Flame-Retardant, High Performance, Polyolefin Heat-Shrinkable Tubing

English

Product Specifications

Application Specification

English