

# SINGLE POLE DISTRIBUTION BLOCK



## CERTIFICATIONS



## FEATURES

Tinned copper or aluminum block allows for copper or aluminum conductor direct connections, or using ferrule

Screw retaining cover is hinged and removable

Design allows for visual inspection of conductor and confirmation of connection

Modular snap-together blocks for building multi-pole power blocks

Easily clips onto DIN rail or mounts to panel with screws

95% fill ratio

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free

## SPECIFICATIONS

**Finish:** Tinned

Table 1/2

Catalog Number	Item Name	Max Current Rating, IEC	Max Current Rating, UL/CSA	Line Side Connection	Load Side Connection	Material

UD-80A	569010	80 A	85 A	Cable	6 Cables	Copper, Thermoplastic
UDF-250A	569041	250 A	255 A	Flat Conductor	6 Cables	Copper, Thermoplastic
UDJ-125A	569020	125 A	150 A	Cable	7 Cables	Copper, Thermoplastic
UDJ-160A	569030	160 A	200 A	Cable	7 Cables	Copper, Thermoplastic
UD-400212AL	569251	400 A	400 A	2 Cables	12 Cables	Aluminum, Thermoplastic
UD-400112AL	569252	400 A	335 A	Cable	12 Cables	Aluminum, Thermoplastic
UD9C630AL	569203	630 A	420 A	Cable	9 Cables	Aluminum, Thermoplastic
UDF9C500AL	569204	500 A	490 A	Flat Conductor	9 Cables	Aluminum, Thermoplastic
UD2C12C630AL	569205	630 A	670 A	2 Cables	12 Cables	Aluminum, Thermoplastic
UD6C500AL	569201	500 A	380 A	Cable	6 Cables	Aluminum, Thermoplastic
UDF6C500AL	569202	500 A	475 A	Flat Conductor	6 Cables	Aluminum, Thermoplastic
UDF12C500AL	569206	500 A	500 A	Flat Conductor	12 Cables	Aluminum, Thermoplastic
UDF-500A	569060	500 A	335 A	Flat Conductor	11 Cables	Copper, Thermoplastic
UD-400212CU	569051	400 A	400 A	2 Cables	12 Cables	Copper, Thermoplastic
UD-400112CU	569052	400 A	335 A	Cable	12 Cables	Copper, Thermoplastic
UD-400A	569050	400 A	335 A	Cable	11 Cables	Copper, Thermoplastic
UD-250A	569040	250 A	255 A	Cable	11 Cables	Copper, Thermoplastic
UD2C12C1000AL	569207	1000 A	760 A	2 Cables	12 Cables	Aluminum, Thermoplastic
UDF12C800AL	569208	800 A	670 A	Flat Conductor	12 Cables	Aluminum, Thermoplastic
UD2C9C1250AL	569209	1250 A	950 A	2 Cables	9 Cables	Aluminum, Thermoplastic
UDF9C1000AL	569210	1000 A	840 A	Flat Conductor	9 Cables	Aluminum, Thermoplastic

Table 2/2

Catalog Number	Item Name	Line Side Max Conductor Size, UL	Load Side Max Conductor Size, UL	Max Working Voltage, IEC (Ui)	Max Working Voltage, UL (Vin)	Certifications
UD-80A	569010	#4	#4	1000	600	cUR, CSA, UR, RoHS, CE, ERIFLEX UD
UDF-250A	569041	70 mm <sup>2</sup>	#4	1000	600	cUR, UR, RoHS, CE, ERIFLEX UD
UDJ-125A	569020	1/0 AWG	#4	1000	600	cUR, CSA, UR, RoHS, CE, ERIFLEX UD
UDJ-160A	569030	3/0 AWG	#4	1000	600	cUR, CSA, UR, RoHS, CE, ERIFLEX UD
UD-400212AL	569251	3/0 AWG	#6	1000, 1500	1000	cUR, CSA, UR, RoHS, CE, ERIFLEX UD
UD-400112AL	569252	400 kcmil	#6	1000, 1500	1000	cUR, CSA, UR, RoHS, CE, ERIFLEX UD
UD9C630AL	569203	600 kcmil	#4	1000, 1500	1000	UL
UDF9C500AL	569204	100 mm <sup>2</sup>	#4	1000, 1500	1000	UL
UD2C12C630AL	569205	400 kcmil	#4	1000, 1500	1000	UL
UD6C500AL	569201	500 kcmil	1/0 AWG	1000, 1500	1000	UL
UDF6C500AL	569202	100 mm <sup>2</sup>	1/0 AWG	1000, 1500	1000	UL
UDF12C500AL	569206	100 mm <sup>2</sup>	#4	1000, 1500	1000	UL
UDF-500A	569060	185 mm <sup>2</sup>	#1	1000	600	cUR, UR, RoHS, CE, ERIFLEX UD
UD-400212CU	569051	3/0 AWG	#6	1000, 1500	1000	cUR, CSA, UR, RoHS, CE, ERIFLEX UD
UD-400112CU	569052	400 kcmil	#6	1000, 1500	1000	cUR, CSA, UR, RoHS, CE, ERIFLEX UD
UD-400A	569050	400 kcmil	#1	1000	600	cUR, CSA, UR, RoHS, CE, ERIFLEX UD
UD-250A	569040	250 kcmil	#1	1000	600	cUR, CSA, UR, RoHS, CE, ERIFLEX UD
UD2C12C1000AL	569207	500 kcmil	#4	1000, 1500	1000	UL

Catalog Number	Item Name	Line Side Max Conductor Size, UL	Load Side Max Conductor Size, UL	Max Working Voltage, IEC (Ui)	Max Working Voltage, UL (Vin)	Certifications
UDF12C800AL	569208	240 mm <sup>2</sup>	#4	1000, 1500	1000	UL
UD2C9C1250AL	569209	750 kcmil	3/0 AWG	1000, 1500	1000	UL
UDF9C1000AL	569210	240 mm <sup>2</sup>	3/0 AWG	1000, 1500	1000	UL

## ADDITIONAL PRODUCT DETAILS

Increase the number of outputs with one input using a jumper on blocks with a Max Current Rating, IEC up to 160 A.

Blocks with 1,000 VAC/DC Max Working Voltage, UL are ideal for solar applications.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°F) to maintain working temperature of 185°F										
Ambient Temperature (°F)	86°	95°	104°	113°	122°	131°	140°	149°	158°	167°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47
*environment around the terminal blocks inside the enclosure										

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**