




PIDG

TE Internal #: 165049
Crimp Wire Pins, Tabs & Ferrules, Wire Pin, Mating Pin Diameter
2.6 mm [.102 in], 12 – 10 AWG Wire Size, 2.62 – 6.64 mm² Wire Size,
PIDG
[View on TE.com >](#)

Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules > PIDG Formed Wire Pins



Crimp Wire Terminal Type: **Wire Pin**
Mating Pin Diameter: **2.6 mm [.102 in]**
Compatible Insulation Diameter Range: **6.3 mm [.25 in]**
Wire Size: **2.62 – 6.64 mm²**

[All PIDG Formed Wire Pins \(6\)](#)

Features

Product Type Features

Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Sleeve Material	Nylon
Insulation Material	Nylon
Primary Product Color	Yellow

Contact Features

Contact Mating Area Length	10 mm[.39 in]
Contact Fabrication	Stamped & Formed
Crimp Wire Terminal Type	Wire Pin



Mating Pin Diameter	2.6 mm[.102 in]
Barrel Type	Closed
Terminal Plating Material	Tin
Contact Shape & Form	Round
Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

DIN Wire Size	2.62 – 6.64 mm²
Compatible Insulation Diameter Range	6.3 mm[.25 in]
Wire Size	5180 – 13100 CMA
Barrel Inside Diameter	6.4 mm[.253 in]
Terminal Material Thickness	.99 mm[.039 in]
Overall Product Length	29.08 mm[1.145 in]

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer








This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	TE Part # 59239-4 HHHT PIDG PG 12-10 ASSY	TE Part # 58423-1 DIE, RBY IS9252	TE Part # 58433-3 PRO CR ASSY, RBY IS9252
TE Part # 539691-2 ERGO DIE R.B.Y	TE Part # 2063030-1 SDE DIESET, RBY, UL	TE Part # 47808-6 DIES PIDG 12-10 DIE SET	TE Part # 679300-1 1210 PIDG CRIMP HEAD
TE Part # 169400 CERTI-LOK FRAME W/O DIES	TE Part # 1-59239-4 HHHT PIDG 16-10 HEAD	TE Part # 1SET191001R0000 CRIMP-HT	TE Part # 1SET191002R0000 TET CRIMP-HT




Also in the Series | PIDG



Customers Also Bought





TE Part #9-1377174-9
SMP 9-0160477-2



TE Part #165168
TERM, WIRE PIN, PIDG, 22-16



TE Part #TCD14745101-004
M12D4-MS-RJ-PUR-22SH-TYPE C
GREEN-3.0M



TE Part #224920-E
MICROS STV 9 407 188 * 0007 J 3
224920 M



TE Part #2271500-1
34 PLUG KIT,M-SER,CC,JS,W/HOOD

Documents

Product Drawings

TERM, WIRE PIN, PIDG, 12 - 10, -ASI

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_165049_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_165049_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_165049_J.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_165049_G.3d_igs.zip

English

Customer View Model

ENG_CVM_165049_G.3d_stp.zip

English

Customer View Model

ENG_CVM_165049_G.2d_dxf.zip

English



By downloading the CAD file I accept and agree to the Terms and Conditions of use.	
Datasheets & Catalog Pages	
PIDG TERMINALS & SPLICES Quick Reference Guide	
English	
Product Specifications	
Application Specification	
English	
Product Environmental Compliance	
MD_165049_11252014019_dmtec	
English	
MD_165049_11252014019_dmtec	
English	
Instruction Sheets	
Instruction Sheet (U.S.)	
English	
Agency Approvals	
UL Report	
English	