





Phase Monitor

SPECIFICATIONS


• 3-Phase - 3 Wire Input

• Trip delay (T) -0.2 to 10 Sec • LED Indication: Relay ON, Power ON


• Slim, Space Saving Design

• DIN Rail Mount


· Monitors, Phase Sequence, Under Voltage, Over Voltage



Terminal Connections



Timing Diagram



ORDERING INFORMATION

PART NUMBER	SUPPLY VOLTAGE	
DPR175A	3Ø/3W, 170 TO 290V AC, P-P	

SPECIFICATIONS					
ACCURACY (TRIP VOLTAGE)	$\pm 0.5\%$ of F.S. (F.S. = Full Scale)				
RESET	Auto reset on removal of fault condition				
OUTPUT CONTACT	SPDT (1 C/O)				
CONTACT RATING	N/0:5A, N/C:3A @ 250V AC				
PHASE SEQUENCE,	Yes				
UNDER VOLTAGE	170 to 224V AC				
OVER VOLTAGE	236 to 290V AC				
TRIP DELAY (T)	0.2 to 10 Sec				
POWER ON DELAY	400 msec				
ACCURACY (TRIP TIME)	\pm 5% of F.S. (F.S. = Full Scale)				
NOMINAL INPUT VOLTAGE	230V AC				
POWER CONSUMPTION	8VA max				
OPERATING VOLTAGE	170 to 290V AC				
TEMPERATURE	Operating:	0 to 50°C (32 to 122°F)			
	Storage:	-20 to 75°C (-4 to 167°F)			
HUMIDITY	Up to 95% RH				
WEIGHT	62 g				
PROTECTION LEVEL	IP50 for faceplate IP40 for housing				

► LED INDICATION CHART

SUPPLY	RELAY LED	POWER LED	
Nominal condition	ON	ON	
Phase reversed	OFF	ON	
UV / OV	OFF	ON	

IP20 for terminals