# **TRACO POWER**

### **DC/DC Converter**

## **TEA 1E Series, 1 Watt**

- Highly cost efficient design
- I/O isolation: 1'500 VDC
- Operating temperature range -40 to +85 °C without derating
- 5 VDC (±10%) input voltage range
- Unregulated outputs
- Efficiency up to 78%
- Industry standard SIP-7 package
- 3-year product warranty



The TEA 1E is an unregulated 1 Watt DC/DC SIP-7 converter series which is specifically designed to offer a low-cost solution while keeping a high quality standard. This new series focuses on a simple but effective design approach, which minimizes component and labor cost and is complemented with a complete automatization of the manufacturing process. An operating temperature range from -40°C to 85°C without derating and an I/O-isolation of 1'500 VDC enables this series to cover many different applications. The industry standard package of this converter offers a broad application range in any space, cost critical application and is especially suited for high volume projects where simple but reliable products are needed.

Ν	Models					
	Order Code	Input Voltage	Output Voltage	Output Current	Efficiency	
		Range	nom.	max.	typ.	
	TEA 1-0505E	4.5 - 5.5 VDC	5 VDC	200 mA	78 %	
		(5 VDC nom.)			10 70	

# **TRACO POWER**

Input Specifications				
Input Current - At no load	28 mA typ.			
Surge Voltage	<b>9 VDC max.</b> (1 s max.)			
Recommended Input Fuse	500 mA (slow blow)			
	(The need of an external fuse has to be assessed			
	in the final application.)			
Input Filter	Internal Capacitor			

Voltage Set Accuracy		<b>±3% max.</b> (at 60 % load)
Regulation	- Input Variation (1% Vin step)	1.5% max.
	- Load Variation (10 - 90%)	9% max.
Ripple and Noise	- 20 MHz Bandwidth	50 mVp-p typ.
		100 mVp-p max.
Capacitive Load		1'000 µF max.
Minimum Load		Not required
Temperature Coefficier	nt	±0.03 %/K max.
Start-up Time		30 ms max.
Short Circuit Protection	1	Limited 1 s max., Automatic recovery

#### **Safety Specifications**

Safety Standards

- IT / Multimedia Equipment

Designed for EN 62368-1 (no certification)

<b>General Specifica</b>	tions		
Relative Humidity		95% max. (non condensing)	
Temperature Ranges	- Operating Temperature	−40°C to +95°C	
	- Case Temperature	+105°C max.	
	- Storage Temperature	−55°C to +125°C	
Power Derating	- High Temperature	5 %/K above 85°C	
		See application note: www.tracopower.com/overview/tea1e	
Cooling System		Natural convection (20 LFM)	
Switching Frequency		100 kHz typ. (Royer)	
Insulation System		Functional Insulation	
Isolation Test Voltage	- Input to Output, 60 s	1'500 VDC	
Isolation Resistance	- Input to Output, 500 VDC	1'000 MΩ min.	
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	30 pF typ.	
Reliability	- Calculated MTBF	2'000'000 h (MIL-HDBK-217F, ground benign)	
Washing Process		Not allowed	
Housing Material		Plastic (UL 94 V-0 rated)	
Potting Material		Epoxy (UL 94 V-0 rated)	
Pin Material		Phosphor Bronze (C5191)	
Pin Foundation Plating		Nickel (1 µm min.)	
Pin Surface Plating		Tin (3 µm min.), bright	
Housing Type		Plastic Case	
Mounting Type		PCB Mount	
Connection Type		THD (Through-Hole Device)	
Footprint Type		SIP7	
Soldering Profile		Wave Soldering	
		265 °C / 5 s max.	
Weight		2 g	

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

# **TRACO POWER**

## **TEA 1E Series, 1 Watt**


www.tracopower.com/overview/tea1e

Environmental Compliance - REACH Declaration	www.tracopower.com/info/reach-declaration.pdf
	REACH SVHC list compliant
	REACH Annex XVII compliant
- RoHS Declaration	www.tracopower.com/info/rohs-declaration.pdf
	Exemptions: 7a, 7c-l
	(RoHS exemptions refer to the component
	concentration only, not to the overall
	concentration in the product (05A rule).)
- SCIP Reference Number	32d47a25-73b5-4ff8-9578-5d32c84ecced

#### **Supporting Documents**

Overview Link (for additional Documents)

**Outline Dimensions** 



	Pinout		
Pin	Function		
1	+Vin (Vcc)		
2	–Vin (GND)		
4	–Vout		
6	+Vout		

© Copyright 2023 Traco Electronic AG



Specifications can be changed without notice.