


- Ultra compact 15 Watt converter in DIP-16 metal casing
- Highest power density of 4.51 W/cm³
- Operating temperature range -40°C to +85°C
- Wide 2:1 input voltage ranges: 9-18, 18-36, 36-75 VDC
- High efficiency (up to 87%) for low thermal loss
- 6-side shielded metal case with insulated baseplate
- Built-in EN 55032 class A filter (conducted)
- Protection against short circuit
- 3-year product warranty



The TEL 15N is a series of isolated 15 Watt converters which come in an ultra compact DIP-16 metal package. The design purpose of this series was to miniaturized low power DC/DC converters to the maximum without sacrificing high efficiency. It solidifies the new standard for power density with 4.51 W/cm³ and effectively doubles the power density compared to 15 Watt converters in DIP-24 packages. The TEL 15N offers a wide 2:1 input voltage range and features a high efficiency of up to 87% which enables an operation temperature of up to +55°C at full load and up to 85°C with 50% load. The converters also have an internal input filter to comply with conducted emission standard EN 55032 class A. It's an economical solution for space critical and cost sensitive applications in instrumentation, IT and industrial electronics.

Models						
Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I _{max}	Vnom	I _{max}	
TEL 15-1211N	9 - 18 VDC (12 VDC nom.)	5.1 VDC	2'940 mA			86 %
TEL 15-1212N		12 VDC	1'250 mA			87 %
TEL 15-1213N		15 VDC	1'000 mA			87 %
TEL 15-1215N		24 VDC	625 mA			87 %
TEL 15-1222N		+12 VDC	625 mA	-12 VDC	625 mA	87 %
TEL 15-1223N		+15 VDC	500 mA	-15 VDC	500 mA	87 %
TEL 15-2411N	18 - 36 VDC (24 VDC nom.)	5.1 VDC	2'940 mA			86 %
TEL 15-2412N		12 VDC	1'250 mA			87 %
TEL 15-2413N		15 VDC	1'000 mA			87 %
TEL 15-2415N		24 VDC	625 mA			87 %
TEL 15-2422N		+12 VDC	625 mA	-12 VDC	625 mA	87 %
TEL 15-2423N		+15 VDC	500 mA	-15 VDC	500 mA	87 %
TEL 15-4811N	36 - 75 VDC (48 VDC nom.)	5.1 VDC	2'940 mA			86 %
TEL 15-4812N		12 VDC	1'250 mA			87 %
TEL 15-4813N		15 VDC	1'000 mA			87 %
TEL 15-4815N		24 VDC	625 mA			87 %
TEL 15-4822N		+12 VDC	625 mA	-12 VDC	625 mA	87 %
TEL 15-4823N		+15 VDC	500 mA	-15 VDC	500 mA	87 %

Note - 48 Vin models: If the input will be switched electromechanically, use an external 27 µF / 200 V / KXY capacitor to reduce voltage transient.

Input Specifications

Input Current	- At no load	12 Vin models: 20 mA typ. 24 Vin models: 10 mA typ. 48 Vin models: 7 mA typ.
	- At full load	12 Vin models: 1'450 mA typ. 24 Vin models: 720 mA typ. 48 Vin models: 360 mA typ.
Surge Voltage		12 Vin models: 25 VDC max. (1 s max.) 24 Vin models: 50 VDC max. (1 s max.) 48 Vin models: 100 VDC max. (1 s max.)
Input Inrush Current		28.6 A typ. (12 Vin models) 38.8 A typ. (24 Vin models) 51.6 A typ. (48 Vin models)
Under Voltage Lockout		12 Vin models: 8 VDC typ. 24 Vin models: 16 VDC typ. 48 Vin models: 34 VDC typ.
Recommended Input Fuse		12 Vin models: 3'000 mA (slow blow) 24 Vin models: 1'500 mA (slow blow) 48 Vin models: 1'000 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Pi-Type

Output Specifications

Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax)	single output models: 0.8% max. dual output models: 0.8% max.
	- Load Variation (0 - 100%)	single output models: 1% max. dual output models: 1% max. (Output 1) 1% max. (Output 2)
	- Voltage Balance (symmetrical load)	dual output models: 2% max.
	- Cross Regulation (25% / 100% asym. load)	dual output models: 5% max.
Ripple and Noise	- 20 MHz Bandwidth	70 mVp-p typ. (w/ 2.2 µF / 50 V MLCC)
Capacitive Load	- single output	5.1 Vout models: 1'800 µF max. 12 Vout models: 820 µF max. 15 Vout models: 820 µF max. 24 Vout models: 270 µF max.
	- dual output	12 / -12 Vout models: 560 / 560 µF max. 15 / -15 Vout models: 270 / 270 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.02 %/K max.
Start-up Time		40 ms max.
Short Circuit Protection		Continuous, Automatic recovery (Hiccup Mode, Automatic Recovery)
Output Current Limitation		110% min. of Iout max.
		160% typ. of Iout max.
Transient Response	- Response Deviation	3% typ. / 5% max. (75% to 100% Load Step)
	- Response Time	500 µs max. (75% to 100% Load Step)

Safety Specifications

Safety Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Certification Documents	www.tracopower.com/overview/tel15n

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Pollution Degree	PD 3
Over Voltage Category	Not mains connected

EMC Specifications

EMI Emissions	- Conducted Emissions	EN 55032 class A (internal filter) EN 55032 class B (with external filter)
	- Radiated Emissions	EN 55032 class A (with external filter) EN 55032 class B (with external filter)
		External filter proposal: www.tracopower.com/overview/tel15n
EMS Immunity		EN 55024 (IT Equipment) EN 55035 (Multimedia)
	- Electrostatic Discharge	Air: EN 61000-4-2, ± 8 kV, perf. criteria A Contact: EN 61000-4-2, ± 6 kV, perf. criteria A
	- RF Electromagnetic Field	EN 61000-4-3, 20 V/m, perf. criteria A
	- EFT (Burst) / Surge	EN 61000-4-4, ± 2 kV, perf. criteria A EN 61000-4-5, ± 2 kV, perf. criteria A
		External filter proposal: www.tracopower.com/overview/tel15n
	- Conducted RF Disturbances - PF Magnetic Field	EN 61000-4-6, 10 Vrms, perf. criteria A Continuous: EN 61000-4-8, 30 A/m, perf. criteria A

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +80°C
	- Case Temperature	+110°C max.
	- Storage Temperature	-50°C to +125°C
Power Derating	- High Temperature	1.9 %/K above 55°C (average)
		See application note: www.tracopower.com/overview/tel15n
Cooling System		Natural convection (20 LFM)
Altitude During Operation		6'000 m max.
Switching Frequency		420 - 540 kHz (PWM)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	1'500 VDC
	- Input to Output, 1 s	1'800 VDC
	- Input to Case, 60 s	1'000 VDC
	- Output to Case, 60 s	1'000 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 M Ω min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	2'200 pF max.
Reliability	- Calculated MTBF	2'150'000 h (MIL-HDBK-217F, ground benign)
Washing Process		According to Cleaning Guideline www.tracopower.com/info/cleaning.pdf
Environment	- Vibration	2.4 g, 3 axis, random waveform, 30 min
	- Mechanical Shock	30 g, 3 axis, half sine, 11 ms
	- Thermal Shock	IPC-9592B
Housing Material		Aluminum
Potting Material		Silicone (UL 94 V-0 rated)
Pin Material		Copper Alloy (C6801)
Pin Foundation Plating		Nickel (2 - 4 μ m)
Pin Surface Plating		Tin (3 - 5 μ m), matte
Housing Type		Metal Case
Mounting Type		PCB Mount
Connection Type		THD (Through-Hole Device)
Footprint Type		DIP16
Soldering Profile		Lead-Free Wave Soldering
		260°C / 10 s
Weight		8.8 g
Thermal Impedance	- Case to Ambient	24.6 K/W typ.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance - REACH Declaration

www.tracopower.com/info/reach-declaration.pdf

- RoHS Declaration

REACH SVHC list compliant

REACH Annex XVII compliant

www.tracopower.com/info/rohs-declaration.pdf

Exemptions: 7a

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule))

- SCIP Reference Number


e74ab8fa-1d15-4362-954c-972163d70177

Supporting Documents

[Overview Link](#) (for additional Documents)

www.tracopower.com/overview/tel15n

Outline Dimensions



Pinout		
Pin	Single	Dual
1	-Vin	
8	NC	Common
9	+Vout	
10	-Vout	
16	+Vin	

NC: Not connected

Dimensions in mm (inch)

Tolerances: X.X ±0.5 (X.XX ±0.02)

X.XX ±0.25 (X.XXX ±0.01)

Pin diameter tolerances: X.X ±0.05 (X.XX ±0.002)