Onsemi

sss s

MOSFET – P-Channel, POWERTRENCH[®]

-30 V, -18 A, 20 mΩ

FDMC4435BZ, FDMC4435BZ-F127, FDMC4435BZ-F127-L701

General Description

This P-Channel MOSFET is produced using onsemi's advanced POWERTRENCH process that has been especially tailored to minimize the on-state resistance. This device is well suited for Power Management and load switching applications common in Notebook Computers and Portable Battery Packs.

Features

- Max $r_{DS(on)} = 20 \text{ m}\Omega$ at $V_{GS} = -10 \text{ V}$, $I_D = -8.5 \text{ A}$
- Max $r_{DS(on)} = 37 \text{ m}\Omega$ at $V_{GS} = -4.5 \text{ V}$, $I_D = -6.3 \text{ A}$
- Extended V_{GSS} Range (-25 V) for Battery Applications
- High Performance Trench Technology for Extremely Low r_{DS(on)}
- High Power and Current Handling Capability
- HBM ESD Protection Level > 7 kV Typical*
- 100% UIL Tested
- These Devices are Pb-Free and are RoHS Compliant

Applications

- High Side in DC DC Buck Converters
- Notebook Battery Power Management
- Load Switch in Notebook



⁸7₆₅

FDMC4435BZ = Specific Device Code

А XY


KK

YW

1

- = Assembly Location
- = 2-Digit Date Code
- = 2-Digit Lot Run Traceability Code
- = Wafer Lot Number
- = Assembly Start Week

PIN ASSIGNMENT



ORDERING INFORMATION

See detailed ordering and shipping information on page 6 of this data sheet

*The diode connected between the gate and source servers only as protection against ESD. No gate overvoltage rating is implied.

MOSFET MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)


Symbol	Parameter				Unit
V _{DS}	Drain to Source Voltage			-30	V
V _{GS}	Gate to Source Voltage			±25	V
ID	Drain Current	Continuous	$T_{C} = 25^{\circ}C$	-18	Α
		Continuous (Note 1a)	T _A = 25°C	-8.5	
		Pulsed		-50	
E _{AS}	Single Pulse Avalanche Energy	(Note 2)		32	mJ
PD	Power Dissipation	tion $T_{\rm C} = 25^{\circ}{\rm C}$		31	W
	Power Dissipation (Note 1a)		T _A = 25°C	2.3	1
T _J , T _{STG}	Operating and Storage Junction	n Temperature Range	•	–55 to + 150	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Symbol	Parameter	Rating	Unit
Rejc	Thermal Resistance, Junction to Case	4	°C/W
RθJA	Thermal Resistance, Junction to Ambient (Note 1a)	53	

1. $R_{\theta JA}$ is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.







b. 125°C/W when mounted on a minimum pad of 2 oz copper

2. Starting T_J = 25°C; P–ch: L = 1 mH, I_{AS} = –8 A, V_{DD} = –27 V, V_{GS} = –10 V.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
OFF CHARACTERISTICS						
BV _{DSS}	Drain to Source Breakdown Voltage	$I_D = -250 \ \mu A, \ V_{GS} = 0 \ V$	-30			V
$\frac{\Delta BV_{DSS}}{\Delta T_{J}}/$	Breakdown Voltage Temperature Coefficient	$I_D = -250 \ \mu\text{A}$, referenced to 25°C		21		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = -24$ V, $V_{GS} = 0$ V			-1	μΑ
		$V_{DS} = -24 \text{ V}, V_{GS} = 0 \text{ V}, T_{J} = 125^{\circ}\text{C}$			-100	
I _{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 25$ V, $V_{DS} = 0$ V			±10	μA

ON CHARACTERISTICS

V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, \ I_D = -250 \ \mu A$	-1.0	-1.8	-3.0	V
${\Delta V_{GS(th)} \over \Delta T_J}$ /	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = -250 \ \mu\text{A}$, referenced to 25°C		-5		mV/°C
r _{DS(on)}	Static Drain to Source On Resistance	$V_{GS} = -10$ V, $I_D = -8.5$ A		14	20	mΩ
		$V_{GS} = -4.5 \text{ V}, \text{ I}_{D} = -6.3 \text{ A}$		21	37	
		$V_{GS} = -10$ V, $I_D = -8.5$ A, $T_J = 125^{\circ}C$		20	29	1
9 FS	Forward Transconductance	$V_{DD} = -5 \text{ V}, \text{ I}_{D} = -8.5 \text{ A}$		25		S

DYNAMIC CHARACTERISTICS

C _{iss}	Input Capacitance	V_{DS} = -15 V, V_{GS} = 0 V, f = 1 MHz	1535	2040	pF
C _{oss}	Output Capacitance		310	410	pF
C _{rss}	Reverse Transfer Capacitance		280	420	pF
Rg	Gate Resistance	f = 1 MHz	4		Ω

SWITCHING CHARACTERISTICS


t _{d(on)}	Turn-On Delay Time	$V_{DD} = -15$ V, $I_D = -8.5$ A, $V_{GS} = -10$ V,	10	20	ns
t _r	Rise Time	$R_{GEN} = 6 \Omega$	9	18	ns
t _{d(off)}	Turn-Off Delay Time		35	56	ns
t _f	Fall Time		19	34	ns
Qg	Total Gate Charge	$V_{GS} = 0 V \text{ to } -10 V,$ $V_{DD} = -15 V, I_D = -8.5 A$	38	53	nC
		$V_{GS} = 0 V \text{ to } -4.5 V,$ $V_{DD} = -15 V, I_D = -8.5 A$	20	28	nC
Q _{gs}	Gate to Source Charge	$V_{DD} = -15 \text{ V}, \text{ I}_{D} = -8.5 \text{ A}$	4.3		nC
Q _{gd}	Gate to Drain "Miller" Charge		11		nC

DRAIN-SOURCE DIODE CHARACTERISTICS

V _{SD}	Source to Drain Diode Forward	V_{GS} = 0 V, I_S = –8.5 A (Note 3)	0.86	1.5	V
	Voltage	$V_{GS} = 0 \text{ V}, \text{ I}_{S} = -1.9 \text{ A} \text{ (Note 3)}$	0.74	1.2	
t _{rr}	Reverse Recovery Time	I _F = -8.5 A, di/dt = 100 A/μs	26	40	ns
Q _{rr}	Reverse Recovery Charge		12	20	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. Pulse Test: Pulse Width < 300 µs, Duty cycle < 2.0%.

TYPICAL CHARACTERISTICS (TJ = 25°C UNLESS OTHERWISE NOTED)



TYPICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ UNLESS OTHERWISE NOTED) (CONTINUED)




Figure 7. Gate Charge Characteristics




Figure 9. Unclamped Inductive Switching Capability




Figure 11. Forward Bias Safe Operating Area




Figure 8. Capacitance vs. Drain to Source Voltage






Figure 10. Maximum Continuous Drain Current vs. Case Temperature





TYPICAL CHARACTERISTICS (T_J = 25°C UNLESS OTHERWISE NOTED) (CONTINUED)








Figure 14. Junction-to-Ambient Transient Thermal Response Curve


ORDERING INFORMATION

Device	Device Marking	Package Type	Shipping [†]
FDMC4435BZ	FDMC4435BZ	WDFN8 3.3x3.3, 0.65P, case 511DR (Pb-Free)	3000 / Tape & Reel
FDMC4435BZ-F127	FDMC4435BZ	WDFN8 3.3x3.3, 0.65P, case 511DR (Pb-Free)	3000 / Tape & Reel
FDMC4435BZ-F127-L701	FDMC4435BZ	WDFN8 3.3x3.3, 0.65P, case 511DQ (Pb-Free)	3000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

POWERTRENCH is registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.






© Semiconductor Components Industries, LLC, 2019

WDFN8 3.3x3.3, 0.65P CASE 511DQ ISSUE 0

DATE 31 OCT 2016




- A. PACKAGE DOES NOT FULLY CONFORM TO
- JEDEC REGISTRATION MO-240.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 2009.
- D. LAND PATTERN RECOMMENDATION IS EXISTING INDUSTRY LAND PATTERN
- E. DIMENSIONS DO NOT INCLUDE BURRS OR MOLD FLASH. BURRS OR MOLD FLASH SHALL NOT EXCEED 0.10MM.

DOCUMENT NUMBER:	98AON13648G	Electronic versions are uncontrolled except when accessed directly from the Document Repositor Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.					
DESCRIPTION:	WDFN8 3.3X3.3, 0.65P	PAGE 2 OF 2					

ON Semiconductor and una are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the right of others.

MECHANICAL CASE OUTLINE

PACKAGE DIMENSIONS



DUSEM

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>