

**TRPL 12-60VUC 1CO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The all-rounder. Compact relay modules, 6 mm width with extensive accessories, maximum vibration resistance, and unlimited cross-connection possibilities.

- 1 CO contacts
- Contact material: AgNi
- Unique multi-voltage input from 12 to 60 V UC and 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white

**General ordering data**

|            |                                                                                                                                                                                        |
|------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version    | TERMSERIES-compact, Relay module, Number of contacts: 1, CO contact AgNi, Rated control voltage: 12...60 V UC $\pm 10\%$ , Continuous current: 6 A, PUSH IN, Test button available: No |
| Order No.  | <a href="#">2773770000</a>                                                                                                                                                             |
| Type       | TRPL 12-60VUC 1CO                                                                                                                                                                      |
| GTIN (EAN) | 4064675037545                                                                                                                                                                          |
| Qty.       | 10 pc(s).                                                                                                                                                                              |

Creation date August 21, 2023 9:15:00 PM CEST

Catalogue status 18.08.2023 / We reserve the right to make technical changes.

## TRPL 12-60VUC 1CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 62.5 mm | Depth (inches)  | 2.461 inch |
| Height     | 89.4 mm | Height (inches) | 3.52 inch  |
| Width      | 6.4 mm  | Width (inches)  | 0.252 inch |
| Net weight | 30 g    |                 |            |

## Temperatures

|                             |                                                                |                             |                |
|-----------------------------|----------------------------------------------------------------|-----------------------------|----------------|
| Storage temperature         | -40 °C...85 °C                                                 | Operating temperature       | -40 °C...60 °C |
| Operating temperature, min. | -40 °C                                                         | Operating temperature, max. | 60 °C          |
| Humidity                    | 5-85% relative humidity,<br>Tu = 40°C, without<br>condensation |                             |                |

## Control side

|                                |                                  |                  |                                                                          |
|--------------------------------|----------------------------------|------------------|--------------------------------------------------------------------------|
| Rated control voltage          | 12...60 V UC $\pm$ 10 %          | Rated current AC | 41 mA @ 12 V AC, 10.2 mA @ 60 V AC                                       |
| Rated current DC               | 20 mA @ 12 V DC, 5 mA @ 60 V DC  | Power rating     | 215 mW @ 12 V DC, 325 mW @ 60 V DC, 790 mVA @ 12 V AC, 440 mVA @ 60 V AC |
| Pull-in/drop-out voltage, typ. | 8.9 V / 6 V AC<br>8.7 V / 6 V DC | Status indicator | Green LED                                                                |
| Protective circuit             | Rectifier                        | Input frequency  | 45 - 65 Hz                                                               |

## Load side

|                                         |                                      |                                         |                                         |
|-----------------------------------------|--------------------------------------|-----------------------------------------|-----------------------------------------|
| Rated switching voltage                 | 250 V AC                             | Continuous current                      | 6 A                                     |
| Max. switching frequency at rated load  | 0.1 Hz                               | Max. switching voltage, DC              | 250 V                                   |
| Inrush current                          | 20 A / 20 ms                         | AC switching capacity (resistive), max. | 1500 VA                                 |
| DC switching capacity (resistive), max. | 72 W @ 12 V                          | Switch-on delay                         | < 40 ms                                 |
| Switch-off delay                        | < 35 ms                              | Contact type                            | 1 CO contact (AgNi)                     |
| Mechanical service life                 | 5 x 10 <sup>6</sup> switching cycles | Min. switching power                    | 1 mA @ 24 V, 10 mA @ 12 V, 100 mA @ 5 V |

## General data

|                                      |                                |                        |  |
|--------------------------------------|--------------------------------|------------------------|--|
| Operating altitude                   | $\leq$ 2000 m, above sea level |                        |  |
| Rail                                 | TS 35                          |                        |  |
| Test button available                | No                             |                        |  |
| Mechanical switch position indicator | No                             |                        |  |
| Colour                               | black                          |                        |  |
| UL94 flammability rating component   | Component                      | Housing                |  |
|                                      | UL94 flammability rating       | V-0                    |  |
|                                      | Component                      | Relay status indicator |  |
|                                      | UL94 flammability rating       | V-2                    |  |
|                                      | Component                      | Pusher                 |  |
|                                      | UL94 flammability rating       | V-0                    |  |

## Insulation coordination

|                                       |                       |                                                               |             |
|---------------------------------------|-----------------------|---------------------------------------------------------------|-------------|
| Rated voltage                         | 300 V                 | Pollution severity                                            | 2           |
| Surge voltage category                | III                   | Clearance and creepage distances for control side - load side | $\geq$ 6 mm |
| Type of isolation at input and output | reinforced insulation | Protection degree                                             | IP20        |

Creation date August 21, 2023 9:15:00 PM CEST

Catalogue status 18.08.2023 / We reserve the right to make technical changes.

## TRPL 12-60VUC 1CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Connection data

|                                                                                         |                     |                                                                                         |                      |
|-----------------------------------------------------------------------------------------|---------------------|-----------------------------------------------------------------------------------------|----------------------|
| Wire connection method                                                                  | PUSH IN             | Stripping length, rated connection                                                      | 9 mm                 |
| Clamping range, rated connection                                                        | 1.5 mm <sup>2</sup> | Clamping range, min.                                                                    | 0.14 mm <sup>2</sup> |
| Clamping range, max.                                                                    | 2.5 mm <sup>2</sup> | Wire connection cross section AWG, min.                                                 | AWG 26               |
| Wire connection cross section AWG, max.                                                 | AWG 14              | Wire cross-section, solid, min.                                                         | 0.14 mm <sup>2</sup> |
| Wire cross-section, solid, max.                                                         | 1.5 mm <sup>2</sup> | Wire cross-section, solid, min. (AWG)                                                   | AWG 26               |
| Wire cross-section, solid, max. (AWG)                                                   | AWG 16              | Wire connection cross section, finely stranded, min.                                    | 0.14 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, max.                                    | 2.5 mm <sup>2</sup> | Wire cross-section, finely stranded, min. (AWG)                                         | AWG 26               |
| Wire cross-section, finely stranded, max. (AWG)                                         | AWG 14              | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.14 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1.5 mm <sup>2</sup> | Conductor cross-section, flexible, AEH (DIN 46228-1), min.                              | 0.14 mm <sup>2</sup> |
| Conductor cross-section, flexible, AEH (DIN 46228-1), max.                              | 1.5 mm <sup>2</sup> | Twin wire-end ferrules, min.                                                            | 0.5 mm <sup>2</sup>  |
| Twin wire-end ferrules, max.                                                            | 1 mm <sup>2</sup>   | Blade size                                                                              | 0.6 x 3.5 mm         |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001437    | ETIM 7.0    | EC001437    |
| ETIM 8.0    | EC001437    | ECLASS 9.0  | 27-37-16-01 |
| ECLASS 9.1  | 27-37-16-01 | ECLASS 10.0 | 27-37-16-01 |
| ECLASS 11.0 | 27-37-16-01 | ECLASS 12.0 | 27-37-16-01 |

## Downloads

|                    |                                          |
|--------------------|------------------------------------------|
| Engineering Data   | <a href="#">CAD data – STEP</a>          |
| User Documentation | <a href="#">IS TRPL 6.4MM</a>            |
| Catalogues         | <a href="#">Catalogues in PDF-format</a> |

## TRPL 12-60VUC 1CO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


[www.weidmueller.com](http://www.weidmueller.com)

## Drawings


## Similar to illustration





## Wiring diagram



## Graph



## Graph



## TRPL 12-60VUC 1CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## TERMSERIES interface adapter



Faster signal wiring with less space

To reduce wiring times, pre-assembled cables are used between the control system and the interface level and are simply connected to the TERMSERIES adapter. This enables throughput times in electrical cabinet building to be significantly reduced. The adapter has a universal fit and offers a genuine space advantage in interaction with the TERMSERIES products with identical contours.

- Reduced wiring time due to plug-and-play concept with pre-assembled cables
- Can be applied to the input and output sides of the TERMSERIES
- Ready for plus and minus switching logic
- High space-saving due to universal fit to other TERMSERIES products

## General ordering data


|            |                            |                                                                         |
|------------|----------------------------|-------------------------------------------------------------------------|
| Type       | TIAL F10                   | Version                                                                 |
| Order No.  | <a href="#">1463540000</a> | TERMSERIES, Adapter, 10-pole plug according to DIN EN 60603-13,         |
| GTIN (EAN) | 4050118323559              | long locking lever, Number of signal paths: 8, Rated voltage DC : 24 V, |
| Qty.       | 1 pc(s).                   | Rated current (per signal path): 125 mA                                 |
| Type       | TIA F10                    | Version                                                                 |
| Order No.  | <a href="#">1463520000</a> | TERMSERIES, Adapter, 10-pole plug according to DIN EN 60603-13,         |
| GTIN (EAN) | 4050118323535              | long locking lever, Number of signal paths: 8, Rated voltage DC : 24 V, |
| Qty.       | 1 pc(s).                   | Rated current (per signal path): 125 mA                                 |
| Type       | TIAL F20                   | Version                                                                 |
| Order No.  | <a href="#">1463550000</a> | TERMSERIES, Adapter, 20-pole plug according to DIN EN 60603-13,         |
| GTIN (EAN) | 4050118331783              | long locking lever, Number of signal paths: 16, Rated voltage DC : 24   |
| Qty.       | 1 pc(s).                   | V, Rated current (per signal path): 60 mA                               |
| Type       | TIA SUBD 15S               | Version                                                                 |
| Order No.  | <a href="#">1463530000</a> | TERMSERIES, Adapter, Sub-D, 15-pole, DIN 41652 / IEC 60807,             |
| GTIN (EAN) | 4050118323542              | Number of signal paths: 8, Rated voltage DC : 24 V, Rated current (per  |
| Qty.       | 1 pc(s).                   | signal path): 125 mA                                                    |

**TRPL 12-60VUC 1CO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold


Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Slotted screwdriver**

Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

**General ordering data**

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | SDS 0.6X3.5X100            | Version                                                           |
| Order No.  | <a href="#">2749340000</a> | Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118895568              | thickness (A): 0.6 mm                                             |
| Qty.       | 10 pc(s).                  |                                                                   |

**Slotted screwdriver**

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

**General ordering data**

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | SDIS 0.6X3.5X100           | Version                                                           |
| Order No.  | <a href="#">2749810000</a> | Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118897012              | thickness (A): 0.6 mm                                             |
| Qty.       | 1 pc(s).                   |                                                                   |

**TRPL 12-60VUC 1CO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Feed through module****Precision-fit feed-through terminals**

The precisely fitting terminals enable potentials to be brought from the control side to the load side and vice versa. Due to the compatibility with the TERMSERIES, there is a uniform test system with a standardised test tap.

**General ordering data**

|            |                            |                                                    |
|------------|----------------------------|----------------------------------------------------|
| Type       | TXPL FT                    | Version                                            |
| Order No.  | <a href="#">2774080000</a> | TERMSERIES-compact, Feed-through terminal, PUSH IN |
| GTIN (EAN) | 4064675037859              |                                                    |
| Qty.       | 1 pc(s).                   |                                                    |

**Supply module****Space-saving feed-in terminals**

For easy feed-in of neutral or negative potentials at the input of switched potentials at the output. Cross-connections enable space-saving connection of sensors and actuators without additional feed-through terminal blocks.

**General ordering data**

|            |                            |                                            |
|------------|----------------------------|--------------------------------------------|
| Type       | TXPL S                     | Version                                    |
| Order No.  | <a href="#">2774100000</a> | TERMSERIES-compact, Supply module, PUSH IN |
| GTIN (EAN) | 4064675037873              |                                            |
| Qty.       | 1 pc(s).                   |                                            |

## TRPL 12-60VUC 1CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## WS 12/6



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

|            |                            |                                                    |
|------------|----------------------------|----------------------------------------------------|
| Type       | WS 12/6 MM WS              | Version                                            |
| Order No.  | <a href="#">2007200000</a> | WS, Terminal marker, 12 x 6 mm, Weidmueller, white |
| GTIN (EAN) | 4050118391886              |                                                    |
| Qty.       | 600 pc(s).                 |                                                    |

## Cross-connections



## Adjustable cross-connections

Increase the flexibility of your cross-connections. The TERM SERIES CROSS-CONNECTION (TCC) enables individually adjustable cross-connections with up to 51 poles. The maximum number of pluggable poles has been increased to 32 poles. The strip material can be shortened to the required length very easily. The cross-connectors convince thanks to their easy handling and visibility as well as their universal connection possibilities. An additional web prevents the spring from deforming during assembly.

- Individually adjustable cross-connection with 51 poles
- Additional bar to avoid deformation of the spring
- Increased cross-connection – up to 32 poles possible
- Vibration resistance

## General ordering data

|            |                            |                             |
|------------|----------------------------|-----------------------------|
| Type       | TCC 12.8/26 OR             | Version                     |
| Order No.  | <a href="#">2556380000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566697              |                             |
| Qty.       | 10 pc(s).                  |                             |

## TRPL 12-60VUC 1CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |                             |
|------------|----------------------------|-----------------------------|
| Type       | TCC 12.8/26 BK             | Version                     |
| Order No.  | <a href="#">2556500000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118567014              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 6.4/10 RD              | Version                     |
| Order No.  | <a href="#">2556400000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566918              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 6.4/51 RD              | Version                     |
| Order No.  | <a href="#">2556410000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566925              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 6.4/51 BL              | Version                     |
| Order No.  | <a href="#">2556450000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566963              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 6.4/51 BK              | Version                     |
| Order No.  | <a href="#">2556490000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118567007              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 6.4/2 BL               | Version                     |
| Order No.  | <a href="#">2556430000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566949              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 6.4/2 BK               | Version                     |
| Order No.  | <a href="#">2556470000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566987              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 6.4/10 BL              | Version                     |
| Order No.  | <a href="#">2556440000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566956              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 6.4/2 RD               | Version                     |
| Order No.  | <a href="#">2556390000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566901              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 12.8/26 BL             | Version                     |
| Order No.  | <a href="#">2556460000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566970              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 12.8/26 RD             | Version                     |
| Order No.  | <a href="#">2556420000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566932              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 6.4/51 OR              | Version                     |
| Order No.  | <a href="#">2556370000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566680              |                             |
| Qty.       | 10 pc(s).                  |                             |
| Type       | TCC 6.4/10 BK              | Version                     |
| Order No.  | <a href="#">2556480000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566994              |                             |
| Qty.       | 10 pc(s).                  |                             |

Creation date August 21, 2023 9:15:00 PM CEST

Catalogue status 18.08.2023 / We reserve the right to make technical changes.

## TRPL 12-60VUC 1CO

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

|            |                            |                             |
|------------|----------------------------|-----------------------------|
| Type       | TCC 6.4/2 OR               | Version                     |
| Order No.  | <a href="#">2556350000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566826              |                             |
| Qty.       | 10 pc(s).                  |                             |

|            |                            |                             |
|------------|----------------------------|-----------------------------|
| Type       | TCC 6.4/10 OR              | Version                     |
| Order No.  | <a href="#">2556360000</a> | TERMSERIES, Cross-connector |
| GTIN (EAN) | 4050118566673              |                             |
| Qty.       | 10 pc(s).                  |                             |

## Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | WS 10/6 M MC NE WS         | Version                                                            |
| Order No.  | <a href="#">1818400000</a> | WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, |
| GTIN (EAN) | 4032248310876              | Allen-Bradley, white                                               |
| Qty.       | 600 pc(s).                 |                                                                    |

## TRPL 12-60VUC 1CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Partition plate



## Versatile separation plates

Separation plates can be used to group together signals visually, to electrically isolate modules and to insert markings for a better overview. This makes them a particularly versatile accessory. Separation plates increase the clearance and creepage distances between two modules, thus increasing the rated insulation voltage between two modules to up to 600 V. Double separation plates can be marked with WAD5 or WS10/5 markers and enable continuous cross-connections. Installation is made easier with the perforations to individually break out the cross-connection channels.

- Partition plates visually separates groups from each other
- Indentations for individual breaking out the crossconnection channels
- Partition plates isolates between two modules by increasing the clearance and creepage distances of up to 600 V

## General ordering data

|            |                            |                                     |
|------------|----------------------------|-------------------------------------|
| Type       | TW TXS/TXZ R3.2            | Version                             |
| Order No.  | <a href="#">1240800000</a> | TERMSERIES, Partition plate         |
| GTIN (EAN) | 4050118028188              |                                     |
| Qty.       | 10 pc(s).                  |                                     |
| Type       | TXL PP                     | Version                             |
| Order No.  | <a href="#">2774090000</a> | TERMSERIES-compact, Partition plate |
| GTIN (EAN) | 4064675037866              |                                     |
| Qty.       | 10 pc(s).                  |                                     |

## TRPL 12-60VUC 1CO


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

## Miscellaneous

## Type code electromechanical relay (TERMSERIES-compact)



Type codes