206705-2 - ACTIVE

### AMP | AMP CPC

TE Internal #: 206705-2 Circular Power Connectors, Housing, 600 VDC, Wire-to-Wire, 9 Position, Wire & Cable, Receptacle, Pin, Power & Signal, Black, All Plastic, AMP CPC

### View on TE.com >





Connector Product Type: Housing

Operating Voltage: 600 VDC

Connector System: Wire-to-Wire

Number of Positions: 9

Sealable: No

### All Cable/Panel Mount Connector, CPC Series 1 (57)



## Features

### Product Type Features

Connector Product Type	Housing			
Connector System	Wire-to-Wire			
Sealable	No			
Connector & Contact Terminates To	Wire & Cable			
Connector & Housing Type	Receptacle			
Circular Connector Shell Type	All Plastic			
Configuration Features				
Reverse Numbering	Without			
Number of Positions	9			
Number of Power Positions	0			
Number of Signal Positions	9			
Electrical Characteristics				

Circular Power Connectors, Housing, 600 VDC, Wire-to-Wire, 9 Position, Wire & Cable, Receptacle, Pin, Power & Signal, Black, All Plastic, AMP CPC



Operating Voltage	600 VAC
Contact Features	
Reverse Gender	No
Contact Type	Pin
Contact Protection	With
Mechanical Attachment	
Mating Alignment Type	Keyed
Mating Alignment	With
Mating Retention Type	Threaded Coupling
Thread Size	3/4 - 20 UNEF-2A
Polarization Code	A
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	With
Panel Mount Feature	Without
Housing Features	
Body Orientation	Straight
Housing Color	Black
Housing Material	Thermoplastic
Circular Connector Shell Size	13
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None
Operation/Application	
Circuit Application	Power & Signal
Shielded	No
Industry Standards	
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	1
	Package

# **Product Compliance**

Circular Power Connectors, Housing, 600 VDC, Wire-to-Wire, 9 Position, Wire & Cable, Receptacle, Pin, Power & Signal, Black, All Plastic, AMP CPC



#### For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-

## **Compatible Parts**






Circular Power Connectors, Housing, 600 VDC, Wire-to-Wire, 9 Position, Wire & Cable, Receptacle, Pin, Power & Signal, Black, All Plastic, AMP CPC



# Also in the Series AMP CPC

00			
Circular Connector Adapters(7)	Circular Connector Caps & Covers(16)	Circular Connector Hardware(3)	Circular Connector Keying Plugs(2)
Circular Power Connectors(458)	Connector Backshells(56)	Connector Seals & Cavity Plugs(36)	Connector Strain Relief(6)



Insertion & Extraction Tools(1)	Power Contacts(6)	Sealing Sleeves(2)

# Customers Also Bought





Circular Power Connectors, Housing, 600 VDC, Wire-to-Wire, 9 Position, Wire & Cable, Receptacle, Pin, Power & Signal, Black, All Plastic, AMP CPC



## Documents

CAD Files 3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_206705-2\_AL.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_206705-2\_AL.3d\_igs.zip

English

Customer View Model ENG\_CVM\_CVM\_206705-2\_AL.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages AMP Circular Connectors for Commercial Signal & Power Applications

English

Product Specifications Application Specification

English

Product Environmental Compliance

Product Compliance Document

English

Product Compliance Document

English

Instruction Sheets Instruction Sheet (U.S.)

English

Agency Approvals UL Report

English