




## Power supply connectors




Power supply chassis socket, straight version, with break contact and solder eyes, for front side mounting



## NEB/J 21 C 16








S

B

0

-0.15

# 12.8 11.8



### \*a port in mounting plate

## **Environmental conditions**

Temperature range	-20 °C/+70 °C
Materials	
Insulating body	ABS, HB according to UL94
Contact	CuZn/CuSn, nickel-plated/silver- plated
Insulation	PBT GF (may be PF in a transitional phase)
Hexagonal nut	PA
Mechanical data	

Diameter opening	6.3 mm
Diameter center pin	1.95 mm
Mating cycles	5000 <sup>1</sup>
Insertion force	≤ 30 N <sup>1</sup>
Withdrawal force	3-30 N <sup>1</sup>
<sup>1</sup> measured with a gauge plug	

## Electrical data (at Tamb 20 °C)

≤ 30 mΩ
0.5 A
12 V DC
500 V/60 s
100 MΩ

## Associated products

Counterparts		
<b>⊡</b> <sup>•</sup> 1633 02	<b>1633 03</b>	🗗 NES/J 21
Image: C <sup>™</sup> NES/J 21 W	🗗 NES/J 210	🖙 XNES/J 210





Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
NEB/J 21 C	2	250	750

## Packaging:

in bulk, in a cardboard box or a plastic bag