



### Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure nominal dimensions	-
Mounting plate description	Plain
Range compatibility	Spacial (Spacial SF) Spacial (Spacial SM) Spacial (Spacial SFX) Spacial (Spacial SMX)
Device composition	1 mounting plate 2 sliding shoes
Quantity per Set	Set of 1
Material	Galvanised steel

### Complementary

Fixing mode	By fixing brackets
Maximum load	300 kg/m <sup>2</sup>
Permanent permissible load	1102.31 Lb(US) (500 kg) intermediate position 1322.77 lb(US) (600 kg) back of the enclosure
Height	Fixing centers 72.83 in (1850 mm) Nominal 78.74 in (2000 mm) Real 74.69 in (1897 mm)
Width	Fixing centers 33.46 in (850 mm) Nominal 39.37 in (1000 mm) Real 35.28 in (896 mm)
Depth	1.06 in (27 mm)

### Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606485126913
Returnability	No
Country of origin	ES

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	35.43 in (90.0 cm)
Package 1 Length	75.20 in (191.0 cm)
Package 1 Weight	83.78 lb(US) (38.0 kg)
Unit Type of Package 2	P2M
Number of Units in Package 2	20
Package 2 Height	29.92 in (76.0 cm)

Package 2 Width	78.74 in (200.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	1739.45 lb(US) (789.0 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------