



Main

Bereich	Spacial
Kategorie	Lifting accessory
Product or Component Type	Lifting bracket Lifting eye
Anwendung	Multi-purpose
Mounting Location	Enclosure top
Range compatibility	Spacial (Spacial SF) Spacial (Spacial SM)
Device composition	4 eyebolt 4 fixing nuts
Quantity per Set	Set of 1

Complementary

Material	Cast steel
Surface Finish	Galvanized
Fixing mode	Screwed
Permanent permissible load	749.57 lb(US) (340 kg) for 1 eyebolt vertical direction
Height	2.42 in (61.5 mm)
Width	2.13 in (54 mm)
Depth	1.02 in (26 mm)
Diameter	1.14 in (29 mm)
ISO thread	M12

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480146596
Returnability	Yes
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 in (6.0 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	5.71 in (14.5 cm)
Package 1 Weight	2.33 lb(US) (1.058 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	240
Package 2 Height	17.72 in (45.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	610.68 lb(US) (277.0 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------