



Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 12

BERGQUIST HI FLOW THF 1600P known as Hi-Flow 300P

SDS No. : 611566
V001.1

Revision: 22.08.2022

printing date: 03.10.2023

Replaces version from: 02.05.2019

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

BERGQUIST HI FLOW THF 1600P known as Hi-Flow 300P

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Thermal Conductive Material

1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA

Henkelstr. 67

40589 Düsseldorf

Germany

Phone: +49 211 797 0

ua-productsafety.uk@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.2. Label elements

Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

Supplemental information Safety data sheet available on request.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

Following substances are present in a concentration $\geq 0,1\%$ and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in concentration \geq the concentration limit that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No. EC Number REACH-Reg No.	Concentration	Classification	Specific Conc. Limits, M-factors and ATEs	Add. Information
diboron trioxide 1303-86-2 215-125-8 01-2119486655-24	0,1- < 0,3 %	Repr. 1B, H360FD		SVHC

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

water, carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO₂) can be released.

In case of fire, keep containers cool with water spray.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid contact with skin and eyes.
Wear protective equipment.
Ensure adequate ventilation.
Remove sources of ignition.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Scrape up as much material as possible.
Sweep up spilled material. Avoid creating dust.
Store in a partly filled, closed container until disposal.
Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Avoid skin and eye contact.
See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed.
Wash hands before work breaks and after finishing work.
Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Ensure good ventilation/extraction.
Keep container tightly sealed.
Refer to Technical Data Sheet

7.3. Specific end use(s)

Thermal Conductive Material

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Aluminium oxide 1344-28-1 [ALUMINIUM OXIDES, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Aluminium oxide 1344-28-1 [ALUMINIUM OXIDES, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Paraffin waxes and Hydrocarbon waxes 8002-74-2 [Paraffin wax, fume]		6	Short Term Exposure Limit (STEL):	15 minutes	EH40 WEL
Paraffin waxes and Hydrocarbon waxes 8002-74-2 [Paraffin wax, fume]		2	Time Weighted Average (TWA):		EH40 WEL
Diboron trioxide 1303-86-2 [DIBORON TRIOXIDE]		10	Time Weighted Average (TWA):		EH40 WEL
Diboron trioxide 1303-86-2 [DIBORON TRIOXIDE]		20	Short Term Exposure Limit (STEL):	15 minutes	EH40 WEL

Occupational Exposure Limits

Valid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Aluminium oxide 1344-28-1 [ALUMINIUM OXIDES]		4	Time Weighted Average (TWA):		IR_OEL
Aluminium oxide 1344-28-1 [ALUMINIUM OXIDES]		10	Time Weighted Average (TWA):		IR_OEL
Paraffin waxes and Hydrocarbon waxes 8002-74-2 [PARAFFIN WAX]		2	Time Weighted Average (TWA):		IR_OEL
Paraffin waxes and Hydrocarbon waxes 8002-74-2 [PARAFFIN WAX]		6	Short Term Exposure Limit (STEL):	15 minutes	IR_OEL
Diboron trioxide 1303-86-2 [BORON OXIDE]		10	Time Weighted Average (TWA):		IR_OEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
diboron trioxide 1303-86-2	aqua (freshwater)		2,9 mg/l				
diboron trioxide 1303-86-2	aqua (marine water)		2,9 mg/l				
diboron trioxide 1303-86-2	sewage treatment plant (STP)		10 mg/l				
diboron trioxide 1303-86-2	Soil				5,7 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
diboron trioxide 1303-86-2	Workers	inhalation	Long term exposure - systemic effects		4,66 mg/m ³	
diboron trioxide 1303-86-2	Workers	dermal	Long term exposure - systemic effects		220,6 mg/kg	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:
Ensure good ventilation/extraction.

Respiratory protection:
Ensure adequate ventilation.
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area
Filter type: A (EN 14387)

Hand protection:
Chemical-resistant protective gloves (EN 374).
Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):
nitrile rubber (NBR; ≥ 0.4 mm thickness)
Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):
nitrile rubber (NBR; ≥ 0.4 mm thickness)
This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:
Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.
Protective eye equipment should conform to EN166.

Skin protection:
Wear suitable protective clothing.
Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	solid
Delivery form	solid
Colour	green
Odor	Slight
Melting point	Not available.
Solidification temperature	Not applicable, Product is a solid.

Initial boiling point	> 200 °C (> 392 °F)
Flammability	non flammable
Explosive limits	Currently under determination
Flash point	Product is a solid.
Auto-ignition temperature	Not applicable, Product is a solid.
Decomposition temperature	Currently under determination
pH	Currently under determination
Viscosity (kinematic)	Not applicable, Product is a solid.
Solubility (qualitative)	Currently under determination
Partition coefficient: n-octanol/water	Currently under determination
Vapour pressure	Not available.
Density	Currently under determination
Relative vapour density:	Not available.
Particle characteristics	Not applicable Product is not powder.

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with oxidants, acids and lyes

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Excessive heat.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

No decomposition if used according to specifications.

SECTION 11: Toxicological information

General toxicological information:

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

1.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
diboron trioxide 1303-86-2	LD50	> 2.600 mg/kg	rat	OECD Guideline 401 (Acute Oral Toxicity)

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
diboron trioxide 1303-86-2	LD50	> 2.000 mg/kg	rabbit	not specified

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
diboron trioxide 1303-86-2	not irritating	24 h	rabbit	not specified

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
diboron trioxide 1303-86-2	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
diboron trioxide 1303-86-2	not sensitising	Buehler test	guinea pig	OECD Guideline 406 (Skin Sensitisation)

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
diboron trioxide 1303-86-2	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		not specified
diboron trioxide 1303-86-2	negative	mammalian cell gene mutation assay	with and without		not specified
diboron trioxide 1303-86-2	negative	sister chromatid exchange assay in mammalian cells	with and without		not specified
diboron trioxide 1303-86-2	negative	oral: gavage		mouse	OECD Guideline 474 (Mammalian Erythrocyte Micronucleus Test)

Carcinogenicity

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Sex	Method
diboron trioxide 1303-86-2	not carcinogenic	oral: feed	103 w daily	mouse	male/female	OECD Guideline 451 (Carcinogenicity Studies)

Reproductive toxicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
diboron trioxide 1303-86-2	NOAEL P 336 mg/kg NOAEL F1 100 mg/kg NOAEL F2 100 mg/kg	three-generation study	oral: feed	rat	not specified

STOT-single exposure:

No data available.

STOT-repeated exposure::

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
diboron trioxide 1303-86-2	NOAEL 100 mg/kg	oral: feed	2 y daily	rat	not specified

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information

General ecological information:

Do not empty into drains / surface water / ground water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
diboron trioxide 1303-86-2	LC50	513,3 mg/l	96 h	Pimephales promelas	other guideline:
diboron trioxide 1303-86-2	NOEC	41,2 mg/l	34 d	Danio rerio (reported as Brachydanio rerio)	OECD Guideline 210 (fish early lite stage toxicity test)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
diboron trioxide 1303-86-2	EC50	586,04 mg/l	48 h	Ceriodaphnia dubia	other guideline:

Chronic toxicity to aquatic invertebrates

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
diboron trioxide 1303-86-2	NOEC	69,6 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
diboron trioxide 1303-86-2	EC50	337,5 mg/l	72 h	Pseudokirchneriella subcapitata (reported as Raphidocelis subcapitata)	OECD Guideline 201 (Alga, Growth Inhibition Test)
diboron trioxide 1303-86-2	EC10	225,4 mg/l	72 h	Pseudokirchneriella subcapitata (reported as Raphidocelis subcapitata)	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

No data available.

12.2. Persistence and degradability

The product is not biodegradable.

No substance data available.

12.3. Bioaccumulative potential

No data available.

No substance data available.

12.4. Mobility in soil

Cured adhesives are immobile.

No substance data available.

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
diboron trioxide 1303-86-2	According to Annex XIII of regulation (EC) 1907/2006 a PBT and vPvB assessment shall not be conducted for inorganic substances.

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Do not empty into drains / surface water / ground water.

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09* waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information

- 14.1. UN number**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packing group**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Maritime transport in bulk according to IMO instruments**
not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009):	Not applicable
Prior Informed Consent (PIC) (Regulation (EU) No 649/2012):	Not applicable
Persistent organic pollutants (Regulation (EU) 2019/1021):	Not applicable
VOC content (2010/75/EC)	< 5 %

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H360FD May damage fertility. May damage the unborn child.

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2:	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.