US Office: Tel: 800.648.2800 or +1.847.671.6690 UK Office: Tel: (+44) 1543 459 555 www.mobilemark.com





This multiband Stud mount antenna integrates several broadband/ data networks with GPS. The antenna operates on 2.4 WiFi, 5 GHz WiFi, and GPS. The antenna will also operate on 2.4 Video Surveillance, and 4.9 GHz for Public Safety Broadband. The antenna is excellent for any application needing a secure and stealthy antenna.

The design uses a 5/8" feed thru (1.6 cm) for securing to the vehicle. Access to the underside of the body surface is required to complete the installation. The GPS feed of the antennas are outfitted with 15 feet (4.5 m) of RG-174 cable & SMB or SMA connectors. All connectors are male (plugs). The broadband cable is 15 feet of Low Loss-195 cable (4.5 m).

GPS performance is 26 dB, with 5 dBi antenna gain. The GPS circuit has a low noise figure (2.0 dB max) with excellent filter characteristics. Power for the GPS amplifier (2.7-5 VDC) and signal is applied through the same cabling directly to the GPS circuit.

The dome portion of the antenna measures  $2.85^{"}$  D x  $1.45^{"}$  H total (7.2 cm x 3.7 cm). It is made of weatherproof ASA Resin, which is a strong, durable outdoor material with UV stable properties. The antenna is supplied with a weatherseal gasket for the underside and mounting nut.

## Surface Mount Multi-band 2.4, 4.9-6 GHz & GPS

- Stud mounts easily to roof, trunk or bulkhead
- High performance GPS with 26 dB active amplifier
- Operates 2.4/5 GHz & 4.9 Public Safety Bands

Model Configurator					
DM-W15 Cable/Connector 1 Cable/Connector 2					
Color — Cable Length in Inches (eg. 12 or 180)					

Example: DM-W15-3A2C-WHT-180

Also available as a Mag-mount. Mag-mount option: MGD-W15-3A2C-WHT-180

Cable Options:		<u>Connec</u>	tor Options:	Color Options:	
<u>Code</u>	Cable	<u>Code</u>	Connector	Code	<u>Color</u>
1	RG-58	Α	TNC	WHT	White
2	RG-174	В	Mini UHF	BLK	Black
3	LL-195	C	SMA		
		D	SMB		

(Other Configurations available.)

Specifications			
Frequency:	2.4/4.9-6 GHz	2.4/5 GHz	LL-195, 15 ft (4.5 m)
		,	, , ,
Gain:	2.5 dBi	Surface mount Case:	2.85″D x 1.45″H
			(7.2 cm x 3.7 cm)
GPS	1575 MHz	Mag-mount Case:	3.75" D x 1.9"H
GPS Gain:	26 dB LNA		(9.5 cm x 4.6 cm)
	5 dBi nominal RHCP Antenna	Case Material:	White or black ASA
VSWR:	2:1 max over range	Stud Mounting:	5/8" dia x 3/4" long
Noise Figure:	2.0 dB max, 1.7 dB typical	Stad Mounting.	(1.6  cm x  1.9  cm)
Ū.	-40° to +80° C		for 3/8" thick
Operating Temp:			
Nominal Impedance:	50 Ohm		(9.5 mm) metal
Maximum Power:	10 Watts	Hardware:	Locknut and gasket included
Amplifier Bias:	2.7 to 5 VDC	Connector:	See above, others available
Current:	20 mA max, 10 mA typical	Shock & Vibration:	EN 61373, IEEE 1478,
Cable:	<i>"</i>		MIL-810G, TIA-329.2-C
GPS	RG-174, 15 ft (4.5 m)	Water Ingress:	IPx7
		0	