
Remote Transceiver Type G 8840 5549





- Small-sized transceiver
- Output load: 8 A/63 VAC
- Powered via Dupline®
- Address coding by GAP 1605
- 3 contact inputs
- 1 tamper channel

Product Description

The Dupline® decentralised transceiver has a built-in SPDT relay for control of a load of up to 8 A/63 VAC. The module is especially designed for applications requiring a flexible, decentralised instal-

lation with a separate power and signal (control) bus. The compact size of the module makes it fit in small enclosures.

G 8840 5549

| Type: Dupline® | | |
|------------------------------|-----|--|
| Housing | | |
| Transceiver — | | |
| No. of channels/in- and outp | uts | |
| Output type — | | |

Type Selection

Ordering no.

G 8840 5549

Output Specifications

| μ (micro gap) |
|---------------------------------|
| 8 A/63 VAC |
| 8 A/24 VDC |
| 0,8 A/63 VDC |
| > 2x10 ⁶ operations |
| > 1x10 ⁶ operations/ |
| 24 VDC 2A |
| > 1x10 ⁵ operations/ |
| / IXTO Operations/ |
| 24 VDC 8A |
| |
| 24 VDC 8Å |
| |

Supply Specifications

| Supplied by Dupline® Normal consumption Charge consumption | ≤ 1.6 mA ≤ 3.1 mA (for max 1 s after |
|--|--|
| Power-on delay Power-off delay | relay state change) Typ. 2 s ≤ 1 s |
| | |
| | |

Input Specifications

Inputs

Open loop voltage Short-circuit current Operating time for signal "1" Operating time for signal "0" Contact resistance Cable length Dielectric Voltage Inputs - Dupline® Inputs - Output

Dupline® - Output

3 contacts + one tamper channel (I/O 5-8) 2 to 3 VDC 25 μ A \leq 1 pulse train + 10 ms \leq 1 pulse train + 110 ms \leq 1 k Ω \leq 3 m

≥ 200 VAC (rms)

≥ 200 VAC (rms)

General Specifications

| Environment Pollution degree Operation temperature Storage temperature | 3 (IEC 60664) 0° to +50°C (32° to 122°F) -50° to +85°C (-58° to 185°F) |
|--|--|
| Humidity (non-condensing) | 20 to 80% |
| Housing Material Dimensions (h x w x d) | Noryl GFN 1, black 26 x 39 x 17 mm |



Mode of Operation

The in- and output addresses and fail polarity can be coded by means of the code programmer GAP 1605, with the GAP-THP-CAB cable. Upon loss of the Dupline® carrier, the output goes to the predefined fail polarity. The three contact inputs are located on in/out 5, 6 and 7 on the GAP 1605.

Tamper channel: If a channel is programmed on in/out 8, it will be transmitted as long as the module is connected to Dupline.

Wire Connections

Bus: White = Dupline® signal

Black = Dupline® GND

Output: Brown - Blue = Relay contact-set NC

Brown - Orange = Relay contact-set NO

Bus wires: 2 x 0.75 mm²,

250 V isolation, single core, 150 mm


Output wires: $3 \times 1.5 \text{ mm}^2$,

250 V isolation, single core, 150 mm

Input wires: 3 x 0.25 mm²,

Multi core, 150 mm

Wiring Diagram



Channel Configuration

On GAP 1605 the in/out configuration is as follows:

In/out 1: Relay output.

In/out 5: Contact input 1. Green wire.
In/out 6: Contact input 2. Yellow wire.
In/out 7: Contact input 3. Violet wire.
In/out 8: Tamper channel (built-in)

Dimensions

