


- Ultra compact 6 Watt converter in DIP-16 metal casing
- High power density of 1,6W/cm³
- 6-side shielded metal case with insulated baseplate
- Wide 4:1 input voltage range: 4.5-18, 9-36, 18-75 VDC
- High efficiency (up to 87%) for low thermal loss
- Operating temperature range -40°C to +85°C
- Meets EN 55032 class A (conducted and radiated) with a single input capacitor
- Protection against short circuit
- 3-year product warranty



The TEL 6WI is an isolated 6 Watt converters series which comes in an ultra compact DIP-16 metal package. It solidifies the new package standard in this power range with a power density of 1,6 W/cm³ which almost doubles the power density compared to 6 Watt converters in DIP-24 packages. The TEL 6WI offers a wide 4:1 input voltage range and featured a high efficiency of up to 87% which enables an operation temperature of up to +70°C at full load and up to 85°C with 60% load. With only a single input capacitor (SMD) the converters comply with conducted and radiated emission standard EN 55032 class A. Overall they feature an economical solution for space critical and cost sensitive applications in instrumentation, IT and industrial electronics.

Models

Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I _{max}	Vnom	I _{max}	
TEL 6-1211WI	4.5 - 18 VDC (12 VDC nom.)	5 VDC	1'200 mA			82 %
TEL 6-1212WI		12 VDC	500 mA			85 %
TEL 6-1213WI		15 VDC	400 mA			86 %
TEL 6-1215WI		24 VDC	250 mA			87 %
TEL 6-1222WI		+12 VDC	250 mA	-12 VDC	250 mA	85 %
TEL 6-1223WI		+15 VDC	200 mA	-15 VDC	200 mA	85 %
TEL 6-2411WI	9 - 36 VDC (24 VDC nom.)	5 VDC	1'200 mA			81 %
TEL 6-2412WI		12 VDC	500 mA			84 %
TEL 6-2413WI		15 VDC	400 mA			84 %
TEL 6-2415WI		24 VDC	250 mA			85 %
TEL 6-2422WI		+12 VDC	250 mA	-12 VDC	250 mA	85 %
TEL 6-2423WI		+15 VDC	200 mA	-15 VDC	200 mA	84 %
TEL 6-4811WI	18 - 75 VDC (48 VDC nom.)	5 VDC	1'200 mA			81 %
TEL 6-4812WI		12 VDC	500 mA			85 %
TEL 6-4813WI		15 VDC	400 mA			85 %
TEL 6-4815WI		24 VDC	250 mA			85 %
TEL 6-4822WI		+12 VDC	250 mA	-12 VDC	250 mA	86 %
TEL 6-4823WI		+15 VDC	200 mA	-15 VDC	200 mA	86 %

Input Specifications

Input Current	- At no load	12 Vin models: 12 mA typ. 24 Vin models: 10 mA typ. 48 Vin models: 10 mA typ.
	- At full load	12 Vin models: 587 mA typ. 24 Vin models: 299 mA typ. 48 Vin models: 148 mA typ.
Surge Voltage		12 Vin models: 25 VDC max. (1 s max.) 24 Vin models: 50 VDC max. (1 s max.) 48 Vin models: 100 VDC max. (1 s max.)
Under Voltage Lockout		12 Vin models: 3 VDC min. / 3.5 VDC typ. 24 Vin models: 5.5 VDC min. / 6.5 VDC typ. 48 Vin models: 12 VDC min. / 15.5 VDC typ.
Reflected Ripple Current		50 mAp-p typ.
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Pi-Type

Output Specifications

Voltage Set Accuracy		±2% max.
Regulation	- Input Variation (Vmin - Vmax)	single output models: 0.5% max. dual output models: 0.5% max. (Output 1) 1% max. (Output 2)
	- Load Variation (5 - 100%)	single output models: 1% max. dual output models: 1% max. (Output 1) 1.5% max. (Output 2)
	- Cross Regulation (25% / 100% asym. load)	dual output models: 5% max.
Ripple and Noise	- 20 MHz Bandwidth	100 mVp-p max. (w/ 1 µF MLCC 10µF Tantalum)
Capacitive Load	- single output	5 Vout models: 1'000 µF max. 12 Vout models: 470 µF max. 15 Vout models: 220 µF max. 24 Vout models: 100 µF max.
	- dual output	12 / -12 Vout models: 330 / 330 µF max. 15 / -15 Vout models: 220 / 220 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.03 %/K max.
Start-up Time		150 ms max.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		110 - 230% of Iout max. 160% typ. of Iout max.
Transient Response	- Response Deviation	5% typ. / 8% max. (25% Load Step) (5 Vout models) 3% typ. / 5% max. (25% Load Step) (other models)
	- Response Time	300 µs typ. / 500 µs max. (25% Load Step)

Safety Specifications

Safety Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Certification Documents	www.tracopower.com/overview/tel6wi (Max. 800 V transient on input side must be considered in final installation)
Pollution Degree		PD 2

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

EMC Specifications

EMI Emissions	- Conducted Emissions	External filter proposal:	EN 55032 class A (with external filter)
	- Radiated Emissions		EN 55032 class B (with external filter)
EMS Immunity	- Electrostatic Discharge	Air: Contact:	EN 55032 class A (with external filter)
	- RF Electromagnetic Field		EN 55032 class B (with external filter)
	- EFT (Burst) / Surge	External filter proposal:	(Note: Class A emissions can be met using only a single input capacitor.)
	- Conducted RF Disturbances		EN 61000-4-2, ± 8 kV, perf. criteria A
			EN 61000-4-2, ± 6 kV, perf. criteria A
			EN 61000-4-3, 20 V/m, perf. criteria A
			EN 61000-4-4, ± 2 kV, perf. criteria A
			EN 61000-4-5, ± 2 kV, perf. criteria A
			EN 61000-4-6, 10 Vrms, perf. criteria A

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +85°C
	- Case Temperature	+105°C max.
	- Storage Temperature	-55°C to +125°C
Power Derating	- High Temperature	Depending on model
Cooling System		Natural convection (20 LFM)
Switching Frequency		150 - 402 kHz (PWM, PFM) (12 Vin models)
		48 - 427 kHz (PWM, PFM) (24 Vin single models)
		36 - 320 kHz (PWM, PFM) (48 Vin single models)
		48 - 427 kHz (PWM, PFM) (24 & 48 Vin dual models)
		(Above 50% load PWM is used, below 50% load PFM is used)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	1'500 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 M Ω min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	2'200 pF typ.
Reliability	- Calculated MTBF	1'000'000 h (MIL-HDBK-217F, ground benign)
Washing Process		According to Cleaning Guideline
Environment	- Vibration	IEC 60068-2-6
	- Mechanical Shock	5 g, 3 axis, random waveform, 10-150 Hz
	- Thermal Shock	IEC 60068-2-27
		15 g, 3 axis, half sine, 11 ms
		IEC 60068-2-14
Housing Material		Alu alloy, black anodized coating
Base Material		Rynite® FR530 BK507
Potting Material		Epoxy (UL 94 V-0 rated)
Pin Material		Brass
Pin Foundation Plating		Nickel (1 - 3 μ m)
Pin Surface Plating		Gold (50 - 75 nm), glossy
Housing Type		Metal Case
Mounting Type		PCB Mount
Connection Type		THD (Through-Hole Device)
Footprint Type		DIP16
Soldering Profile		Lead-Free Wave Soldering
		265°C / 10 s max.
Weight		7.5 g

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.


Thermal Impedance	- Case to Ambient	20 K/W typ. (at Vin min.)
Environmental Compliance	- REACH Declaration	www.tracopower.com/info/reach-declaration.pdf
	- RoHS Declaration	REACH SVHC list compliant REACH Annex XVII compliant www.tracopower.com/info/rohs-declaration.pdf
	- SCIP Reference Number	Exemptions: 7a, 7c-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).) d16381e8-40dd-4d44-9951-68eaf8f4e86c

Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tel6wi

Outline Dimensions



Dimensions in mm (inch)
Pin diameter tolerances: ± 0.10 (± 0.004)
General tolerances: ± 0.50 (± 0.020)

Pinout		
Pin	Single	Dual
1	-Vin (GND)	
8	NTC	Common
9	+Vout	
10	-Vout	
16	+Vin (Vcc)	

NTC: Not to connect