

PRODUCT-DETAILS

F202 A-25/0.03 AP-R F202 A-25/0.03 AP-R Residual Current Circuit Breaker 2P A type 30 mA



General Information		
Extended Product Type	F202 A-25/0.03 AP-R	
Product ID	2CSF202401R1250	
EAN	8012542785101	
Catalog Description	F202 A-25/0.03 AP-R Residual Current Circuit Breaker 2P A type 30 m	
Long Description	The RCCBs F200 series assures protection to people and installations against fault curren to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications. This product provides the best compromise between safety and continuity in the service, thanks to the resistance to unwanted trippings.	
Гас Тисковананан		
Eco Transparency	0AVV109467A2700	
Environmental Product Declaration - EPD	9AKK108467A3700	
Environmental Product	9AKK108467A3700	
Environmental Product Declaration - EPD	9AKK108467A3700 IEC/EN 61008 UL 1053	
Environmental Product Declaration - EPD Technical	IEC/EN 61008 UL 1053	
Environmental Product Declaration - EPD Technical Standards	IEC/EN 61008	

F202 A-25/0.03 AP-R 2

Rated Insulation Voltage (U _i)	500 V		
Rated Impulse Withstand Voltage (U _{imp})	4 kV		
Input Voltage Type	AC		
Rated Current (I _n)	25 A		
Rated Residual Current	30 mA		
Rated Conditional Short-	10 kA		
Circuit Current (I _{nc})	10.000		
Rated Service Short- Circuit Breaking Capacity (I _{cs})	1 kA		
Maximum Surge Current	3 kA		
Leakage Current Type	A		
Rated Frequency (f)	50 60 Hz		
Power Loss	at Rated Operating Conditions per Pole 1 W		
Power Supply Connection	Arbitrary		
Electrical Endurance	10000 cycle		
Number of Poles	2		
Operating Characteristic	Instantaneous (APR High Immunity)		
Mounting Type	DIN-Rail		
Options Provided	None		
Accessories Available	Yes		
Connecting Capacity	Busbar 10 mm² Rigid 25 25 mm² Flexible 25 25 mm²		
Rated Cross-Section	4 - Multi-Wired 025 mm² 1 - Solid-Core 2525 mm²		
Environmental			
Ambient Temperature	-2555 °C		
Ambient Air Temperature	Operation -2555 °C		
Degree of Protection	IP2X		
Pollution Degree	2		
Resistance to Vibrations acc. to IEC 60068-2-6	0.1 mm or 1 g - 20 cycles at 51505 Hz		
Resistance to Shock acc. to IEC 60068-2-27	25g 2 shocks 13 ms		
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019		
RoHS Information	9AKK106713A5602		
REACH Declaration	9AKK108467A9482		
Environmental Information	Refer to RoHS		
SCIP	18f132b0-8f03-4611-9c59-dba03cc369bf ltaly (IT)		
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363		
Technical UL/CSA			
Maximum Operating Voltage UL/CSA	277 V AC		
01 10: 10			

Short-Circuit Current Rating (SCCR)

30 mA

F202 A-25/0.03 AP-R 3

Dimensions		
Width in Number of		
Modular Spacings		
Product Net Width	0.035 m	
Product Net Height	0.085 m	
Product Net Depth / Length	0.069 m	
Product Net Weight	0.200 kg	
Built-In Depth (t ₂)	69 mm	
Ordering		
Minimum Order Quantity	1 piece	
Package Level 1 Units	box 1 piece	
Package Level 1 Gross Weight	0.235 kg	
Customs Tariff Number	85363030	
E-Number (Finland)	3259656	
E-Number (Sweden)	2160175	
Country of Origin	Italy (IT)	
Declaration of Conformity - CE	9AKK106713A5602	
Popular Downloads		
Data Sheet, Technical	9AKK107991A8329	
Information		
Instructions and Manuals	9AKK107991A6127	
Classifications		
ETIM 8	EC000003 - Residual current circuit breaker (RCCB)	
ETIM 9	EC000003 - Residual current circuit breaker (RCCB)	
EPLAN Catalog Tree	Electrical engineering / Protection devices / Ground fault current circuit breaker	
EPLAN Function Definition	Ground fault current circuit-breaker / Ground fault current circuit breakers, 4 connection points / Ground fault current circuit breaker, two-pole 1/2 2/1 3/4 4/3	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)	
WEEE B2C / B2B	Business To Consumer	
CN8	85363030	
UNSPSC	39121601	
eClass IDEA Granular Category Code (ICCC)	V11.0 : 27142201 4875 >> Residual current circuit breaker (RCCB)	
Code (IGCC) Object Classification Code	F	
Supplies of the control of the contr		

Accessories

F202 A-25/0.03 AP-R 4

Unit Of Measure	Quantity	Туре	Description	Identifier
piece	2	S2C-H6R	S2C-H6R Auxiliary Contact	2CDS200912R0001
piece	2	S2C-S/H6R	S2C-S/H6R Signal / Auxiliary Contact	2CDS200922R0001
piece	1	S2C-H6-11R	S2C-H6-11R Auxiliary Contact	2CDS200946R0001
piece	1	S2C-H6-02R	S2C-H6-02R Auxiliary Contact	2CDS200946R0003
piece	1	S2C-H6-20R	S2C-H6-20R Auxiliary Contact	2CDS200946R0002
piece	1	F2C-A1	F2C-A1 Shunt trip	2CSS200933R0011
piece	1	F2C-A2	F2C-A2 Shunt trip	2CSS200933R0012
piece	1	S2C-UA 230 AC	S2C-UA 230 AC Undervoltage release	2CSS200911R0005
piece	1	S2C-UA 24 DC Undervoltage release S2C-UA 24 DC		2CSS200911R0007
piece	1	S2C-UA 24 AC Undervoltage release S2C-UA 24 AC		2CSS200911R0002
piece	1	0911R0008 S2C-UA 48 DC Undervoltage release S2C-UA 48 DC		2CSS200911R0008
piece	1	S2C-UA 110 AC	S2C-UA 110 AC Undervoltage release	2CSS200911R0004
piece	1	S2C-UA 400 AC	S2C-UA 400 AC Undervoltage release	2CSS200911R0006
piece	1	S2C-UA 12 DC Undervoltage release S2C-UA 12 DC		2CSS200911R0001
piece	1	S2C-UA 230 DC	S2C-UA 230 DC Undervoltage release	2CSS200911R0010
piece	1	S2C-UA 110 DC	S2C-UA 110 DC Undervoltage release	2CSS200911R0009
piece	1	S2C-UA 48 AC Undervoltage release S2C-UA 48 AC		2CSS200911R0003
piece	1	S2C-OVP1	S2C-OVP1 Overvoltage release	2CSS200910R0005
piece	1	S2C-OVP2	S2C-OVP2 Overvoltage release	2CSS200993R0005
piece	1	F2C-CM	F2C-CM Motor operating device	2CSF200997R0013
piece	1	F2C-ARI	F2C-ARI Auto-reclosing unit	2CSF200996R0013
piece	1	F2C-ARI30	F2C-ARI30 Auto-reclosing unit	2CSF200995R0013
piece	1	F2C-ARH	F2C-ARH Auto-reclosing unit	2CSF200992R0005
piece	1	F2C-ARH -T	F2C-ARH -T Auto-reclosing unit with autotest	2CSF200991R0005

Categories

 $Low\ Voltage\ Products\ and\ Systems \to Modular\ DIN\ Rail\ Products \to Residual\ Current\ Devices\ RCDs \to Residual\ Current\ Devices\ RCDs$





