



Ratchet P-Clamp

The Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The robust design and durable materials make it ideal for heavy duty applications, both in- and outdoors. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This nondestructive release allows the clamp to be reused without removing or replacing any bolts or screws. The Ratchet P-Clamp is offered in four sizes and multiple mounting configurations.

Features and benefits

- One-piece ratchet closure design allows for easy installation during pre- or final assembly
- Multiple configurations handle a wide range of diameters and applications, reducing part inventory
- Clamp interior is designed to guide and center bundle to reduce pinching
- Easy release feature allows for quick adjustments and maintenance
- Impact modified, heat and UV stabilized PA66 provides long-term durability, in- and outdoors
- Steel mounting plate tolerates high torque mounting and is treated to resist chemicals and salt spray

Multiple configurations

The wiring schemes in heavy duty applications become more complex day after day. Using a single mounting point, you can combine Ratchet P-Clamps to match the number, position and diameters of the wires or bundles inherent to today's wire management challenges. You will see



Ratchet P-Clamp - A more versatile way to mount and clamp cables.




www.HellermannTyton.co.uk/PClamp-cat22




**Material specification
please see page 26.**


below just a few of the nearly endless number of configurations you can arrange by mixing Ratchet P-Clamps of varying sizes and different mounting plates.




You can piggy-back Ratchet P-Clamps by using different length mounting plates to secure parallel cable configurations.



Ratchet P-Clamp mounting plates are shaped to allow face-to-face positioning. By using different length mounting plates, you can vary the distance between bundles and take advantage of the optimal routing path.



Add a spacer between Ratchet P-Clamps to speed installation and maintenance of stacked wire bundles.



90° angle mounting plates enable you to work around obstacles and protect wire from contacting moving parts.



Ratchet P-Clamp

For bundle diameters from 6.2 mm to 13.7 mm, A-Series

TYPE	Drawing	Width (W)	Length (L2)	Bundle Ø min.	Bundle Ø max.	Hole Ø (FH)	Fixing Hole Centres (F)	Variant	Material	Colour	Article-No.
RCA180LM6		34.9	134.1	6.2	13.7	6.5	101.5	Long	PA66HIRHSUV, ST, ZN	Black (BK)	151-01639
RCA180MM6		34.9	105.1	6.2	13.7	6.5	72.5	Medium	PA66HIRHSUV, ST, ZN	Black (BK)	151-01638
RCA180SM6		34.9	83.1	6.2	13.7	6.5	50.5	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01637
RCA180SM8		34.9	83.1	6.2	13.7	8.31	50.5	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01416
RCA90LM6		34.9	96.8	6.2	13.7	6.5	24.9	Long	PA66HIRHSUV, ST, ZN	Black (BK)	151-01644
RCA90LM8		34.9	96.8	6.2	13.7	8.31	24.9	Long	PA66HIRHSUV, ST, ZN	Black (BK)	151-01437
RCA90SM6		34.9	68.8	6.2	13.7	6.5	24.9	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01643

All dimensions in mm. Subject to technical changes.

For bundle diameters from 12.7 mm to 19.5 mm, B-Series

TYPE	Drawing	Width (W)	Length (L2)	Bundle Ø min.	Bundle Ø max.	Hole Ø (FH)	Fixing Hole Centres (F)	Variant	Material	Colour	Article-No.
RCB180LM6		34.9	134.1	12.7	19.5	6.5	103.8	Long	PA66HIRHSUV, ST, ZN	Black (BK)	151-01647
RCB180SM6		34.9	83.1	12.7	19.5	6.5	52.8	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01645
RCB180SM8		34.9	83.1	12.7	19.5	8.31	52.8	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01440
RCB180SM10		34.9	83.1	12.7	19.5	10.29	52.8	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01390
RCB180SM12		34.9	83.1	12.7	19.5	12.95	52.8	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01441
RCB90LM6		34.9	96.8	12.7	19.5	6.5	26.7	Long	PA66HIRHSUV, ST, ZN	Black (BK)	151-01652
RCB90LM8		34.9	96.8	12.7	19.5	8.31	26.7	Long	PA66HIRHSUV, ST, ZN	Black (BK)	151-01460
RCB90SM6		34.9	68.8	12.7	19.5	6.5	26.7	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01651
RCB90SM8		34.9	68.8	12.7	19.5	8.31	26.7	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01457

All dimensions in mm. Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.



Add items to your watchlist!

www.HT.click/49-185



Ratchet P-Clamp

For bundle diameters from 19.4 mm to 36.0 mm, C-Series

TYPE	Drawing	Width (W)	Length (L2)	Bundle Ø min.	Bundle Ø max.	Hole Ø (FH)	Fixing Hole Centres (F)	Variant	Material	Colour	Article-No.
RCC180LM6		34.9	154.0	19.4	36.0	6.5	113.3	Long	PA66HIRHSUV, ST, ZN	Black (BK)	151-01655
RCC180SM6		34.9	103.0	19.4	36.0	6.5	62.3	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01653
RCC180SM8		34.9	103.0	19.4	36.0	8.31	62.3	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01474
RCC90LM6		34.9	129.2	19.4	36.0	6.5	39.9	Long	PA66HIRHSUV, ST, ZN	Black (BK)	151-01660
RCC90LM8		34.9	129.2	19.4	36.0	8.31	39.9	Long	PA66HIRHSUV, ST, ZN	Black (BK)	151-01495
RCC90SM6		34.9	101.2	19.4	36.0	6.5	39.9	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01659
RCC90SM8		34.9	101.2	19.4	36.0	8.31	39.9	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01492

All dimensions in mm. Subject to technical changes.

Material specification
please see page 26.

For bundle diameters from 36.0 mm to 51.0 mm, D-Series

TYPE	Drawing	Width (W)	Length (L2)	Bundle Ø min.	Bundle Ø max.	Hole Ø (FH)	Fixing Hole Centres (F)	Variant	Material	Colour	Article-No.
RCD180SM8		34.9	115.5	36.0	51.0	8.31	70.0	Short	PA66HIRHSUV, ST, ZN	Black (BK)	151-01499
RCD90LM8		34.9	116.7	36.0	51.0	8.31	42.4	Long	PA66HIRHSUV, ST, ZN	Black (BK)	151-01521

All dimensions in mm. Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.



Material Specification Overview

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Aluminium alloy	AL	-40 °C to +180 °C	Natural (NA)		<ul style="list-style-type: none"> Corrosion resistant Antimagnetic 	RoHS
Chloroprene rubber	CR	-20 °C to +80 °C	Black (BK)		<ul style="list-style-type: none"> Weather resistant High yield strength 	RoHS
Ethylene Tetrafluoroethylene (Tefzel®)	E/TFE	-80 °C to +170 °C	Blue (BU)	UL 94 V0	<ul style="list-style-type: none"> Resistance to radioactivity UV resistant, not moisture sensitive Good chemical resistance to acids, bases, oxidizing agents 	RoHS
Polyacetal	POM	-40 °C to +90 °C, (+110 °C, 500 h)	Natural (NA)	UL 94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Flexible at low temperature Not moisture sensitive Robust on impact 	RoHS
Polyamide 11	PA11	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	<ul style="list-style-type: none"> Bio-plastic, derived from vegetable oil Strong impact resistance at low temperature Very low moisture absorption Weather resistant Good chemical resistance 	HF RoHS
Polyamide 12	PA12	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	<ul style="list-style-type: none"> Good chemical resistance to acids, bases, oxidizing agents UV resistant 	HF RoHS
Polyamide 4.6	PA46	-40 °C to +130 °C, (+150 °C, 5000 h; +195 °C, 500 h)	Natural (NA), Grey (GY)	UL 94 V2	<ul style="list-style-type: none"> Resistance to high temperatures Very moisture sensitive Low smoke sensitivity 	HF LFH RoHS
Polyamide 6	PA6	-40 °C to +80 °C	Black (BK)	UL 94 V2	<ul style="list-style-type: none"> High yield strength 	RoHS
Polyamide 6, high impact modified	PA6HIR	-40 °C to +80 °C	Black (BK)	UL 94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Higher flexibility at low temperature 	RoHS
Polyamide 6.6	PA66	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK), Natural (NA)	UL 94 V2	<ul style="list-style-type: none"> High yield strength 	HF RoHS
Polyamide 6.6, glass-fibre reinforced	PA66GF13	-40 °C to +105 °C, (+105 °C for 500 h)	Black (BK)	UL 94 HB	<ul style="list-style-type: none"> Good resistance to lubricants, fuels, salt water and solvents 	HF RoHS
Polyamide 6.6, heat and UV-stabilised	PA66HSUV	-40 °C to +105 °C, (+105 °C for 500 h)	Black (BK)	UL 94 V2	<ul style="list-style-type: none"> High yield strength Modified elevated maximum temperature UV resistant 	HF RoHS
Polyamide 6.6, heat stabilised	PA66HS	-40 °C to +105 °C, (+105 °C for 500 h)	Black (BK), Natural (NA)	UL 94 V2	<ul style="list-style-type: none"> High yield strength Modified elevated maximum temperature 	HF RoHS
Polyamide 6.6, high impact modified	PA66HIR	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Higher flexibility at low temperature 	RoHS
Polyamide 6.6, high impact modified, heat and UV-stabilised	PA66HIRHSUV	-40 °C to +110 °C	Black (BK)	UL 94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Higher flexibility at low temperature Modified elevated maximum temperature High yield strength, UV resistant 	RoHS
Polyamide 6.6, high impact modified, heat stabilised	PA66HIRHS	-40 °C to +105 °C, (+105 °C for 500 h)	Black (BK)	UL 94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Higher flexibility at low temperature Modified elevated maximum temperature 	RoHS
Polyamide 6.6, high impact modified, scan black	PA66HIR(S)	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Higher flexibility at low temperature 	RoHS
Polyamide 6.6, UV-resistant	PA66W	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 V2	<ul style="list-style-type: none"> High yield strength UV resistant 	HF RoHS
Polyamide 6.6, with metal particles	PA66MP	-40 °C to +85 °C, (+105 °C, 500 h)	Blue (BU)	UL 94 HB	<ul style="list-style-type: none"> High yield strength Metal and X-Ray detectable 	HF RoHS
Polyamide 6.6, with metal particles	PA66MP+	-40 °C to +85 °C	Blue (BU)	not flame-retardant	<ul style="list-style-type: none"> High yield strength Metal and X-Ray detectable 	HF RoHS

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Polyamide 6.6 V0	PA66V0	-40 °C to +85 °C	White (WH)	UL 94 V0	<ul style="list-style-type: none"> High yield strength Low smoke emission 	HF LFH RoHS
Polyester	SP	-50 °C to +150 °C	Black (BK)		<ul style="list-style-type: none"> UV resistant Good chemical resistance to most acids, bases and oils 	HF LFH RoHS
Polyetheretherketone	PEEK	-55 °C to +240 °C	Beige (BGE)	UL 94 V0	<ul style="list-style-type: none"> Resistance to radioactivity Not moisture sensitive Good chemical resistance to acids, bases, oxidising agents 	HF LFH RoHS
Polyethylene	PE	-40 °C to +50 °C	Black (BK), Grey (GY)	UL 94 HB	<ul style="list-style-type: none"> Low moisture absorption Good chemical resistance to most acids, bases, alcohol, oils 	HF RoHS
Polyolefin	PO	-40 °C to +90 °C	Black (BK)	UL 94 V0	<ul style="list-style-type: none"> Low smoke emissions 	HF LFH RoHS
Polypropylene	PP	-40 °C to +115 °C	Black (BK), Natural (NA)	UL 94 HB	<ul style="list-style-type: none"> Floats in water Moderate yield strength Good chemical resistance to acids, bases and solvents 	HF RoHS
Polypropylene, Ethylene Propylene Diene Terpolymer rubber free of Nitrosamine	PP, EPDM	-20 °C to +95 °C	Black (BK)	UL 94 HB	<ul style="list-style-type: none"> Good resistance to high temperature Good chemical and abrasion resistance 	HF RoHS
Polypropylene with metal particles	PPMP	-40 °C to +115 °C	Blue (BU)	UL 94 HB	<ul style="list-style-type: none"> Metal and X-Ray detectable Heat resistant Moderate yield strength Good chemical resistance 	RoHS
Polypropylene with metal particles	PPMP+	-40 °C to +85 °C	Blue (BU)	not flame-retardant	<ul style="list-style-type: none"> High yield strength Metal and X-Ray detectable 	HF RoHS
Polyvinylchloride	PVC	-10 °C to +70 °C	Black (BK), Natural (NA)	UL 94 V0	<ul style="list-style-type: none"> Low moisture absorption Good chemical resistance to acids, bases, salts, alcohol, oils 	RoHS
Stainless Steel	SS304, SS316	-80 °C to +538 °C	Natural (NA)	Non burning	<ul style="list-style-type: none"> Corrosion resistant Antimagnetic Weather resistant Chemical resistance SS316 also resistant against seawater, salt spray and anorganic acids 	HF LFH RoHS
Thermoplastic Polyurethane	TPU	-40 °C to +85 °C	Black (BK)	UL 94 HB	<ul style="list-style-type: none"> High elasticity Good chemical resistance to: acids, bases and oxidizing agents 	HF RoHS

Tefzel® is a registered trademark of DuPont. General linguistic usage for cable ties made from raw material E/TFE is Tefzel®-Tie. In addition to Tefzel® from DuPont HellermannTyton also uses equivalent E/TFE raw material from other suppliers.

**Further colours available on request.

*These details are only guide values. They should not be regarded as a exhaustive material specification and are no substitute for suitability tests. Please see our datasheets for further details.

HF = Halogen Free

LFH = Limited Fire Hazard

RoHS = Restriction of Hazardous Substances

 = Minimum Loop Tensile Strength for Cable Ties (newton)