

Stainless Steel Printing System

M-BOSS Compact Markers

M-BOSS Compact Markers are used in all areas where severe mechanical or chemical conditions occur e.g. offshore industry, marine engineering, petrochemical industry, mining, underground or on radio and cellular masts where mark permanence is critical.

The raised surface of the embossed print ensures that the text remains visible even with dirt, grease, and paint cover the marker. The physical characteristics of the metal and the height of the embossed mark allows users to apply a stiff or metallic brush to the surface and remove excess layers of paint or grease without damaging the integrity of the text.

Features and benefits

- Raised marking ensure text visibility even when covered in dust, debris, grease and oil
- Stainless steel grade SS316 is suited for use in harsh environments
- Marker plates are designed for use with stainless steel cable ties with a 4.6 mm strap width
- Apply ties with a MK9SST



Identification for hazardous environments: M-BOSS Compact stainless steel markers.




www.HellermannTyton.co.uk/M-BOSS-cat22




A range of metal plate sizes to suit your needs.

MATERIAL	Stainless Steel (SS316)
Operating Temperature	-80 °C to +538 °C



MBML



TYPE	Strap Width max. (G)	Number of lines	Characters per line	Number of characters	Width (W)	Length (L)	Pack Cont.	Article-No.
MBML10X45	4.6	1	8	8	10.0	44.5	1,000 pcs.	544-80101
MBML10X90	4.6	1	23	23	10.0	89.5	500 pcs.	544-80102
MBML20X45	4.6	3	8	24	20.0	44.5	1,000 pcs.	544-80201
MBML20X90	4.6	3	23	69	20.0	89.5	500 pcs.	544-80202

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

