


PRODUCT DATA SHEET

PL12SL Series (Bi-colour)
 Ø12mm stainless steel panel lights


Product Configuration



Example Part Number

PL12SL023 Panel indicator 12mm diameter, stainless steel bezel, lead wire terminated, flat lens, Green, 24V.

Outline Dimensions (mm) - Not to scale



Colour	Typ. Wavelength (nm)		Viewing Angle (°)		Typ. Luminous Intensity (mcd)	
	Rnd	Flat	Rnd	Flat	Rnd	Flat
Red	623	625	15	25	350	3500
Green	518	520	15	25	1000	6500

Notes:

- 1 **Optical Data** Applies to component LED @ 25°C, 20mA
- 2 **Body Material** Bezel - Stainless Steel 304, Housing – PA6
- 9 **Wire Gauge** 28 AWG
- 3 **LED Life (Average)** 50000 Hrs
- 4 **Operating Current** AC/DC
- 5 **Current Rating** ≤ 20mA
- 6 **Protection** IP67
- 7 **Environmental** RoHS & REACH SVHC compliant
- 8 **Marking** Voltage, colour, CE/UKCA (110V, 240V only)
- 9 **Operating Temp** -25°C~+65°C