



Wi-Fi 6E Tri-Band Omni Array Antenna 2.4-2.484, 4.9-7.125 GHz

The OCX24688-FNM is a 2.4-2.484 / 4.9-7.125 GHz tri-band omnidirectional array antenna especially designed to complement interior or exterior mounted Wi-Fi 6E wireless network systems.

The integrated male N-connector is embedded in the antenna base cap for direct AP mounting. Sealing permits either upright or inverted orientation in outdoor locations. The antenna may also be pole-mounted when separation from the AP is required for optimal positioning.

FEATURES AND BENEFITS

- Tri-Band Wi-Fi coverage including legacy Wi-Fi, Wi-Fi 6, Wi-Fi 6E and Wi-Fi 7
- High performance beam pattern with optimized sidelobe suppression for maximized coverage in target area
- IP67 outdoor rated
- Direct mounting to access points or pole/mast mountable
- Suitable for upright or inverted orientation in both indoor and outdoor locations

APPLICATIONS

- WLAN
- Wi-Fi Wi-Fi 7 (802.11be), Wi-Fi 6E (802.11ax), Wi-Fi 6 (802.11ax), Wi-Fi 5 (802.11ac), Wi-Fi 4 (802.11n), 802.11b/g
- Automation and control
- Outdoor and indoor rated


ELECTRICAL SPECIFICATION							
Operating Frequency (MHz)	2400-2484	4900-4990	5170-5330	5490-7125			
VSWR - Average	<2.5:1	<2.2:1	<2.0:1	<2.0:1			
Peak Gain - Max (dBi)	5.0	5.5	6.7	7			
Average Gain, Near Horizon (dBi)	3.5 ± 0.5	5.0 ± 1.0	5.0 ± 1.0	5.5 ± 1.0			
Average 3 dB Beamwidth (°)	37	23	22	20			
Input Max Power (W)	2						
Polarization	Linear, Vertical						
Azimuth Beamwidth (All Models)	360°, Omnidirectional						
Nominal Impedance (Ohms)	50						

MECHANICAL SPECIFICATION				
Dimensions - height x circumference - mm (in.)	287 x 32Ø (11.3 x 1.26)			
Weight - g (lbs.)	137 (0.3)			
Radome	Polycarbonate, UV (White)			
Cap and Base	ASA, UV			

ENVIRONMENTAL SPECIFICATION				
Operating Temperature – °C (°F)	-40 to +70°C (-40 to +158°F)			
Storage Temperature - °C (°F)	-40 to +85°C (-40 to +185°F)			
Ingress Protection (IP Rating)	IP67			
Material Substance Compliance	RoHS Compliant CE & UKCA			
Wind Loading (mph)	165			

MECHANICAL DRAWINGS






RADIATION PATTERNS


Radiation Patterns at 2.4 - 2.484 GHz


Azimuth Plane

Phi 0° Plane

Phi 90° Plane









Radiation Patterns at 4.9 - 4.99 GHz


Azimuth Plane

Phi 0° Plane

Phi 90° Plane









Radiation Patterns at 5.17 - 5.33 GHz


Azimuth Plane

Phi 0° Plane

Phi 90° Plane









Radiation Patterns at 5.49 - 5.9 GHz


Azimuth Plane

Phi 0° Plane

Phi 90° Plane









Radiation Patterns at 6.0 - 6.4 GHz


Azimuth Plane

Phi 0° Plane

Phi 90° Plane









Radiation Patterns at 6.5 - 7.125 GHz


Azimuth Plane

Phi 0° Plane

Phi 90° Plane









Radiation Patterns at 7.0 - 7.125 GHz


Azimuth Plane




Phi 0° Plane





Phi 90° Plane



PACKING INFORMATION









PACKAGED DIMENSIONS	Unit Carton	MASTER CARTON	AIR PALLET	OCEAN PALLET
Number of Antennas	1	16	768	960
Height mm(in)	305 (12)	210 (8.27)	1466 (57.24)	1791 (69.96)
Length mm(in)	45 (1.77)	355 (13.98)	1200 (47.24)	1200 (47.24)
Width mm(in)	45 (1.77)	255 (10.04)	800 (31.50)	800 (31.50)
Est. Shipping Weight kg (lbs.)	0.125 (0.28)	2.5 (5.51)	108 (238.10)	132 (291.01)

TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 +1 (905) 475-6222 Canada: Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 +44 (0) 800-267666 UK: +33 (0) 1-3420-8686 France: Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not to exceed one (1) year from the original date of the end product purchase.

©2023 TE Connectivity. All Rights Reserved.

05/23 Original

