## Non Isolated Board Mount DC / DC Converters







### **Features**

- · High efficiency up to 96%
- No-load input current as low as 0.1mA
- Operating ambient temperature range: -40°C to +85°C
- · Output short-circuit protection

### **Selection Guide**

		Input Voltage (V DC)*	Out	Output		Capacitive	
Part Number	Certification	Nominal (Range)	Voltage (V DC)	Current (mA) Max.	Typ. Vin Min. / Vin Max.	Load (µF) Max.	
MP-K7803-2000R3		24 (6-36)	3.3	2000	89/85	1800	
WP-K/603-2000K3		12 (8-31)	-3.3	1000	85/83	1000	
MD K7905 2000D2	EN/BS EN	24 (8-36)	5	2000	92/89	1000	
MP-K7805-2000R3		12 (8-30)	-5	1000	86/84	680	

Note: For input voltage exceeding 30V DC, an input electrolytic capacitor of 22µF/50V is required to prevent the module from being damaged by voltage spikes.

### **Input Specifications**

Item	Operating Conditions			Тур.	Max.	Unit
	Positive output,	1.8V/2.5V Output	-	0.2	0.5	
No-load Input Current	nominal input voltage	Others	-	0.1	1	] <sub>mA</sub>
No load input outlett	Negative output, nominal input voltage -3.3V/-5V Output		-	-	1	
Reverse Polarity at Input -			A <sup>1</sup>	void / No	ot protec	ted
Input Filter	-			Capacit	ance filte	er

### **Output Specifications**

Item	Operating Conditions			Тур.	Max.	Unit	
Voltage Acquire ov	Full load,	Full load, ±3.3V output		±2	±4		
Voltage Accuracy	Input Voltage Range	Other positive and negative output	-	±2	±3	] "	
Linear Regulation	Full load, input voltage range			±0.4	±0.8	70	
Load Regulation	10% -100% load step;	nominal input voltage	-	±0.5	±1.5		

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



## Non Isolated Board Mount DC / DC Converters



Item	Operating Conditions			Min.	Тур.	Max.	Unit
Disula 9 Mais at	Positive output, 20MHz bandwidth, nominal input voltage, 100% load			-	30	75	m\/n n
Ripple & Noise*	Negative output, 20MHz bandwidth, nominal input voltage, 100% load			-	-	150	mVp-p
Temperature Coefficient	Operating temperature -40°C to +85°C			-	-	±0.03	%/°C
	Nominal input, 25% load step (25%-50%-25%,	Positive output	1.8V, 2.5V output	-	±80	±150	_
Transient Response Deviation			Other output	-	±50	±150	
Deviation	50%-75%-50% step)	Negative output	gative output		±100	±150	
Transient Recovery Time	Nominal input, 25% load step (25%-50%-25%, 50%-75%-50% step)			-	0.2	1	ms
Short-circuit Protection	Nominal input				tinuous,	Self-red	covery

Notes: \*1. The "parallel cable" method is used for ripple and noise test, please refer to Non-isolated DC-DC Converter Application Notes for specific information;

### **General Specifications**

Item	Operating Conditions	Min.	Тур.	Max.	Unit
Operating Temperature	-	-40	1	85	
Storage Temperature	-	-55	-	125	°C
Pin Soldering Resistance Temperature	Soldering time: 10s (Max.)	-	-	260	Ü
Storage Humidity	Non-condensing	5	-	95	%RH
Switching Frequency	Full load, nominal input	-	400	-	kHz
MTBF	MIL-HDBK-217F @ 25°C	2000	-	-	k hours

### **Mechanical Specifications**

Case Material	lack plastic; flame-retardant and heat-resistant (UL94V-0)			
Dimensions	11.5mm × 9mm × 17.5mm			
Weight	3.8g (Typ.)			
Cooling Method	Free Air Convection			



<sup>\*2.</sup> Positive output: Input voltage range, 20%-100% load ripple & noise is less than 100mVp-p, 0%-20% load ripple & noise is less than 180mVp-p.

<sup>\*3.</sup> Negative output: Input voltage range, 20%-100% load ripple & noise is less than 150mVp-p, 0%-20% load ripple & noise is less than 180mVp-p.


### Non Isolated Board Mount DC / DC Converters




### **Typical Characteristic Curves**

### 1. Forced convection curve (Positive output)


# 3.3V/5V output




### 2. Free air convection curve (Positive output)




### 3. Free air convection curve (Negative output)






### **Design Reference**

### **Typical application**






Part Number	C1 (Ceramic Capacitor)	C2 (Ceramic Capacitor)	
MP-K7803-2000R3	22115/501/	22uF/10V	
MP-K7805-2000R3	22μF/50V	22μΓ/100	

#### Note:

- 1. The required C1 and C2 capacitors must be connected as close as possible to the terminals of the module;
- 2. Refer to Table 1 for C1 and C2 capacitor values;
- 3. For certain applications, increased values of C2 and/or tantalum or low ESR electrolytic capacitors may also be used instead;
- 4. Converter cannot be used for hot swap and with output in parallel.

### **EMC** compliance circuit



EMC recommended circuit

FUSE	C0	LDM1	C4	C1/C2	C3
Selected based on the actual input current in application	100µF /100V	22µH	680µF /50V	10μF /50V	22µF /25V


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro





## Non Isolated Board Mount DC / DC Converters



### **Diagram**







Note: Grid 2.54\*2.54mm

Pin-Out							
Pin Positive Output Negative Output							
1	Vin	Vin					
2	GND	-Vo					
3	+Vo	GND					

Dimensions: Millimetres (Inches)

Pin Diameter Tolerances: ±0.1mm (±0.004") General Tolerances: ±0.5mm (±0.02")

### **Part Number Table**

Description	Part Number
Non Isolated Board Mount, DC / DC Converter, 3.3V, 2A	MP-K7803-2000R3
Non Isolated Board Mount, DC / DC Converter, 5V, 2A	MP-K7805-2000R3

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

