





Features

- · High efficiency up to 96%
- No-load input current as low as 0.1mA
- Operating ambient temperature range: -40°C to +85°C
- Support the negative output
- · Output short-circuit protection

Selection Guide

Part Number	Certification	Input Voltage (V DC)*	Out	tput	Full Load	Capacitive Load (µF)	
Part Number	Certification	Nominal (Range)	Voltage (V DC)	Current (mA) Max.	Efficiency(%) Vin Min. / Vin Max.	Max.	
MP-K7805-1000R3L		24 (8-36)	5	1000	93/86	680	
WIP-R/603-1000R3L		12 (8-27)	-5	-500	86/82	330	
MP-K7809-1000R3L		24 (13-36)	9	1000	95/90	680	
MP-K7812-1000R3L	UL/EN/BS EN/IEC	24 (16-36)	12	1000	96/93	680	
WIP-R/012-1000R3L		12 (8-20)	-12	-300	89/88	330	
MP-K7815-1000R3L		24 (20-36)	15	1000	96/94	680	
WIF-R/013-1000R3L		12 (8-18)	-15	-300	89/89	330	

Note: For input voltages exceeding 30V DC, an input capacitor of 22µF/50V is required. L-suffix: Add L-suffix for horizontal mount with 90 degree angled pins

Input Specifications

Item	Operating Conditions	Min.	Тур.	Max.	Unit
No-load Input Current	Positive output	1	0.3	1	mA
Reverse Polarity at Input			Forb	idden	
Input Filter			Capacit	ance filte	er

Output Specifications

Item	Operating Conditions	Min.	Тур.	Max.	Unit
Voltage Accuracy	Full load, Input Voltage Range	-	±2	±3	
Linear Regulation	Full load, input voltage range	-	±0.2	±0.4	%
Load Regulation	Nominal input voltage, 10% -100% load	-	±0.4	±0.6	
Ripple & Noise*	20MHz bandwidth, nominal input, 20% -100% load	-	20	75	mVp-p





Item	Operating Conditions		Тур.	Max.	Unit
Temperature Coefficient	Operating ambient temperature -40°C to +85°C		-	±0.03	%/°C
Transient Response Deviation	Nominal input voltage, 25% load step change		50	300	mV
Transient Recovery Time		-	0.1	1	ms
Short-circuit Protection	Nominal input voltage	Con	tinuous,	self-rec	overy

Notes:

- *1. The "parallel cable" method is used for ripple and noise test, please refer to DC-DC Converter Application Notes for specific information;
- 2. With light loads at or below 20%, the maximum Ripple and Noise for 3.3/5V output parts increase to 100mVp-p and for 9/12/15V output parts increase to 2%Vo Max.


General Specifications

Item	Operating Conditions			Тур.	Max.	Unit
Operating Temperature*	Derating if the temperature	Derating if the temperature ≥71°C		-	85	
Storage Temperature	-	'	-55	-	125] °c
Pin Soldering Resistance Temperature	Soldering time: 10 seconds	Soldering time: 10 seconds		-	260	
Storage Humidity	Non-condensing		5	-	95	%RH
Cuitobing Fraguency	100% load, input voltage	MP-K7805-1000R3L	420	520	620	kHz
Switching Frequency	range	Other output	580	680	780	KF1Z
MTBF	MIL-HDBK-217F @ 25°C		2000	-	-	k hours

Mechanical Specifications

Case Material	Black plastic; flame-retardant and heat-resistant (UL94V-0)
Dimensions	19mm × 11.5mm × 9mm
Weight	3.8g (Typ.)
Cooling Method	Free Air Convection


Typical Characteristic Curves










Typical Characteristic Curves











Design Reference


Typical application




Positive output application circuit



Negative output application circuit






Notes:

- 1. The required capacitors C1 and C2 (C3 and C4) must be connected close as possible to the terminals of the module.
- 2. Refer to Table 1 for C1 and C2 (C3 and C4) capacitor values.
- 3. For certain applications, increased values for C2 and C4 and/or tantalum or low ESR electrolytic capacitors may also be used instead .
- 4. When using configurations as shown, we recommended to add an inductor (LDM) with a value of up to 10μH which helps reducing mutual interference.
- 5. Converter cannot be used for hot swap and with output in parallel.

EMC compliance circuit










FUSE	MOV	LDM1	C0	C1/C2	C5	LDM2
Select fuse value according to actual input current	S20K30	82µH	680μF/50V	Refer to table 1	4.7μF / 50V	12µH

Diagram







Pin-Out					
Pin	Positive Output	Negative Output			
1	Vin	Vin			
2	GND	-Vo			
3	+Vo	GND			

Dimensions: Millimetres (Inches)

Pin Diameter Tolerances: ±0.1mm (±0.004") General Tolerances: ±0.5mm (±0.02")

Part Number Table

Description	Part Number
Non Isolated Board Mount, DC / DC Converters, 5V, 1A	MP-K7805-1000R3L
Non Isolated Board Mount, DC / DC Converters, 9V, 1A	MP-K7809-1000R3L
Non Isolated Board Mount, DC / DC Converters, 12V, 1A	MP-K7812-1000R3L
Non Isolated Board Mount, DC / DC Converters, 15V, 1A	MP-K7815-1000R3L

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

