

ATL-1Z090610S

Request Samples



Check Inventory ()



9.3 x 6.1 x 10.2 mm RoHS/RoHS II Compliant MSL Level = 1

Features

- Ferrite Core
- High Saturation current, up to 98A
- Minimized DC losses due to extremely low DCR
- Inductance up to 220nH
- Low interwinding capacitance
- Compact size for dense designs

Applications

- Servers and data centers
- Networking and telecommunication systems
- Industrial automation and control
- Voltage Regulator Module (VRM) for FPGAs, ASICs and microprocessors
- Point-of-Load (PoL) and Multiphase DC-DC converters

Electrical Specifications

Part Number	OCL@ 0ADC ±15%	OCL@ Isat 1 Min	Leakage Inductance Max	Interwinding Capacitance	DC Resistance ±10%		Isat1	Isat2	Isat3	Irms	
Units	nH	nH	nН	pF	m	$oldsymbol{\Omega}$	A		A		
ATL-1Z090610S	1-4/2-3	1-4	1-4	1-4/2-3	1-4	2-3	1-4			1-4	2-3
ATL-1Z090610SR10LT	100	64	10	7	0.125	0.330	98	83	78	75	40
ATL-1Z090610SR12LT	120	77					79	67	63		
ATL-1Z090610SR15LT	150	96					62	53	49		
ATL-1Z090610SR18LT	180	115					54	46	43		
ATL-1Z090610SR22LT	220	140					50	-	-		

Test Conditions:

Open Circuit Inductance (OCL)@0ADC and @Isat1: 100KHz, 1.0Vrms

Isat1: DC current at which the inductance drops 20% from its nominal value at 25°C.

Isat2: DC current at which the inductance drops 20% from its nominal value at 100°C.

Isat3: DC current at which the inductance drops 20% from its nominal value at 125°C.

Irms: DC current that causes the temperature rise (ΔT, approximate 40 °C) from 25°C ambient.

Max Operating Voltage: 80V

Core to windings breakdown Voltage: 200V

Operating Temperature: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$ (including self-temperature rise)

Storage Condition: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$ (on board), $-10^{\circ}\text{C} \sim +40^{\circ}\text{C}$ (with packaging) and R.H. 60 max.

ATL-1Z090610S Series is RoHS Compliant and Pb free.





ATL-1Z090610S

Request Samples





Check Inventory (>)



9.3 x 6.1 x 10.2 mm **RoHS/RoHS II Compliant** MSL Level = 1

Electrical Specifications (Cont'd)





 $\Delta B(Gauss) = 0.42 * L(nH) * \Delta I(Amps)$





ATL-1Z090610S

Request Samples (>)




Check Inventory (>)




9.3 x 6.1 x 10.2 mm **RoHS/RoHS II Compliant** MSL Level = 1

Part Identification



*Only part numbers listed in the Electrical Specs table are available. For custom builds, please contact Abracon.

Schematic







ATL-1Z090610S

Request Samples (>)





Check Inventory (>)




9.3 x 6.1 x 10.2 mm **RoHS/RoHS II Compliant** MSL Level = 1


Mechanical Specifications







Recommended Land Pattern



Dimensions: Inches[mm]



REVISION: IR 09-21-23

ABRACON IS ISO9001-2015 CERTIFIED



ATL-1Z090610S

Request Samples (>)




Check Inventory (>)



9.3 x 6.1 x 10.2 mm **RoHS/RoHS II Compliant** MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times			
1	Preheat	$\begin{split} T_{SMIN} \sim T_{SMAX} \\ 150^{\circ}C \sim 200^{\circ}C \end{split}$	$60 \sim 120 \text{ sec.}$			
2	Reflow	T _L 217°C	$60 \sim 150 \text{ sec.}$			
3	Peak Temperature	Tc 260°C	5 sec. max			

Max. ramp up rate: 3°C/sec. Max. ramp down rate: 6°C/sec.

Time from 25°C to peak Temperature: 8mins max.

Ref. Solder paste: Sn/3.0Ag/0.5Cu





ATL-1Z090610S

Request Samples




Check Inventory (>)




9.3 x 6.1 x 10.2 mm RoHS/RoHS II Compliant MSL Level = 1

Packaging

Tape & Reel: 500 pcs/reel



Series	W	E	F	P0	P1	D0	A0	B0	T	K0
ATL-1Z090610S	24.00	1.75	11.50	4.00	2.00	1.50	6.60	9.80	0.50	10.70
	±0.30	± 0.10	± 0.10	± 0.10	±0.10	± 0.10	±0.30	± 0.30	± 0.05	±0.30



Dimensions: mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

