


## Data sheet | Item number: 2002-1891

End and intermediate plate; 1 mm thick; gray

[www.wago.com/2002-1891](http://www.wago.com/2002-1891)



### Data

#### Physical data

Width	1 mm / 0.039 inches
Height	87.5 mm / 3.445 inches
Depth	32.9 mm / 1.295 inches

#### Mechanical Data

Mounting type	snap-on type
---------------	--------------

#### Material Data

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	gray
Material group	I
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.084 MJ
Weight	2.4 g

#### Commercial data

Product Group	22 (TOPJOB S)
---------------	---------------

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.


eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 8.0	EC000886
ETIM 7.0	EC000886
PU (SPU)	100 (25) pcs
Packaging type	box
Country of origin	DE
GTIN	4045454371906
Customs tariff number	85389099990

## Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

## Approvals / Certificates

### Declarations of conformity and manufacturer's declarations

Logo	Approval	Additional Approval Text	Certificate name
	<b>ATEX-Attestation of Conformity</b> WAGO GmbH & Co. KG	-	-
	<b>Railway</b> WAGO GmbH & Co. KG	-	Railway Ready

### Approvals for hazardous areas

Logo	Approval	Additional Approval Text	Certificate name
	<b>ATEX</b> KIWA Netherlands B.V.	EN 60079	KIWA 17ATEX0030 U
	<b>CCC</b> CNEX	GB/T 3836.3	2020312313000180 (Ex ec IIC Gc)
	<b>IECEX</b> KIWA Netherlands B.V.	EN 60079	IECEX KIWA 17.0014 U (Ex ec IIC Gc)

Subject to changes. Please also observe the further product documentation!







WAGO GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.




## Required accessories

### End plate



#### Through terminal block

	<b>Item no.: 2002-1802</b> 4-conductor through terminal block; 2.5 mm <sup>2</sup> ; with test option; same profile as 4-conductor disconnect terminal block; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; orange	<a href="http://www.wago.com/2002-1802">www.wago.com/2002-1802</a>
	<b>Item no.: 2002-1801</b> 4-conductor through terminal block; 2.5 mm <sup>2</sup> ; with test option; same profile as 4-conductor disconnect terminal block; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; gray	<a href="http://www.wago.com/2002-1801">www.wago.com/2002-1801</a>
	<b>Item no.: 2002-1804</b> 4-conductor through terminal block; 2.5 mm <sup>2</sup> ; with test option; for Ex e II and Ex i applications; same profile as 4-conductor disconnect terminal block; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; blue	<a href="http://www.wago.com/2002-1804">www.wago.com/2002-1804</a>
	<b>Item no.: 2202-1801</b> 4-conductor through terminal block; with push-button; 2.5 mm <sup>2</sup> ; with test option; same profile as 4-conductor disconnect terminal block; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; gray	<a href="http://www.wago.com/2202-1801">www.wago.com/2202-1801</a>
	<b>Item no.: 2202-1802</b> 4-conductor through terminal block; with push-button; 2.5 mm <sup>2</sup> ; with test option; same profile as 4-conductor disconnect terminal block; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; orange	<a href="http://www.wago.com/2202-1802">www.wago.com/2202-1802</a>
	<b>Item no.: 2202-1804</b> 4-conductor through terminal block; with push-button; 2.5 mm <sup>2</sup> ; with test option; same profile as 4-conductor disconnect terminal block; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; blue	<a href="http://www.wago.com/2202-1804">www.wago.com/2202-1804</a>

#### Disconnect terminal block for test and measurement

	<b>Item no.: 2002-1874/401-000</b> 4-conductor disconnect/test terminal block; with mechanical interlock; with test option; orange disconnect link; suitable for Ex i applications; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; blue	<a href="http://www.wago.com/2002-1874/401-000">www.wago.com/2002-1874/401-000</a>
	<b>Item no.: 2002-1872/401-000</b> 4-conductor disconnect/test terminal block; with mechanical interlock; with test option; orange disconnect link; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; orange	<a href="http://www.wago.com/2002-1872/401-000">www.wago.com/2002-1872/401-000</a>
	<b>Item no.: 2002-1871/401-000</b> 4-conductor disconnect/test terminal block; with mechanical interlock; with test option; orange disconnect link; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; gray	<a href="http://www.wago.com/2002-1871/401-000">www.wago.com/2002-1871/401-000</a>

#### Disconnect terminal block

	<b>Item no.: 2002-1871</b> 4-conductor disconnect/test terminal block; with test option; orange disconnect link; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; gray	<a href="http://www.wago.com/2002-1871">www.wago.com/2002-1871</a>
	<b>Item no.: 2002-1872</b> 4-conductor disconnect/test terminal block; with test option; orange disconnect link; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; Push-in CAGE CLAMP®; 2,50 mm <sup>2</sup> ; orange	<a href="http://www.wago.com/2002-1872">www.wago.com/2002-1872</a>

**Item no.: 2002-1874**

Subject to changes. Please also observe the further product documentation!



4-conductor disconnect/test terminal block; with test option; orange disconnect link; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm<sup>2</sup>; Push-in CAGE CLAMP<sup>®</sup>; 2,50 mm<sup>2</sup>; blue [www.wago.com/2002-1874](http://www.wago.com/2002-1874)



**Item no.: 2202-1871**  
4-conductor disconnect/test terminal block; with push-button; with test option; orange disconnect link; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm<sup>2</sup>; Push-in CAGE CLAMP<sup>®</sup>; 2,50 mm<sup>2</sup>; gray [www.wago.com/2202-1871](http://www.wago.com/2202-1871)



**Item no.: 2202-1874**  
4-conductor disconnect/test terminal block; with push-button; with test option; orange disconnect link; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm<sup>2</sup>; Push-in CAGE CLAMP<sup>®</sup>; 2,50 mm<sup>2</sup>; blue [www.wago.com/2202-1874](http://www.wago.com/2202-1874)



**Item no.: 2202-1872**  
4-conductor disconnect/test terminal block; with push-button; with test option; orange disconnect link; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm<sup>2</sup>; Push-in CAGE CLAMP<sup>®</sup>; 2,50 mm<sup>2</sup>; orange [www.wago.com/2202-1872](http://www.wago.com/2202-1872)

Carrier terminal block for modules and plugs



**Item no.: 2002-1861**  
4-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm<sup>2</sup>; Push-in CAGE CLAMP<sup>®</sup>; 2,50 mm<sup>2</sup>; gray [www.wago.com/2002-1861](http://www.wago.com/2002-1861)



**Item no.: 2202-1861**  
4-conductor carrier terminal block; with push-button; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm<sup>2</sup>; Push-in CAGE CLAMP<sup>®</sup>; 2,50 mm<sup>2</sup>; gray [www.wago.com/2202-1861](http://www.wago.com/2202-1861)

Fuse terminal block



**Item no.: 2002-1881**  
4-conductor fuse terminal block; for mini-automotive blade-style fuses; with test option; without blown fuse indication; 2.5 mm<sup>2</sup>; Push-in CAGE CLAMP<sup>®</sup>; 2,50 mm<sup>2</sup>; gray [www.wago.com/2002-1881](http://www.wago.com/2002-1881)



**Item no.: 2202-1881**  
4-conductor fuse terminal block; for mini-automotive blade-style fuses; per DIN 7258-3f, ISO 8820-3; with test option; with push-button; without blown fuse indication; 2.5 mm<sup>2</sup>; Push-in CAGE CLAMP<sup>®</sup>; 2,50 mm<sup>2</sup>; gray [www.wago.com/2202-1881](http://www.wago.com/2202-1881)

Optional accessories

End plate

Switching module



**Item no.: 2042-1008**  
Switching module; with changeover rocker switch; Switching voltage: 250 VAC; translucent [www.wago.com/2042-1008](http://www.wago.com/2042-1008)



**Item no.: 2042-1108**  
Switching module; with momentary switch; Switching voltage: 250 VAC; translucent [www.wago.com/2042-1108](http://www.wago.com/2042-1108)

Solid-state relay module

Subject to changes. Please also observe the further product documentation!



**Item no.: 2042-7304**

Solid-state relay module; Nominal input voltage: 24 VDC; Limiting continuous current: 0.5 A; Railway; Frequency: 100 kHz; Module width: 15 mm

[www.wago.com/2042-7304](http://www.wago.com/2042-7304)



**Item no.: 2042-7504**

Solid-state relay module; Nominal input voltage: 24 VDC; Output voltage range: 0 ... 48 VDC; Limiting continuous current: 4 A; 2-wire connection; Railway; Green status indicator; Module width: 10 mm

[www.wago.com/2042-7504](http://www.wago.com/2042-7504)



**Item no.: 2042-7204**

Solid-state relay module; Nominal input voltage: 24 VDC; Output voltage range: 3 ... 60 VDC; Limiting continuous current: 0.1 A; 2-wire connection; Railway; Frequency: 10 kHz; Green status indicator; Module width: 10 mm

[www.wago.com/2042-7204](http://www.wago.com/2042-7204)



**Item no.: 2042-7604**

Solid-state relay module; Nominal input voltage: 24 VDC; Output voltage range: 16.8 ... 30 VDC; Limiting continuous current: 5 A; 3-wire connection/high-side switching; Railway; Frequency: 5 kHz; Green status indicator; Module width: 15 mm

[www.wago.com/2042-7604](http://www.wago.com/2042-7604)

Relay module



**Item no.: 2042-3074**

Relay module; Nominal input voltage: 24 VDC; 3 break contacts and 1 make contact; Limiting continuous current: 5 A; Railway; Green status indicator; Module width: 25 mm

[www.wago.com/2042-3074](http://www.wago.com/2042-3074)



**Item no.: 2042-3014**

Relay module; Nominal input voltage: 24 VDC; 2 make contact; Limiting continuous current: 8 A; Railway; Green status indicator; Module width: 20 mm

[www.wago.com/2042-3014](http://www.wago.com/2042-3014)



**Item no.: 2042-3034**

Relay module; Nominal input voltage: 24 VDC; 1 changeover contact; Limiting continuous current: 10 A; Railway; Green status indicator; Module width: 15 mm

[www.wago.com/2042-3034](http://www.wago.com/2042-3034)



**Item no.: 2042-3044**

Relay module; Nominal input voltage: 24 VDC; 2 changeover contacts; Limiting continuous current: 8 A; Railway; Green status indicator; Module width: 20 mm

[www.wago.com/2042-3044](http://www.wago.com/2042-3044)



**Item no.: 2042-3024**

Relay module; Nominal input voltage: 24 VDC; 4 make contacts; Limiting continuous current: 5 A; Railway; Green status indicator; Module width: 25 mm

[www.wago.com/2042-3024](http://www.wago.com/2042-3024)



**Item no.: 2042-3064**

Relay module; Nominal input voltage: 24 VDC; 1 break and 1 make contact; Limiting continuous current: 8 A; Railway; Green status indicator; Module width: 20 mm

[www.wago.com/2042-3064](http://www.wago.com/2042-3064)



**Item no.: 2042-3084**

Relay module; Nominal input voltage: 24 VDC; 2 break and 2 make contacts; Limiting continuous current: 5 A; Railway; Green status indicator; Module width: 25 mm

[www.wago.com/2042-3084](http://www.wago.com/2042-3084)

Subject to changes. Please also observe the further product documentation!



**Item no.: 2042-3819**

Relay module; Nominal input voltage: 24 ... 230 V AC/DC; 2 make contact; Limiting continuous current: [www.wago.com/2042-3819](http://www.wago.com/2042-3819)  
5 A; Green status indicator; Module width: 20 mm



**Item no.: 2042-3829**

Relay module; Nominal input voltage: 24 ... 230 V AC/DC; 4 make contacts; Limiting continuous current: [www.wago.com/2042-3829](http://www.wago.com/2042-3829)  
3 A; Green status indicator; Module width: 25 mm



**Item no.: 2042-3869**

Relay module; Nominal input voltage: 24 ... 230 V AC/DC; 1 break and 1 make contact; Limiting continuous current: [www.wago.com/2042-3869](http://www.wago.com/2042-3869)  
5 A; Green status indicator; Module width: 20 mm



**Item no.: 2042-3889**

Relay module; Nominal input voltage: 24 ... 230 V AC/DC; 2 break and 2 make contacts; Limiting continuous current: [www.wago.com/2042-3889](http://www.wago.com/2042-3889)  
3 A; Green status indicator; Module width: 25 mm



**Item no.: 2042-3849**

Relay module; Nominal input voltage: 24 ... 230 V AC/DC; 2 changeover contacts; Limiting continuous current: [www.wago.com/2042-3849](http://www.wago.com/2042-3849)  
5 A; Green status indicator; Module width: 20 mm



**Item no.: 2042-3879**

Relay module; Nominal input voltage: 24 ... 230 V AC/DC; 3 break contacts and 1 make contact; Limiting continuous current: [www.wago.com/2042-3879](http://www.wago.com/2042-3879)  
3 A; Green status indicator; Module width: 25 mm



**Item no.: 2042-3839**

Relay module; Nominal input voltage: 24 ... 230 V AC/DC; 1 changeover contact; Limiting continuous current: [www.wago.com/2042-3839](http://www.wago.com/2042-3839)  
4 A; Green status indicator; Module width: 15 mm



**Item no.: 2042-3054**

Relay module; Nominal input voltage: 24 VDC; 1 break contact; Limiting continuous current: [www.wago.com/2042-3054](http://www.wago.com/2042-3054)  
6 A; Railway; Green status indicator; Module width: 10 mm



**Item no.: 2042-3004**

Relay module; Nominal input voltage: 24 VDC; 1 make contact; Limiting continuous current: [www.wago.com/2042-3004](http://www.wago.com/2042-3004)  
6 A; Railway; Green status indicator; Module width: 10 mm



**Item no.: 2042-3809**

Relay module; Nominal input voltage: 24 ... 230 V AC/DC; 1 make contact; Limiting continuous current: [www.wago.com/2042-3809](http://www.wago.com/2042-3809)  
3 A; Green status indicator; Module width: 10 mm

**Item no.: 2042-3859**

Subject to changes. Please also observe the further product documentation!



Relay module; Nominal input voltage: 24 ... 230 V AC/DC; 1 break contact; Limiting continuous current: [www.wago.com/2042-3859](http://www.wago.com/2042-3859)  
6 A; Green status indicator; Module width: 10 mm

## Downloads

### Documentation

#### Bid Text

2002-1891 X81 - Datei	19 Feb 2019	xml 2.6 kB	Download
--------------------------	-------------	---------------	----------

2002-1891 doc - Datei	27 Apr 2017	doc 24.1 kB	Download
--------------------------	-------------	----------------	----------

#### Additional Information

		pdf 2.2 MB	Download
--	--	---------------	----------

## CAD/CAE-Data

### CAD data

2D/3D Models 2002-1891		URL	Download
------------------------	--	-----	----------

### CAE data

EPLAN Data Portal 2002-1891		URL	Download
-----------------------------	--	-----	----------

WSCAD Universe 2002-1891		URL	Download
--------------------------	--	-----	----------

ZUKEN Portal 2002-1891		URL	Download
------------------------	--	-----	----------

## Environmental Product Compliance

### Compliance Search

Environmental Product Compliance 2002-1891 End and intermediate plate; 1 mm thick; gray		URL	Download
--	--	-----	----------

Subject to changes. Please also observe the further product documentation!



## Installation Notes

## Product family

### TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!