



- Industry Standard micro-ISO plug-in relay
- Up to 120A 12VDC inrush capability
- PCB Mounting option
- 40A Continuous current rating
- Cost effective

		RoHS Compliant				
Contacts		Ordering Code				
Contact arrangement	SPST-NO (1 Form A); SPDT (1 Form C)					
Contact material	AgNi0.15; AgNi90/10; AgSnOInO	D G 8 2 - 2 0 1 1 - 7 6 - 1 0 1 2 - H B D				
Max. switching voltage DC	16VDC (current dependent - see Fig 3)					
Rated load (max. continuous current) DC	40A/12VDC (NO); 30A/12VDC (NC)	Series Coil code:				
Max. switching current3 make	90A (120A:AgSnOInO) (NO); 45A (NC)	See table 1				
breal	40A (NO); 30A (NC)	Contact material				
Minimum load	AgNi0.15: 0.1A/12VDC, AgSnOInO: 0.5A/12VDC	20: AgNi 90/10				
Initial resistance	50mΩ, max. at 0.1A/6VDC	70: AgSnOInO				
Coil		80: AgNi 0.15				
Nominal voltage DC	624V					
Must release voltage	≥0.1Un	Contact arrangement				
Operating range of supply voltage	See table 1	11: SPDT (1 C/O, 1 Form C)				
Power consumption (approx.)	1.2W (SPST-NO) / 1.5W (SPDT) ; 1.8W with resistor	21: SPST-NO (1 N/O, 1 Form A)				
Insulation						
Insulation resistance	100MΩ at 500VDC, 50%RH	Environmental protection				
Dielectric strength coil to contac	t 500Vrms, 1min	3: In cover, sealed IP67				
open contacts	500Vrms, 1min	7: In cover, dust cover IP54				
General Data						
Operating time typ	. 9ms	Mounting & terminations				
Release time typ	. 7ms	5: For PCB				
Electrical life2 ops	. 2 x 10⁵	6: Flat blades				
Mechanical life ops	. 1 x 10 ⁷					
Environmental		Coil options				
Environmental protection	IP54, IP67 optional	Blank: UL Class F coil insulation				
Ambient temperature operating	-40 to 125°C (Derate above 85°C - consult factory)	H: UL Class H insulation for higher ambient				
storage	e -40 to +155°C	temperatures consult factory				
Shock resistance functiona	l 20g, 11ms					
destructive	e 100g	Parallel component options				
Vibration resistance	DA 1.27mm 10-40Hz / 40-70Hz:5g	Blank: No option R: Resistor (see table 1 for values)				
	DA 0.5mm 100-500Hz: 10g					
Dimensions L x W x H	23.5 x 15.7 x 26.0 mm (excluding terminals)	D: Diode (+85/-86)				
Weight approx	. Plug-in: 21g / PCB: 19g	DR: Diode reversed (-85/+86) - standard				
		BD: Bidirectional diode				

(1)


DURAKOOL

DG82 Series Micro Plug-in / PCB Automotive Relay

Coil Data Table										
Coil code	Nominal	Coil resistance (Ω) ±10%		Must operate	Allowable voltage (VDC)*		Must release	Parallel		
	voltage (VDC)	1 Form A	1 Form C	voltage max. (VDC)	1 Form A	1 Form C	voltage min. (VDC)	resistor (optional) (Ω)		
1006	6	32	25	3.6	10.4	9.2	0.6	170		
1012	12	123	97	7.2	20.4	18.1	1.2	680		
1024	24	483	384	14.4	40.4	36.0	2.4	2720		

* At ambient temperature of 85°C, maximum allowable voltage should be reduced by 28%

Dimensions mm Fig. 1 РСВ Туре Plug-In Type 5,7 max 5.7 mox 1 Form C (Z) 1 Form C (Z) 11.7 11.7 23.7mox 23.7 max 00 **\$** 0 26.0max 26.0max 4.5 4.5 4,5 4,5 12.0mox



Notes:

1: All parameters, unless otherwise specified, are measured at ambient temperature of 23°C.

2: Electrical life obtained at resistive or inductive load at 40A, 15VDC with suitable arc suppression circuit attached and with operating frequency of 1 op/sec. 3: Maximum make current refers to lamp load inrush current.

2