

## Product information

# 64 02 115

## Electronics End Cutting Nipper

DIN ISO 9654



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 56 HRC
- End Cutter, with small bevel
- Ball bearing chrome steel, oil hardened




### General

Article No.	64 02 115
EAN	4003773035343
Head	mirror polished
Handles	with multi-component grips
Weight	70 g
Dimensions	115 x 62 x 17 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities soft wire (diameter)	Ø 2.0 mm
Cutting capacities medium hard wire (diameter)	Ø 1.0 mm
Cutting capacities hard wire (diameter)	Ø 0.6 mm
Head width (A)	11 mm
Jaw length (B)	6 mm
Jaw thickness (joint) (D)	7.5 mm
Cutting edge length mm (C)	16 mm

**Technical details**



*technical change and errors excepted*

