



MASTER VALUE LEDspot MV



MASTERLEDspot VLE D 6.2-80W GU10 927 36D UK

Delivering a warm, halogen-like accent beam, the MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it achieves more natural colours, creating cosy and comfortable ambience for residential and hospitality projects, and emphasising the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. The MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General information	
Lighting Technology	LED
Switching Cycle	50,000
Nominal lifetime	25,000 h
Cap base	GU10 [GU10]

Light technical	
Colour Code	927 [CCT of 2700K]
Beam angle (nom.)	36 degree(s)
Luminous Flux	575 lm


Luminous intensity (nom.)	850 cd
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous Efficacy (rated) (Nom)	92.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	90
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	575 lm
Flickering value (PstLM)	1

MASTER VALUE LEDspot MV

Stroboscopic effect	0.4
Operating and electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	6.2 W
Lamp current (nom.)	33 mA
Wattage equivalent	80 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.88
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb shape	PAR16 [PAR 2 inch/50 mm]

Approval and application	
Energy Efficiency Class	F
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	7 kWh
EPREL registration number	391905
EU RoHS compliant	Yes
Product data	
Full EOC	871869967541701
Order product name	MASLEDspot VLE D 6.2-80W GU10 927 36D UK
Order code	67541701
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
Material number (12NC)	929002059599
Full product name	MASTERLEDspot VLE D 6.2-80W GU10 927 36D UK
EAN/UPC - Case	8719514405677


Dimensional drawing




Product	D	C
MASLEDspot VLE D 6.2-80W GU10 927 36D UK	50 mm	54 mm

MASTER VALUE LEDspot MV


Photometric data



Light Distribution Diagram - MASLEDspot VLE D 6.2-80W GU10 927 36D UK




Spectral Power Distribution Colour - MASLEDspot VLE D 6.2-80W GU10 927 36D UK




Technical Parameters (1) Photo Lighting (3) Page 11

Accent Lighting Spots - MASLEDspot VLE D 6.2-80W GU10 927 36D UK

Lifetime



Lumen Maintenance Diagram - MASLEDspot VLE D 6.2-80W GU10 927 36D UK



Life Expectancy Diagram - MASLEDspot VLE D 6.2-80W GU10 927 36D UK

MASTER VALUE LEDspot MV

