



MASTER Value Glass LED bulbs



MASTER VLELEDBulbDT3.4-40WB22 927A60CL G UK

Featuring a classic heritage design, these filament LED bulbs combine the familiar shapes of incandescent bulbs with the benefits of long-lasting LED technology. These MASTER Value Glass LED bulbs offer more energy savings than normal glass LED bulbs. At the same time, they also provide customers with good light experience, enhanced by excellent dimming performance (dimmable glass LED bulbs). MASTER Value Glass LED Bulbs deliver significant energy savings, using 30% less energy compared to normal LED bulbs and provide excellent quality of light. By offering a lifetime of 15,000 hours, these dimmable LED bulbs also reduce maintenance costs.

Product data

General information	
Cap base	B22 [B22]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20000
Tier	MASTER Value
Light technical	
Colour Code	922-927 [CCT of 2,200 K-2,700 K]
Luminous flux (nom.)	470 lm
Colour designation	Warm Glow (WG)
Correlated Colour Temperature (Nom)	2200 2700 K
Luminous efficacy (rated) (nom.)	138.00 lm/W
Colour consistency	<6

Colour rendering index (nom.)	90
LLMF at end of nominal lifetime (nom.)	70 %
Operating and electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	3.4 W
Lamp current (nom.)	24 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.6
Voltage (Nom)	220-240 V

MASTER Value Glass LED bulbs

Temperature

T-Case maximum (nom.) 70 °C

Controls and dimming

Dimmable Yes

Mechanical and housing

Lamp Finish Clear

Bulb shape A60 [A 60mm]

Approval and application

Energy Efficiency Class D

Energy consumption kWh/1,000 hours 4 kWh

1109130

Product data

Full product code 871951432469501

Order product name MASTER VLELEDBulbDT3.4-40WB22 927A60CL G UK

EAN/UPC – product 8719514324695

Order code 32469501


SAP numerator – quantity per pack 1

Numerator – packs per outer box 10

SAP material 929003010199

Net Weight (Piece) 0.030 kg


Dimensional drawing




MASTER VLELEDBulbDT3.4-40WB22 927A60CL G UK

Product	D	C
MASTER VLELEDBulbDT3.4-40WB22 927A60CL G UK	60 mm	103 mm

Photometric data



Spectral Power Distribution Colour



Light Distribution Diagram

